

Lenovo V15 G4 IRU

Empower your workforce with this ultra-powerful device, designed to drive collaboration and deliver performance from anywhere. Weighing at just 1.67kg (3.68 lbs), the Lenovo V15 G4 IRU is fitted with 13th Gen Intel U Series Core i7 processors and up to 1TB storage to sail you through the busiest days at work. From 3D modeling to gaming and video editing, make the most with the device's integrated Intel UHD and Intel Iris Xe Graphics.



Work, play and binge watch your favorite shows with the 15.6" FHD screen, 16:9 aspect ratio and anti-glare display, that rival reality. The HD audio chip, 1.5W x 2 Dolby Audio stereo speakers, HD 720p camera offers unmatched audio and video quality during virtual meetings and events.

The Wi-Fi 6 optimizes connectivity enables faster downloads and eliminates signal interference. With standard ports such as USB 2.0 and USB-C 3.2 Gen 1, the device facilitates seamless data transfers and connectivity to surrounding monitors and peripherals.

The integrated 45Wh battery supports rapid charging and lasts for up to 8.4 hours.

Lenovo devices that are a class apart

The Lenovo V Series provides security, data protection and productivity features in an affordable package.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center
 Lenovo pays for all shipping between the customer and service facility
 Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo 15.6" Laptop Casual Backpack

Extra cushioning and padding for maximum comfort
 Waterproof fabric to keep your gadgets dry and safe
 Conveniently placed compartments and pockets for easy access.



PN: GX40Q17225

Lenovo Essential Compact Wireless Mouse

Compact and easy to carry, weighs just under 50g (1.76oz)
 Ergonomic and ambidextrous design with 3 buttons
 Highly durable design, tested to last up to 8 million clicks



PN: 4Y50R20864 – (with battery) 4Y50R20865 – (w/o battery)

Lenovo V15 G4 IRU

Key Specifications

Processor

13th Gen Intel U Series Core i3 / i5 / i7

Operating System

Windows 11 Pro, Windows 11 Home, Windows 11 Home Single Language, Windows 11 DG Windows 10 Pro 64

Display

15.6", FHD (1920x1080), TN, 16:9 Aspect Ratio, Anti-glare surface
- 250nits Brightness, 45% NTSC Color Gamut

15.6", FHD (1920x1080), IPS, 16:9 Aspect Ratio, Anti-glare surface
- 300nits Brightness, 45% NTSC Color Gamut

Touchscreen

Non-touch

Graphics

Intel UHD Graphics (Integrated), Intel Iris Xe Graphics eligible (Integrated)

Memory

Up to 16GB DDR4-3200 offering, 1x Soldered + 1x SO-DIMM

Storage

Model with 38Wh battery:
up to two drives, 1x 2.5" HDD + 1x M.2 SSD

2.5" HDD up to 1TB
M.2 2242 SSD up to 512GB

Model with 45Wh battery:
up to 1x 512GB M.2 2242 PCIe NVMe SSD

Audio

High Definition (HD) Audio
1.5W x2, Dolby Audio Stereo speakers
Dual-array microphone with noise-cancelling technology

Battery†

38Wh (up to 6.4 hr) or 45Wh (up to 6.8 hr) battery, Rapid Charge support

Power Adapter

One of the following
65W Round Tip (3-pin)
65W USB-C (3-pin)

Camera

HD 720p with Privacy Shutter

Keyboard

6-row, spill-resistant, numeric keypad,
Mylar surface touchpad, 62 x 104 mm (2.44 x 4.09 inches)

Dimensions

359.2 x 235.8 x 19.9 mm (14.14 x 9.28 x 0.78 inches)

Weight

Starting at 1.65 kg (3.63 lbs)

Green Certifications

Optional EPEAT Silver, ENERGY STAR 8.0, ErP Lot 6, ErP Lot 26, FSC certified carton, RoHS compliant

Other Certifications

MIL-STD-810H military tested, TUV Rheinland Low Blue Light (Software Solution)

Connectivity

I/O Ports

1x USB 2.0, 1x USB 3.2 Gen 1, 1x USB-C 3.2 Gen 1, 1x HDMI, 1x Ethernet (RJ-45), 1x Headphone / microphone combo jack (3.5mm), 1x Power connector

WLAN + Bluetooth

One of the following
11ac 2x2 + BT5.1
Wi-Fi 6, 11ax 2x2 + BT5.1

Security & Privacy

Firmware TPM 2.0
Kensington Nano Security Slot
Camera privacy shutter