

15W Wireless Charging Pad for iPhone - MagSafe Charging, Adjustable Stand, 5 ft. Cable, White

MODEL NUMBER: U280MS-005



Wirelessly charges a MagSafe-compatible iPhone 12 and above with up to 15W of power.

Features

Wireless Cell Phone Charger Delivers Power to Apple iPhone

Who wants to plug and unplug power cords when you want to charge your iPhone? The U280MS-005 makes charging easier by doing it wirelessly. Just place your Qi-certified iPhone (iPhone 12 and above) on the 15W charging pad. That's all there is to it. Connect no cable to your phone. The U280MS-005 is developed and tested to MFi standards.

Supports Apple MagSafe Technology for a Secure Charge Every Time

Built-in MagSafe technology helps ensure your iPhone and the U280MS-005 wireless charging pad work together for a complete charge whenever you need it. Magnets inside both your phone and the charging pad prevent the iPhone from falling off the charger and being disconnected while charging. MagSafe also allows the U280MS-005 to deliver up to 15W of power to get your iPhone to battery capacity even faster.

Adjustable Stand Gives You More Flexibility Over Charging

You can charge your iPhone while it lays flat on the charging pad, or you can use the adjustable kickstand for flexible placement during charging. You can place the phone vertically to read notifications and messages while it charges or horizontally to stream video. Note: A device that supports non-magnetic wireless charging can only be charged while laying flat on the charging pad.

Compact Charging Pad Fits Comfortably on Any Counter, Table or Workspace

The portable U280MS-005 takes up hardly any space, making it ideal for your bedside table or for carrying in a backpack or laptop bag. A built-in five-foot (1.5-meter) USB-C cable connects the charging pad to a wall charger, such as the 9V 2.2A U280-W01-20C1-G (sold separately).

Highlights

- MagSafe technology snaps your smartphone into place for secure charging every time
- Developed and tested to Apple's MFi standards, including charging up to 15W
- Charges your iPhone through its MagSafe case to avoid the hassle of removing it
- Adjustable stand allows scrolling, texting or watching video vertically or horizontally
- Compatible with Apple iPhone 14, iPhone 13 and iPhone 12 smartphone series

System Requirements

- Compatible with all Qi-enabled smartphones
- Magnetic charging function requires a compatible smartphone or other device
- Requires a USB-C wall charger up to 20W or a laptop or PC with a USB-C port

Package Includes

- U280MS-005 15W Wireless Charging Pad
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332279316
Product Type	Charging Pad
Charging Form Factor	Pad/Stand



Powering Business Worldwide

TRIPP LITE
SERIES

Device Compatibility	Phone
Technology	Wireless
Country/Region	Global
Host Connector	USB C (MALE)
INPUT	
Nominal Input Voltage(s) Supported	5V DC; 9V DC
Input Connection Type	USB Type-C
Input Cord Gauge (AWG)	24
Input Plug Type	USB-C (MALE)
Bus Powered	No
OUTPUT	
Output Capacity (Watts)	15
Overload Protection	Yes
POWER	
Power Source Type	USB
Power Source	Unit (Included)
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	Magnetic Charger
Connector Style	Straight
CHARGING	
Number of Charging Ports	0
Total Charging Amps	2.2
Total Charging Watts	15
Charging Method	Wireless
Charging Port Type	WIRELESS CHARGING COIL
Charging Ports Details	Charge a MagSafe compatible iPhone 14, iPhone 13 or iPhone 12 series smartphone with up to 15 Watts of power
Charging Ports / Amps	2A
Magnetic Charging	Yes
Wireless Charging	Yes
Overcharge Protection	Yes
Compatible Devices	Smartphone



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	White
Material of Construction	Plastic
Cable Jacket Color	White
Connector Color	White
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	3.8
Wire Gauge (AWG)	22
Charging Station Form Factor	Pad/Stand
Cable Length (ft.)	5
Cable Length (m)	1.52
Cable Length (in.)	60
Cable Length (cm)	152.4
Total Number of Ports	1
Unit Dimensions (hwd / in.)	2.350 x 2.350 x 0.657
Unit Dimensions (hwd / cm)	1.67 x 5.98
Unit Dimensions (hwd / mm)	16.7 x 59.8
Unit Dimensions (in.)	2.48 x 0.66
Unit Packaging Type	Box
Unit Weight (lbs.)	0.2196
Unit Weight (kg)	0.10
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 104°F (-20° to 40°C)
Operating Humidity Range	10% to 80% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Driver Required	No
Qi Compliant	Yes
STANDARDS & COMPLIANCE	

Product Certifications	ICES (Canada); MFi
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS3; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.