

PCAP TOUCH SOLUTION

75" Integrated Touchscreen Display


TSI Touch's Projected Capacitive (PCAP)
Metal Mesh solution for Samsung®'s 75"
Q-series monitors allows for a highly
accurate touchscreen experience. Through
the use of advanced Metal Mesh sensor
technology, coupled with a state of the art
controller, our PCAP touch solution provides
the interactive experience your end users
expect, all while requiring little to no
maintenance.

Our double pan design provides an edge to edge glass flat fronted touch experience, allowing for easy cleaning and sanitization, as well as providing considerable protection to the display.



SPECIFICATION	DETAIL			
Product Name	Touchscreen only	QB75B with Integrated Touchscreen	QH75B with Integrated Touchscreen	QM75B with Integrated Touchscreen
Part Number	TSI75NS156HJGZZ	TSI75PSXA6HJGZZ	TSI75PSXM6HJGZZ	TSI75PSWP6HJGZZ
Touchscreen Type	Projected Capacitive Metal Mesh on Anti-Glare Glass			
Number of Touch Points	40 points simultaneous touch maximum			
Touchscreen Interface	USB 2.0 Type A Male connector with 2 meter cable			
Touchscreen Power	USB 5VDC Maximum 1.6W Peak			
Touch Response Time	5ms			
Touch Accuracy	0.53% of sensor area			
Minimum Object Separation	2.64%			
Orientation Compatibility	Landscape, Portrait			
Brightness (w/touchscreen)	N/A	308 nit	616 nit	440 nit
Brightness (w/o touchscreen)	N/A	350 nit	700 nit	500 nit
Display Resolution	3840 x 2160			
Contrast Ratio	4000:1			

Viewing Angle	178/178	
Aspect Ratio	16:9	
Video Inputs	HDMI 2.0 (3)	
Audio Output	Stereo Mini Jack	
Operating System Compatability	Microsoft® Windows®, Samsung® SoC, Google® Chrome®, Android®, MacOS®, and many popular Linux® Distributions - HID Compliant Compatability	
Display Power Supply	AC 100 - 240 V, 50/60 Hz	
Display Power Consumption	Typical: 161 Watts/Max: 231 Watts	
Operating Temperature	0°~40° C	
Humidity	10~80% Non-condensing	
Integrated Dimensions (W x H x D)	68.32" x 39.94" x 2.32"	
Viewable Area	65.0" x 36.61"	
Integrated Display Weight	162.7 lbs.	
Packaged Weight	232.1 lbs.	
VESA Pattern	400 x 400 mm	
Recommended Duty Cycle	QB: 16/7 \\\ QH and QM: 24/7	
Service and Support	3 Year Repair & Return Warranty	
In the Box	Integrated Touchscreen Display, Quick Setup Guide, Warranty Card, Power Cord, Remote Controller, Batteries	



For more information, please visit www.tsitouch.com, email sales@tsitouch.com, or call 802-874-0123

*Drawing not to scale.

Specifications and designs are subject to change without notice. Packaged weights are approximate.

Rev. 1.1