

Xerox® C410 Color Printer



Work doesn't slow down,
and your printer shouldn't either.

PRINT SPEED (UP TO:)	
One-sided Speed¹	Color: Up to 42/40 ppm Letter/A4; Black-and-White: Up to 42/40 ppm Letter/A4
Two-sided Speed¹	Color: Up to 21/20 ppm Letter/A4; Black-and-White: Up to 21/20 ppm Letter/A4
Monthly Duty Cycle² (Up To:) Pages Per Month	125,000
Recommended Average Monthly Print Volume (Up To:) Pages Per Month	10,000
Processor/Memory/Storage Clock Speed/Cores Memory/Storage	1 GHz Dual Core Processor 1GB RAM 8GB eMMC/ Optional: 500+GB HDD
Connectivity Device Connectivity	Hi-Speed USB 2.0 (Type A), Hi-Speed USB (Type B) Gigabit Ethernet/ Optional: Wireless Network Adapter (802.11 b/g/n/ac)
Imaging Technology	Color Laser
PRINT	
Print Resolution (Up To:)	1200 x 1200 dpi, 4800 Color Quality
First-Print-Out Time (As Fast As:)	As fast as 6.4 seconds color/6.1 seconds black-and-white
Page Description Languages	PostScript® 3 Emulation, PCL® 6 Emulation, PCL 5 Emulation, PDF v1.7 Emulation, Direct Image
Print Features	One Touch UI, Print Quality, Normal, Secure, Saved and Sample Set Job Types, Duplex, Orientation, Collation, Print Job ID in Margins, Draft Mode, N-up, Booklet Layout, Watermark, Tray and Toner Status, Rotate Image 180 Degrees, Saved Settings, Earth Smart Settings
MOBILE AND CLOUD READY	
Mobile Printing	Apple AirPrint, Mopria Print Service, Chromebook, Wi-Fi Direct ^{®3}
Xerox® Workplace Suite and Xerox® Workplace Cloud	Optional: Xerox Workplace Cloud and Suite is the complete print management platform for security, cost control and mobility delivering workflow productivity to office and hybrid workers. Available as an on-premises version (Workplace Suite) or a cloud-based (Workplace Cloud) it provides the ultimate flexibility in freeing up IT teams time to focus on core business priorities. (Select models may require additional optional equipment to enable.)
Cloud Connectivity	Yes (via Xerox Print and Scan Experience)

Xerox C410 Color Printer

PRINT DETAILS	
First-Print-Out Time – Color (As Fast As:)	6.4 seconds
First-Print-Out Time – B&W (As Fast As:)	6.1 seconds
Resolution (Up To:)	1200 x 1200 dpi, 4800 Color Quality
Page Description Languages	PostScript® 3 Emulation, PCL® 6 Emulation, PCL 5 Emulation, PDF v1.7 Emulation, Direct Image
Unprintable Page Margin	Print: 4.2 mm from each edge
Print from USB	Yes. Documents; PDF, HTML, XPS, Microsoft file formats (.doc, .docx, .xls, .xlsx, .ppt, .pptx) Images: .dcm, .gif, .JPEG (.jpg), .bmp, .pcx, .TIFF (.tif), .png
Print Driver Types/Operating Systems	Windows® 11, Windows® 10, Windows Server 2022, Windows Server 2019, Windows Server 2016, Windows Server 2012 R2, Windows Server 2012, macOS 13.x, macOS 12.x, macOS 11.x. Microsoft Universal Print. For the latest information about supported Operating Systems, please visit our Drivers & Downloads page and specify your device at support.xerox.com .
Network Protocols	TCP/IP: HTTP/HTTPS, IPP, LPR/LDP, Raw Socket Printing/Port 9100, IPv4/IPv6, MS Web Services WSD-Print, 802.1x, SNMP, ThinPrint, Universal Print, Bonjour
Font Capability	PCL6 89 scalable fonts, 2 bitmapped PS emulation 158 scalable fonts
DEVICE MANAGEMENT	
Device Management	Xerox Easy Assist, Remote Operator Panel, Embedded Web Server
Xerox® CentreWare® Web Software	Yes
SECURITY	
Security Protocols/Features	Digitally Signed Firmware Updates, Trusted Platform Module (TPM), TLS 1.3, FIPS 140-2, Certificate Management, Secure Password Reset, TCP Connection Filtering, Port Filtering, Access Controls, Confidential Print, Non-Volatile Memory Wipe, Protected USB Ports, IPsec, Image Overwrite ⁴
WI-FI SECURITY (REQUIRES WIRELESS NETWORK ADAPTER)	
Authentication and Encryption Methods	Infrastructure (BSS) Mode, WEP Encryption (64 & 128 bit keys), WPA2/WPA Personal AES PSK, WPA2-Personal, WPA3 Support, 802.1x; EAP-MD5, EAP-MSCHAPv2, EAP-TLS, EAP-TTLS (CHAP/MSCHAP/MSCHAPv2/PAP), LEAP, PEAP
PAPER HANDLING	
MANUAL FEED SLOT	
Standard/Optional	Standard
Capacity	1 sheet
Minimum Media Size (in)	3 x 5 in
Minimum Media Size (mm)	76 x 127 mm
Maximum Media Size (in)	Legal (8.5 x 14 in)
Maximum Media Size (mm)	216 x 356 mm
Minimum Media Weight (gsm)	60 gsm
Minimum Media Weight – Duplex (gsm)	60 gsm
Maximum Media Weight (gsm)	200 gsm
Maximum Media Weight – Duplex (gsm)	105 gsm
Media Types Supported	Plain Paper, Light Paper, Heavy Paper, Letterhead, Cardstock, Recycled, Bond, Labels, Glossy, Vinyl, Pre-Printed, Envelope, Colored Paper, Rough Cotton, Custom
MAIN TRAY	
Standard/Optional	Standard
Capacity (Up To:)	250 sheets of 20 lb bond/75 gsm
Minimum Media Size (in)	3.9 x 5.8 in
Minimum Media Size (mm)	98 x 148 mm
Maximum Media Size (in)	Legal (8.5 x 14 in)
Maximum Media Size (mm)	216 x 356 mm
Minimum Media Weight (gsm)	60 gsm
Minimum Media Weight – Duplex (gsm)	60 gsm
Maximum Media Weight (gsm)	200 gsm
Maximum Media Weight – Duplex (gsm)	105 gsm
Media Types Supported	Plain Paper, Light Paper, Heavy Paper, Letterhead, Cardstock, Recycled, Bond, Labels, Glossy, Vinyl, Pre-Printed, Envelope, Colored Paper, Rough Cotton, Custom

Xerox C410 Color Printer

OPTIONAL 550+100-SHEET TRAY (INCLUDES 550-SHEETS STANDARD CAPACITY AND ADDITIONAL 100-SHEET BYPASS TRAY)	
550+100-SHEET TRAY – 100-SHEET BYPASS TRAY	
Capacity (Up To:)	100 sheets of 20 lb bond/75 gsm
Minimum Media Size (in)	3 x 5 in
Minimum Media Size (mm)	76 x 127 mm
Maximum Media Size (in)	Legal (8.5 x 14 in)
Maximum Media Size (mm)	216 x 356 mm
Minimum Media Weight (gsm)	60 gsm
Minimum Media Weight – Duplex (gsm)	60 gsm
Maximum Media Weight (gsm)	176 gsm
Maximum Media Weight – Duplex (gsm)	105 gsm
Media Types Supported	Plain Paper, Light Paper, Heavy Paper, Letterhead, Cardstock, Recycled, Bond, Labels, Glossy, Vinyl, Pre-Printed, Envelope, Colored Paper, Rough Cotton, Custom
550+100-SHEET TRAY – 550-SHEET TRAY	
Capacity (Up To:)	550 sheets of 20 lb bond/75 gsm
Minimum Media Size (in)	5.8 x 8.3 in
Minimum Media Size (mm)	148 x 210 mm
Maximum Media Size (in)	Legal (8.5 x 14 in)
Maximum Media Size (mm)	216 x 356 mm
Minimum Media Weight (gsm)	60 gsm
Minimum Media Weight – Duplex (gsm)	60 gsm
Maximum Media Weight (gsm)	176 gsm
Maximum Media Weight – Duplex (gsm)	105 gsm
Media Types Supported	Plain Paper, Light Paper, Heavy Paper, Letterhead, Cardstock, Recycled, Bond, Labels, Glossy, Vinyl, Pre-Printed, Colored Paper, Rough Cotton, Custom
OPTIONAL 550-SHEET TRAY (REQUIRES THE 550+100-SHEET TRAY)	
Capacity (Up To:)	550 sheets of 20 lb bond/75 gsm (Add up to 2 additional 550-sheet trays)
Minimum Media Size (in)	5.8 x 8.3 in
Minimum Media Size (mm)	148 x 210 mm
Maximum Media Size (in)	Legal (8.5 x 14 in)
Maximum Media Size (mm)	216 x 356 mm
Minimum Media Weight (gsm)	60 gsm
Minimum Media Weight – Duplex (gsm)	60 gsm
Maximum Media Weight (gsm)	176 gsm
Maximum Media Weight – Duplex (gsm)	105 gsm
Media Types Supported	Plain Paper, Light Paper, Heavy Paper, Letterhead, Cardstock, Recycled, Bond, Labels, Glossy, Vinyl, Pre-Printed, Envelope, Colored Paper, Rough Cotton, Custom
STANDARD/MAXIMUM INPUT CAPACITY	
Standard Input Capacity	251
Maximum Input Capacity	2001
OUTPUT CAPACITY	
Output Capacity	125

Xerox C410 Color Printer

DEVICE SPECIFICATIONS	
ELECTRICAL REQUIREMENTS	
North America	100 to 127 volts (V) (100 – 110 Japan) at 47 to 53 hz or 57 to 63 hertz (HZ) nominal 90 to 140 volts (90 – 110 Japan), extreme
Europe	220 to 240 volts (V) at 47 to 53 hz or 57 to 63 hertz (HZ) nominal (not available in all countries) 198 to 259 volts, extreme
POWER CONSUMPTION	
Operation/Running – 110V/220V	Simplex 530W; Duplex 360W
Standby Mode – 110V/220V	22W
Auto Off/Sleep Mode – 110V/220V	1.61W
Power Off Mode – 110V/220V	0.2W
Default Time to Sleep Mode	15 minutes
Time to First Print from Sleep Mode	15 seconds
Time to Ready from Off	42 seconds
OPERATING ENVIRONMENT	
Required Temperature Range – Fahrenheit (storage)	60 to 90° F Shipping: -40 to 104° F
Required Temperature Range – Fahrenheit (operating)	60 to 90° F
Required Temperature Range – Celsius (storage)	15 to 32° C Shipping: -40 to 40° C
Required Temperature Range – Celsius (operating)	15 to 32° C
Required Relative Humidity	8% to 80% RH
SOUND POWER LEVELS	
Sound Pressure Levels	Operating simplex b&w/col 51/52 dB(A) Operating duplex 53/54 dB(A) Quiet mode simplex 47/48 dB(A) Idle 14 dB(A)
Sound Power Levels	Operating simplex b&w/col 6.6/6.7 B(A) Operating duplex 6.7/6.8 B(A) Quiet mode simplex 6.2/6.2 B(A) Idle 3.1 B(A)

Xerox C410 Color Printer

DIMENSIONS AND WEIGHTS

Printer (Packaged)	Width: 19.5 in/495 mm Depth: 23.4 in/595 mm Height: 15.8 in/402 mm Weight: 52.5 lb/23.9 kg
Printer (Unpackaged)	Width: 17.9 in/445 mm Depth: 16.6 in/423 mm Height: 12.5 in/318 mm Weight: 45.3 lb/20.6 kg
550-Sheet Tray (requires the 550+100-Sheet Tray) (Packaged)	Width: 8.6 in/218 mm Depth: 20.0 in/508 mm Height: 18.8 in/478 mm Weight: 11.45 lb/5.2 kg
550-Sheet Tray (requires the 550+100-Sheet Tray) (Unpackaged)	Width: 16.7 in/424 mm Depth: 16.4 in/416 mm Height: 5.2 in/133 mm Weight: 8.6 lb/3.9 kg
550+100-Sheet Tray (Packaged)	Width: 8.6 in/218 mm Depth: 20.0 in/508 mm Height: 18.8 in/478 mm Weight: 11.45 lb/5.2 kg
550+100-Sheet Tray (Unpackaged)	Width: 16.7 in/424 mm Depth: 16.4 in/416 mm Height: 5.2 in/133 mm Weight: 9.3 lb/4.2 kg
Printer Stand (Packaged)	Width: 20.7 in/525 mm Depth: 22.2 in/565 mm Height: 9.2 in/235 mm Weight: 37.7 lb/17.1 kg
Printer Stand (Unpackaged)	Width: 18.2 in/463 mm Depth: 20 in/510 mm Height: 17.3 in/440 mm Weight: 32.7 lb/14.8 kg

INSTALLATION CONSIDERATIONS

Clear area around the device is necessary for access and ventilation. The below table shows the area needed on each side for correct installation.

Top	10 in/254 mm
Rear	4 in/101.6 mm
Left	3 in/76.2 mm
Right	3 in/76.2 mm
Front	3 in/76.2 mm

SYSTEM CERTIFICATION/REGULATORY COMPLIANCE

Certifications To view the latest list of certifications, go to xerox.com/OfficeCertifications

WHAT'S IN THE BOX

All items contained in the box	C410 Color Printer Power Cord Installation Guide Product Safety Sheet Quick Use Guide Software and Documentation CD Pre-installed Starter Capacity Print Cartridges: One of each (Cyan, Magenta, Yellow) 2,000 print capacity ³ ; Black cartridge: 2,400 print capacity ⁵
---------------------------------------	--

Xerox C410 Color Printer

SUPPLIES AND ACCESSORIES	NORTH AMERICA AND EUROPE*	ALL OTHER REGIONS
Genuine Xerox Black Standard Capacity Toner Cartridge, Xerox C410 Color Printer (2,400 Pages) ⁵	006R04677	006R04677
Genuine Xerox Cyan Standard Capacity Toner Cartridge, Xerox C410 Color Printer (2,000 Pages) ⁵	006R04678	006R04678
Genuine Xerox Magenta Standard Capacity Toner Cartridge, Xerox C410 Color Printer (2,000 Pages) ⁵	006R04679	006R04679
Genuine Xerox Yellow Standard Capacity Toner Cartridge, Xerox C410 Color Printer (2,000 Pages) ⁵	006R04680	006R04680
Genuine Xerox Black High Capacity Toner Cartridge, Xerox C410 Color Printer (10,500 Pages) ⁵	006R04685	006R04764
Genuine Xerox Cyan High Capacity Toner Cartridge, Xerox C410 Color Printer (7,000 Pages) ⁵	006R04686	006R04765
Genuine Xerox Magenta High Capacity Toner Cartridge, Xerox C410 Color Printer (7,000 Pages) ⁵	006R04687	006R04766
Genuine Xerox Yellow High Capacity Toner Cartridge, Xerox C410 Color Printer (7,000 Pages) ⁵	006R04688	006R04767
Genuine Xerox Waste Toner Bottle, Xerox C410 Color Printer (30,000 Pages)	008R13325	008R13325
Genuine Xerox Black Imaging Kit, Xerox C410 Color Printer (125,000 Pages) ⁶	013R00700	013R00700
Genuine Xerox Color Imaging Kit (CMYK), Xerox C410 Color Printer (125,000 Pages) ⁶	013R00701	013R00701
OPTIONAL ACCESSORIES		
550+100-Sheet Tray	097N02468	
550-Sheet Tray (requires the 550+100-Sheet Tray)	097N02465	
500+GB Hard Disk	097N02464	
Xerox Printer Stand	097S05244	
Wireless Network Adapter	097N02470	

* North America (NA): U.S., Canada

Europe (XE): U.K., France, Germany, Spain, Italy, Netherlands, Belgium, Norway, Sweden, Finland, Denmark, Iceland, Luxembourg, Austria, Switzerland, Portugal, Ireland Andorra, Azores, Corsica, Greenland, Iceland, Lichtenstein, Luxembourg, Madeira, San Marino

¹ Declared print speed in accordance with ISO/IEC 24734.

² Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis.

³ Requires Wireless Network Adapter

⁴ Requires 500+GB Hard Disk

⁵ Average standard pages. Declared yield in accordance with ISO/IEC 19798. Yield will vary based on image, area coverage and print mode.

⁶ Approximate pages. Declared yield will vary depending on job run length and media size/orientation and print mode. For more information, visit office.xerox.com/latest/SUPGL-01.PDF

Return spent imaging supplies through the Xerox® Green World Alliance® collection/reuse/recycling program. Visit xerox.com/About-Xerox/Recycling.

For more information, visit us at xerox.com/office.