

Switch SKY-SW28G-001

Wisenet SKY Switch



The Wisenet SKY PoE switches are industry standard highly reliable PoE switches designed to seamlessly integrate with the Wisenet SKY VMS. Gigabit switches are great for display stations that require higher bandwidth, if network topology requires cascading multiple switches, for locations where multiple bridges are deployed, or for flexible mounting options.



FRONT



BACK

Total Number of Ports	28
PoE Ports	24 PoE+
Uplink Ports	2 RJ-45 and 2 SFP
Power Supply	Built-in Power Supply
Voltage Range	AC100-240V
PoE Specifications	54 VDC 802.3af (max 15.4W), 802.3at (max 30W)
Maximum Power Budget	370W
Speed	10/100/1000 Mbps
Dimension (L x W x H)	440 x 200 x 44mm 17.3 x 7.9 x 1.7in
Switching Capacity	56 Gbps
MAC Address	8K MAC address table
Temperature Range	0-50° C (32-122°F)
Storage Temperature	-20-70° C (-4-158°F)
Rack Mountable	Rack or wall mounting (Brackets included)