



Poly CS540 CONV HS - RENEW (7E2J7AAR)



Overview

Hands-free productivity

The CS540 convertible DECT™ headset provides professional performance so you can get more done — even on the move. The noise-canceling mic reduces background noise interruptions, ensuring great audio quality and easing listener fatigue.

Give everyone more freedom to move

Everyone in the office could use more flexibility. Let them roam confidently up to 400 ft from the headset base. They'll be able to collaborate simply since teams can conference up to four headsets on a single base.

The choice is yours

There's more than one way to make a call — switch up styles to find your groove and introduce your ears to something new. The CS540 convertible design comes with three wearing options: over-the-ear, over-the-head, behind-the-head[1].

Features

It's just easy

Simplify desk phone management with headset audio controls and adding either the HL10 Handset Lifter or Electronic Hook Switch Cable (EHC) for remote call capabilities.^[2,3]

SoundGuard technology

SoundGuard acoustic limiting technology protects against Acoustic Shock by limiting sounds to below 118dBA ensuring listening comfort and protection against audio spikes.

Maximum protection

The CS540 headset includes DECT™ technology that provides better audio quality and eliminates interference from Wi-Fi networks while calls stay safe and secure.^[4]

Extended range and talk time

The adaptive power system optimizes for range and talk time by automatically downshifting to low power when the headset is close to the base — saving battery life and maintaining maximum density.

Superior audio quality

Your choice of narrowband audio to extend talk time or advanced wideband audio for high — definition voice quality. Enhanced Digital Signal Processing (DSP) provides more natural sound, delivering clear audio the way it's intended to be heard.

[2] HL10 Handset Lifter sold separately.

[3] Electronic Hook Switch Cable (EHC) sold separately.

[4] DECT is a trademark of ETSI.

Additional specifications

Acoustic protection technology	SoundGuard ^[1]
Battery life	Up to 7 hours (talk time)
Color	Black
Connection type	DECT™
Manufacturer Warranty	Poly standard one-year limited warranty
Nominal sound pressure level	118 dB SPL
UNSPSC code	52161514
Weight	21 g
Weight	0.04 lb
What's in the box	Office base; AC power adapter; Headband; Telephone interface cable (TIC); Headset with pre-installed battery, eartip and earloop; Kit with eartips and earloops
Wireless range	Up to 120 m
Wireless range (imperial)	Up to 350 ft

[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly APA-23 Electronic Hookswitch TAA	85Q50AA
Poly APA-24 Electronic Hookswitch TAA	85Q52AA
Poly APC-43 Electronic Hookswitch (Bagged) TAA	85Q56AA
Poly APC-43 Electronic Hookswitch TAA	85Q55AA
Poly APC-45 Electronic Hookswitch TAA	85Q57AA
Poly APD-80 Electronic Hookswitch TAA	85Q58AA
Poly APN-91 Electronic Hookswitch TAA	85Q59AA
Poly APP-51 Electronic Hookswitch TAA	85Q60AA
Poly APS-11 Electronic Hookswitch TAA	85Q78AA
Poly APT-31 Electronic Hookswitch TAA	85Q84AA
Poly APU-72 Electronic Hookswitch TAA	85Q95AA
Poly APU-75D Electronic Hookswitch TAA	85Q99AA
Poly APU-76 Electronic Hookswitch TAA	85R00AA
Poly APV-63 Electronic Hookswitch TAA	85R01AA
Poly APV-66 Electronic Hookswitch TAA	85R02AA
Poly CS500 Leatherette Ear Cushions (2 Pieces)	85R11AA
Poly CS540 Battery	85Q98AA
Poly CS540 Battery (Enhanced EU Safety)	784Q3AA
Poly CS540 Earloops and Earbuds	85Q18AA
Poly CS540 Leatherette Ear Cushions (2 Pieces)	85Q20AA
Poly CS540 Medium Eartips (25 Pieces)	85Q23AA
Poly CS540 Small Eartips (25 Pieces)	85Q25AA
Poly CS545-XD Battery Charger	85T22AA
Poly EHS 3.5mm to 3.5mm Cable	85R17AA
Poly HL10 Handset Lifter	784Q1AA
Poly HL10 Handset Lifter with Straight Plug TAA	784Q2AA
Poly RD-1 Electronic Hookswitch	85R71AA
Poly Savi Office Straight Plug Online Indicator	85R52AA
Poly Savi WH500/CS545 Battery and AC Power Supply Charging Cable	85R70AA
Poly Savi WH500/CS545 Battery and USB-A Charging Cable	85R72AA

Poly Savi WH500/CS545 USB-A Battery Charging Cable	85R74AA
Poly TR-11 Electronic Hookswitch	85R84AA

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Feb 13, 2024 5:36 AM UTC+0000