



Poly Savi 7210 Office DECT 1920-1930 MHz Headset TAA (7E2K1AA)

Overview

Move freely, get more done

Help office workers be more productive — it's easier than you think. The Savi 7200 office series of DECT™ wireless headsets for desk phones are crowd pleasers that let workers roam far. Compatible with 800+ desk phones, they're cost effective, too.

Hands-free productivity

Everyone in the office could use more flexibility. They can roam confidently 400 ft / 120 m from the headset base with up to 12 hours of talk time. And collaboration is simple, since teams can conference up to four headsets on a single base.

DECT™ Adaptive Power

Optimize range, save power, and maximize office space with the DECT™ adaptive power system. It automatically adjusts wireless signal strength based on distance from the headset base.

Easy integration

Savi 7200 wireless headsets offer instant integration with over 800 analog and IP desk phones from industry leading makers – including a wide range of phones that Poly offers.

Features

Roam farther

Give workers more flexibility and hands-free productivity with a roaming range of up to 120 m / 400 ft from the headset base.

12 hours talk time

Build more confidence into every call with up to 12 hours of talk time with each charge.

Training made easy

Collaboration is easier with conferencing of up to 4 headsets on one base.

Charge indicator

Provide the peace of mind that comes from knowing headsets are always fully charged with the headset docking charge indicator.

Keep conversations private

Help make every conversation clearer, with a flexible noise-canceling microphone boom that's easy to adjust for optimal placement on every call.

Desk phone compatibility

Take advantage of one-stop shopping, since these headsets are compatible with the wide range of phones that Poly offers.

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Audio	Noise cancellation (NC)
Battery life	Up to 12 hours (talk time)
Battery type	Rechargeable Li-ion polymer
Button user controls	Call answer/end; Mute; Volume +/-; Power on/off
Charge time	3 hours
Color	Black
Connection type	DECT™
Connects to	Desk phone
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear (monoaural)
Indicator light	On call
Management Software	Plantronics Hub (desktop and mobile versions)
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone type	Omnidirectional
Minimum dimensions (W x D x H)	6.1 x 6.53 x 2.63 in
Minimum dimensions (W x D x H)	155 x 166 x 67 mm
Package dimensions (W x D x H)	210 x 185 x 115 mm
Paired devices	Up to 4
Special features	Adjustable headband
UNSPSC code	52161514
UPC number	197192156285
Weight	104 g
Weight	0.23 lb
What's in the box	Wireless headset; Office base; AC power adapter; AC interchangeable plugs; Telephone cable; Safety guide; Warranty card; Quick start guide
Wireless range	Up to 120 m from base
Wireless range (imperial)	Up to 400 ft from base

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Sep 24, 2023 8:59 PM UTC+0000