



Poly Savi 7310-M Office DECT 1920-1930 MHz Single Ear Headset (7S439AA)



Overview

Ensure secure conversations

Keep conversations private. With up to 2x better density, this secure DECT™ wireless headset is an ideal choice for financial, medical, government, and contact centers or anywhere sensitive conversations happen.

DECT™ security

Savi 7300 headsets don't just meet security expectations, they exceed them with secure pairing, 128-bit authentication, and military-grade features, such as 256-bit AFS encryption. Conversations stay private and secure.

Keep conversations private

Make sure nearby conversations are not overheard. The noise-canceling microphone enhanced with Poly Acoustic Fence technology, that meets the Microsoft Teams Open Office specification, private conversations stay private[1].

Interference-free audio

With 2x better density than other DECT™ headsets, more people in shared spaces benefit from wireless headsets with clear, interference-free audio. IT can deploy more Savi 7300 Office Series compared to other DECT™ headsets without concern.

Features

DECT™ security standards

Designed to meet the highest-level DECT™ Security Step C enhanced with military-grade FIPS 140-2 listed features, such as 256-bit AES encryption.^[2]

Meet enterprise security needs

Ideal for use in financial, medical, and government environments, where Bluetooth® technology is typically banned.

Remote management

Stay in control with remote device management for settings, firmware, and security updates.

Roaming range

Give users more freedom to move with a line-of-sight wireless range of up to 580 ft/180 m.

Works with you

Lasts throughout the day with up to 13 hours of talk time. And a choice of wearing style accommodates all your users with monaural or stereo over-the-head (OTH) models.

Certified for Microsoft Teams

Full Microsoft Teams certification takes your Microsoft Teams experience to the next level with a button for instant access to the app and more. Plus, this headset meets Microsoft Teams Open Office premium microphone specification.^[3]

[1] Make sure nearby conversations are not overheard. The noise-canceling microphone enhanced with Poly Acoustic Fence technology, that meets the Microsoft Teams Open Office specification, private conversations stay private.

[2] DECT security standards can be found on <https://etsi.org>

[3] Microsoft Teams Open Office Premium Microphone certification: All headsets are tested to provide clear audio, but open office and other noisy environments pose a greater challenge. Headsets with this designation pick up the voice of the headset user but do not transmit the sound of their neighbors.

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Audio	Noise and echo reduction
Base controls	Desk phone configuration; Softphone selector; Microsoft Teams button
Base ringer	Incoming calls (when not wearing the headset)
Battery life	Up to 13 hours (talk time); Up to 52 hours (standby time)
Battery type	Rechargeable Li-ion polymer
Button user controls	Call answer/end; Mute; Volume +/-; Power on/off; Microsoft Teams
Certified collaboration software	Microsoft Teams
Charge time	2 hours
Color	Black
Connection type	DECT™
Connects to	Desk phone; PC
Datasheet photo 1	https://ssl-product-images.www8-hp.com/digmedialib/proding/lowres/c08404488.png
Datasheet photo 3	https://ssl-product-images.www8-hp.com/digmedialib/proding/lowres/c08401159.png
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear (monoaural)
Indicator light	On call
Management Software	Plantronics Hub (desktop); Plantronics Manager Pro suites (Asset Management and Adoption, Call Quality and Analytics, Health and Safety)
Manufacturer Warranty	Poly standard two-year limited warranty
Speaker size	14.2 mm
Special features	Adjustable headband
UNSPSC code	52161514
UPC number	197497168907
Voice alerts	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
Weight	120 g
Weight	0.26 lb
What's in the box	Wireless headset; Office base; Micro USB to Type-A cable; Micro USB to Type-C® cable; USB Type-C® to USB Type-A cable; Telephone cable; Quick start guide
Wireless range	Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial)	Up to 590 ft in open area; Up to 180 ft in typical office environment

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Services

Poly Services

★ : Recommended

Poly Support Services

3 year Partner Poly+ Savi Service	PSAVI362
3 year Poly+ Savi Service	PSAVI312

Audio

★ : Recommended

Audio Accessories

Poly APA-23 Electronic Hookswitch TAA	85Q50AA
Poly APA-24 Electronic Hookswitch TAA	85Q52AA
Poly APC-43 Electronic Hookswitch (Bagged) TAA	85Q56AA
Poly APC-43 Electronic Hookswitch TAA	85Q55AA
Poly APC-45 Electronic Hookswitch TAA	85Q57AA
Poly APC-82 Electronic Hookswitch TAA	8H981AA
Poly APD-80 Electronic Hookswitch TAA	85Q58AA
Poly APN-91 Electronic Hookswitch TAA	85Q59AA
Poly APP-51 Electronic Hookswitch TAA	85Q60AA
Poly APS-11 Electronic Hookswitch TAA	85Q78AA
Poly APT-31 Electronic Hookswitch TAA	85Q84AA
Poly APU-72 Electronic Hookswitch TAA	85Q95AA
Poly APU-75D Electronic Hookswitch TAA	85Q99AA
Poly APU-76 Electronic Hookswitch TAA	85R00AA
Poly APV-63 Electronic Hookswitch TAA	85R01AA
Poly APV-66 Electronic Hookswitch TAA	85R02AA
Poly EHS 3.5mm to 3.5mm Cable	85R17AA
Poly HL10 Extended Arm	8L554AA
Poly HL10 Handset Lifter	784Q1AA
Poly HL10 Handset Lifter TAA	8R713AA
Poly HL10 Handset Lifter with Straight Plug TAA	784Q2AA
Poly HL10 Lifter Arm +Ring Detector Accessory	8A7E3AA
Poly RD-1 Electronic Hookswitch	85R71AA
Poly Savi 7300 Battery with Removal Tool	784P8AA
Poly Savi 7300 Leatherette Ear Cushion (1 Piece)	783Q7AA
Poly Savi 7300 Leatherette Ear Cushions (2 Pieces)	783Q8AA
Poly Savi D400 UC DECT 1920-1930 MHz Dongle	85T33AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1920-1930 MHz Dongle	85T34AA
Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA	8L5A2AA
Poly Savi Office S2 Telephone Cable	85R55AA

Poly Savi Office Straight Plug Online Indicator	85R52AA
Poly Savi Office Telephone Interface Cable	85R57AA
Poly TR-11 Electronic Hookswitch	85R84AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA
Poly Voyager USB-A Charging Stand	783R6AA
Poly Voyager USB-C Charging Stand	783R7AA

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (us-en) – Oct 23, 2023 10:37 AM UTC+0000