



# Poly Voyager Focus 2 UC Headset +USB-A to USB-C Cable +Charging Stand (7S4L6AA)



## Overview

### The sweet sound of focus

Create a focus zone around you with the Voyager Focus 2, stereo Bluetooth® headset. Smartly engineered for audio perfection – all you will hear is your call. And the focus stays on you, right where it belongs.

### Your focus zone

Experience Poly acoustic excellence with the Voyager Focus 2 headset. Loud and distracting background is reduced with three levels of advanced digital hybrid ANC. You'll be ready to have the most critical conversations with confidence.

### Wear it like it's not there

Stay engaged during a full day of calls wearing a comfortable headband with cushioned sling and plush ear cushions. The Voyager Focus 2 is designed with you in mind – stay focused and productive all day.

### Crystal clear conversations

It's you – loud and clear. That's all callers hear. The discreet microphone boom is not only ultra-noise canceling but, with its Acoustic Fence technology, literally creates a virtual noise-free bubble in front of your mouth.

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard Digital <sup>[1,2]</sup>
<b>Audio</b>	Hybrid Active noise cancellation (ANC); Noise cancellation with Acoustic Fence technology; Smart sensor technology; Rotate microphone boom to mute
<b>Battery life</b>	Up to 25 hours (talk time, ANC and online indicator off); Up to 16 hours (talk time, ANC on and online indicator on, default setting); Up to 40 hours (music time, ANC off); Up to 24 hours (music time, ANC on)
<b>Battery type</b>	Rechargeable Li-ion
<b>Bluetooth version</b>	5.1
<b>Button user controls</b>	Call answer/end; Mute; Volume +/-; ANC: off, low, high; Power on/off; Bluetooth® pairing
<b>Charge time</b>	<2 hours
<b>Charging plug</b>	Micro USB to USB Type-A
<b>Color</b>	Black
<b>Compatibility</b>	Compatible with PCs via included BT700 Bluetooth® adapter or via USB cable; smartphone via Bluetooth®
<b>Compatible Operating Systems</b>	Windows 11; Windows 10; macOS
<b>Connection type</b>	USB Type-A; Bluetooth®
<b>Datasheet photo 1</b>	<a href="https://ssl-product-images.www8-hp.com/digmedialib/proding/lowres/c08559593.png">https://ssl-product-images.www8-hp.com/digmedialib/proding/lowres/c08559593.png</a>
<b>Datasheet photo 2</b>	<a href="https://ssl-product-images.www8-hp.com/digmedialib/proding/lowres/c08559532.png">https://ssl-product-images.www8-hp.com/digmedialib/proding/lowres/c08559532.png</a>
<b>Indicator light</b>	Connectivity; On call
<b>Management Software</b>	Poly Lens
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>Microphone bandwidth</b>	100 Hz to 6.8 kHz
<b>Microphone type</b>	2 digital MEMS; 2 analog ECM
<b>Minimum dimensions (W x D x H)</b>	155 x 66 x 183 mm
<b>Minimum dimensions (W x D x H)</b>	6.1 x 2.6 x 7.2 in
<b>Number of microphones</b>	4
<b>Paired devices</b>	Up to 8
<b>Sensitivity (speaker)</b>	N/A
<b>Speaker size</b>	32 mm
<b>Supported bluetooth profiles</b>	A2DP; AVRCP; HFP; HSP
<b>UNSPSC code</b>	43191638
<b>Voice alerts</b>	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low

<b>Voice assistant</b>	Siri; Google
<b>Weight</b>	175 g
<b>Weight</b>	0.38 lb
<b>What's in the box</b>	Micro USB charging cable; Quick start guide; Travel pouch; Charging stand; Wireless headset; BT700 Bluetooth® USB adapter; USB Type-A to USB Type-C® adapter
<b>Wireless range</b>	Up to 50 m
<b>Wireless range (imperial)</b>	Up to 164 ft

---

*[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).*

*[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.*

---

## Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (us-en) – Oct 30, 2023 10:57 AM UTC+0000