

Poly TC10 White Touch Controller (875J5AA)



Overview

Meet. Schedule. Join

The Poly TC10 touch control panel makes meetings more productive and allows users to easily schedule workspaces and conference rooms.

Easier room scheduling

Meeting spaces are a breeze to schedule with a Zoom-certified scheduling panel. Multi-color LED lights let you know the vacancy status before you approach the door. And the touch screen lets you schedule your next meeting space in seconds.

Clean and simple installation

Our versatile touch panel is sleek and professional. Mount it on walls or glass or place it on a table with its flexible stand. Adjust the angle for visibility. With a single cable for power and connectivity, it maintains a clean profile.

Complete call control

Instantly take charge of calls and enjoy seamless access to your favorite cloud video apps on your room's video system. Control of your video calls with ease and share content with a tap.

Features

Useful inside or outside any room

The incredible versatility enables it to be used outside the room for scheduling, or inside the room as a video and room controller.

Sleek design

The TC10 offers a uniquely tidy, professional-looking setup, thanks to its sleek design and convenient single cable for both power and connectivity.

Certified for Microsoft Teams

Deploy as a controller for Microsoft Teams on Android when paired to a Poly video system or install outside the room as a Microsoft Teams Panel for scheduling.

Large, clear display

The TC10 offers a clear, high-resolution 10" touch display that makes its intuitive controls easy to find and use.

Certified for Zoom

Schedule and conduct Zoom meetings with ease via seamless, Zoom-certified integration with the app.

Additional specifications

Aspect ratio	16:10
Brightness	300 nits
Cartons per layer	5
Cartons per pallet	35
Certified collaboration software	Zoom
Color	White
Contrast ratio	1000:1
Country of origin	Made in China
Display size (diagonal)	10.1"
Display size (diagonal)	25.7 cm (10.1")
Horizontal viewing angle	75°
Interoperability	Support for native 3rd party applications includes: Zoom Rooms, 8x8, BlueJeans, GoToRoom, Tencent, RingCentral, DialPad and others (when paired to a Poly Video OS system); Integration with Extron (environmental controls)
Management Software	Poly Lens; Device Management Service
Manufacturer Warranty	Poly standard one-year limited warranty
Minimum dimensions (W x D x H)	260 x 184 x 64 mm
Minimum dimensions (W x D x H)	10.25 x 7.25 x 2.5 in
Minimum order quantity	1
Native resolution	WXGA (1280 x 800)
Non-Operating Humidity Range	5 to 95%
Non-operating temperature - Celsius	-20 to 60 °C
Non-operating temperature - fahrenheit	-4 to 158 °F
Operating altitude	3,048 m
Operating altitude	10,000 ft
Operating humidity range	15 to 80%
Operating temperature range	32 to 104 °F
Operating temperature range	0 to 40 °C
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package dimensions (W x D x H)	190 x 210 x 55 mm
Package weight	300 g
Package weight	0.66 lb

Pallet (layers)	7
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	357 kg
Pallet weight	787.05 lb
Panel technology	IPS
Physical security	Standard Kensington lock slot
Ports	1 RJ-45
Power	Power over Ethernet (PoE), compatible with IEEE 802.3at class 0
Products per pallet	140
Products per pallet layer	20
Special features	Air Quality Sensor; Proximity sensor; Scheduler; Wall mountable; Standalone mode
UNSPSC code	45111902
UPC number	(ABT) 197497663556; (AC3) 197497663563
Vertical viewing angle	75°
Weight	2.79 lb
Weight	1.27 kg
What's in the box	Poly TC10; Wall mount kit; Table stand; Mounting hardware; RJ-45 cable; Quick start QR code; Warranty card; Poly Lens coaster

Services

Poly Services

★ : Recommended

Poly Support Services

3 Year Poly+ TC10	P37760312 ★
1 Year Partner Poly+ Onsite TC10	P37760158
1 Year Partner Poly+ TC10	P37760160
1 Year Poly Elite Onsite TC10	E37760114
1 Year Poly Elite TC10	E37760112
1 Year Poly+ Onsite TC10	P37760114
1 Year Poly+ TC10	P37760112
1 Year extension of 5yr HW Replacement TC10 with advanced part replacement Poly DaaS	D37760DS1
3 Year Partner Poly+ Onsite TC10	P37760358
3 Year Partner Poly+ TC10	P37760362
3 Year Poly Elite TC10	E37760312
3 Year Poly+ Onsite TC10	P37760314
5 Year Next Business Day HW Replacement TC10 Poly DaaS Service	D37760DS5
Service Reactivation Fee TC10 for product less than one year out of support coverage	R37760801
Service Reactivation Fee TC10 for product more than one year out of support coverage	R37760802
Upgrade embedded 1yr Poly+ to 1yr Poly Elite TC10	E37760912
Upgrade embedded 1yr Poly+ to 1yr Poly+ Onsite TC10	P37760102
Upgrade embedded 1yr Poly+ to 3yr Partner Poly+ Onsite TC10	P37760788
Upgrade embedded 1yr Poly+ to 3yr Partner Poly+ TC10	P37760351
Upgrade embedded 1yr Poly+ to 3yr Poly+ Onsite TC10	P37760309
Upgrade embedded 1yr Poly+ to 3yr Poly+ TC10	P37760103
Upgrade embedded 3yr Partner Poly+ to 3yr Partner Poly+ Onsite TC10	P37760555
Upgrade embedded 3yr Partner Poly+ to 3yr Poly+ Onsite TC10	P37760444
Upgrade embedded 3yr Partner Poly+ to 3yr Poly+ TC10	P37760333

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements

accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Mar 29, 2024 11:24 AM UTC+0000