



Poly Studio X50 All-In-One Video Bar No Radio GSA/TAA JITC (842W2AA)

Overview

Simple video conferencing

Poly Studio X50 video bars simplify and enhance your hybrid meeting experience in medium-sized rooms – no matter what video collaboration software you use. Experience board-room quality audio and video, all optimized into one sleek bar.



Drama-free setup

Get your medium-sized conference rooms up and running in moments. No PC is required, and cloud service platform support is built right in. It's easy to install, and ideal for rooms up to 10 participants.

Production-quality performance

Keep your eye on the action with intelligent camera framing and NoiseBlockAI technology – powered by machine learning. Get exquisite vocal pickup from our next gen mics. Share content over wired or wireless connections via dual monitors.

Features

Smart camera tech

Give everyone in hybrid meetings an equal seat at the virtual table using a choice of framing modes with Poly DirectorAI smart camera technology.

4K camera

No one looks their best with pixilated video. Enjoy richer, more life-like meeting experiences with 4K UltraHD video.

Noise blocking innovations

Outside noise and side conversations can quickly derail a hybrid meeting. Keep background noise in check with Poly NoiseBlockAI and Acoustic Fence technologies.

Beamforming microphone

Make communicating effortless for everyone on the call, with a next-generation beamforming microphone array that clearly picks up all voices in a room.

Native experience

Give everyone the confidence that comes from knowing they can connect to any cloud video service easily — with no PC needed.

Acoustic chamber

Enjoy legendary audio from Poly, with crisp, room-filling sound made possible by an innovative acoustic chamber design.

Additional specifications

Audio	Poly NoiseBlockAI technology; Poly Acoustic Fence technology
Audio standards	22 kHz with Polycom Siren 22 technology; 20 kHz with G.719 (M- Mode) and Polycom Siren 22 technology; 14 kHz with Polycom Siren 14 technology, G.722.1 Annex C; 7 kHz with G.722, G.722.1; 3.4 kHz with G.711, G.728, G.729A
Camera resolution	2160p, 4K UHD (3840 x 2160)
Camera type	Single-lens
Certified collaboration software	Zoom; Microsoft Teams; Google Meet
Content video resolution (input)	UHD (3840 x 2160); HD (1920 x 1080); WSXGA+ (1680 x 1050); UXGA (1600 x 1200); SXGA (1280 x 1024); WXGA (1280 x 768); HD (1280 x 720); XGA (1024 x 768); SVGA (800 x 600)
Content video resolution (output)	UHD (3840 x 2160); WUXGA (1920 x 1200); HD (1920 x 1080); WSXGA+ (1680 x 1050); SXGA+ (1400 x 1050); SXGA (1280 x 1024); HD (1280 x 720); XGA (1024 x 768)
Diagonal field of view (dFoV)	121°
Digital signage	Appspace; Raydiant
Horizontal field of view (hFoV)	110°
Interoperability	Zoom Certified; Microsoft Teams Certified; All cloud service providers through Poly Video App mode; USB Device mode; Support for native 3rd party applications including Zoom, Microsoft Teams, BlueJeans, Dialpad, GoToRoom, RingCentral and StarLeaf
Lens cover capabilities	Attachable
Management Software	Poly Lens
Manufacturer Warranty	Poly standard one-year limited warranty
Microphone pickup range (imperial)	Up to 25 ft
Microphone pickup range (metric)	Up to 7.62 m
Microphone type	Three MEMS microphones; Two second-order microphones
Minimum dimensions (W x D x H)	30 x 4 x 4 in
Minimum dimensions (W x D x H)	762 x 102 x 102 mm
Network capabilities	IPv4; IPv6; 1x 10/100/1G Ethernet; Auto-MDIX; H.323 and/or SIP up to 6 Mbps in Poly App video mode; Polycom Lost Packet Recovery (LPR) technology; Dynamic bandwidth allocation; Reconfigurable MTU size; Web proxy support: basic, digest, and NTLM
Non-Operating Humidity Range	5 to 95%
Non-operating temperature - Celsius	-40 to 70 °C
Non-operating temperature - fahrenheit	-40 to 158 °F
Operating altitude	4,877 m

Operating altitude	16,000 ft
Operating humidity range	15 to 80%
Operating temperature range	0 to 40 °C
Operating temperature range	32 to 104 °F
People video resolution	4K, 30 fps (TX and RX) from 2048 Kbps; 1080p, 60 fps from 1740 Kbps; 1080p, 30 fps from 1024 Kbps; 720p, 60 fps from 832 Kbps; 720p, 30 fps from 512 Kbps
Physical security	Standard Kensington lock slot
Ports	1 USB Type-C® 5Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate; 1 audio-in; 1 audio-out; 1 HDMI-in 1.4 (video and audio); 2 HDMI-out 1.4 (video); 1 line in (optional microphone)
Power	65 BTU h
Power supply type	External
SMART camera technology	Poly DirectorAI with speaker framing; People framing; Group framing; Presenter tracking; DirectorAI perimeter
Sensitivity (speaker)	86.1 dB
Speaker output power	1 x 20 W (RMS); 1 x 40 W (maximum)
Speaker type	Stereo speakers
Special features	Auto sensing power supply
UNSPSC code	45111902
UPC number	197497464894
Video frame rate	5–60 fps (up to 4K resolution at 15 fps in call)
Video standards	H.264 AVC; H.264 High Profile; H.265; H.239
Weight	5.6 lb
Weight	2540 g
What's in the box	Poly Studio X50; Ethernet cable; Wall mount kit; AC power adapter; Privacy cover; Cable bundle
Zoom capability	5x digital

Services

Poly Services

★ : Recommended

Poly Support Services

3 Year Poly+ Studio X50	P85970312 ★	
1 Year One time extension HW Replacement for Studio X50 with NBD advance replacement Poly DaaS	D85970DS1	
1 Year Partner Poly+ Onsite Studio X50	P85970158	
1 Year Partner Poly+ Studio X50	P85970160	
1 Year Poly Elite Onsite 4 hr Studio X50	E85970914	obsolete
1 Year Poly Elite Onsite Studio X50	E85970114	
1 Year Poly Elite Studio X50	E85970112	
1 Year Poly+ Onsite Studio X50	P85970114	
1 Year Poly+ Studio X50	P85970112	
3 Year Partner Poly+ Onsite Studio X50	P85970358	
3 Year Partner Poly+ Studio X50	P85970362	
3 Year Poly Elite Studio X50	E85970312	
3 Year Poly+ Onsite Studio X50	P85970314	
5 Year HW Replacement for Studio X50 with NBD advance replacement Poly DaaS	D85970DS5	
Service reactivation fee Studio X50 for product less than one year out of support coverage	R85970801	
Service reactivation fee Studio X50 for product one year or more out of support coverage	R85970802	
Upgrade from embedded 1y Poly+ to 1y Poly Elite Studio X50	E85970912	
Upgrade from embedded 1yr Poly+ to 1yr Poly+ Onsite Studio X50	P85970102	
Upgrade from embedded 1yr Poly+ to 3yr Partner Poly+ Onsite Studio X50	P85970788	
Upgrade from embedded 1yr Poly+ to 3yr Partner Poly+ Studio X50	P85970351	
Upgrade from embedded 1yr Poly+ to 3yr Poly+ Onsite Studio X50	P85970309	
Upgrade from embedded 1yr Poly+ to 3yr Poly+ Studio X50	P85970103	
Upgrade from embedded 3yr Partner Poly+ to 3yr Partner Poly+ Onsite Studio X50	P85970555	
Upgrade from embedded 3yr Partner Poly+ to 3yr Poly+ Onsite Studio X50	P85970444	
Upgrade from embedded 3yr Partner Poly+ to 3yr Poly+ Studio X50	P85970333	

Professional Services

Poly Remote Installation of One Studio X Video Solution	PROSTDIOXR2	
---	-------------	--

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 18, 2023 7:46 AM UTC+0000