

# Poly Voyager Focus 2-M Microsoft Teams Certified USB-A Headset TAA

## The sweet sound of focus

Create a focus zone around you with the Voyager Focus 2, stereo Bluetooth® headset. Smartly engineered for audio perfection – all you will hear is your call. And the focus stays on you, right where it belongs.



\*Product image may differ from actual product

### Your focus zone

Experience Poly acoustic excellence with the Voyager Focus 2 headset. Loud and distracting background is reduced with three levels of advanced digital hybrid ANC. You'll be ready to have the most critical conversations with confidence.

### Crystal clear conversations

It's you – loud and clear. That's all callers hear. The discreet microphone boom is not only ultra-noise canceling but, with its Acoustic Fence technology, literally creates a virtual noise-free bubble in front of your mouth.

### Wear it like it's not there

Stay engaged during a full day of calls wearing a comfortable headband with cushioned sling and plush ear cushions. The Voyager Focus 2 is designed with you in mind – stay focused and productive all day.

Datasheet

# Poly Voyager Focus 2-M Microsoft Teams Certified USB-A Headset TAA

## Specifications



### Compatible with

**Compatible operating systems:** Windows 11; Windows 10; macOS

### Connectivity and communications

**Wireless range:** Up to 50 m

**Wireless range (Imperial):** Up to 164 ft

**Paired devices:** Up to 8

**Bluetooth version:** 5.1

**Supported bluetooth profiles:** A2DP; AVRCP; HFP; HSP

**Connection type:** USB Type-A; Bluetooth®

**Headphone type:** On-ear (stereo)

**Voice assistant:** Siri; Google

**Voice alerts:** Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low

### User interface features

**Button user controls:** Call answer/end; Mute; Volume +/-; ANC: off, low, high; Power on/off; Bluetooth® pairing

### Audio

#### Audio features:

Hybrid Active noise cancellation (ANC)

Noise cancellation with Acoustic Fence technology

Smart sensor technology

Rotate microphone boom to mute

**Microphone type:** 2 digital MEMS; 2 analog ECM

**Microphone bandwidth:** 100 Hz to 6.8 kHz

**Speaker bandwidth:** 20 Hz to 20 kHz

**Speaker size:** 32 mm

**Charge time:** <2 hours

**Sensitivity (speaker):** N/A

### Battery

**Battery life:** Up to 25 hours (talk time, ANC and online indicator off); Up to 16 hours (talk time, ANC on and online indicator on, default setting); Up to 40 hours (music time, ANC off); Up to 24 hours (music time, ANC on)

**Battery description:** Rechargeable Li-Ion

**Battery capacity:** 560 mAh

### Certifications

**Certified collaboration software:** Microsoft Teams

### Environmental

**Acoustic protection technology:** SoundGuard Digital<sup>1,2</sup>

### Applications supported

**Management software:**

Poly Lens

### Minimum system requirements

USB Type-A port; Bluetooth®

### Weight and dimensions

**Product Primary Color:** Black

**Weight (Imperial):** 0.38 lb

**Weight (metric):** 175 g

**Product dimensions (Imperial):** 6.1 x 2.6 x 7.2 in

**Product Dimensions (metric):** 155 x 66 x 183 mm

**UPC number:** 197192156315

**Product number:** 7E2K4AA

### Warranty

Poly standard two-year limited warranty

### What is in the box

Micro USB charging cable

Quick start guide

Travel pouch

Wireless headset

BT700 Bluetooth® USB adapter

### Technical Specifications Footnotes

<sup>1</sup> SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the <sup>2</sup> Requires Poly Lens Desktop App to enable SoundGuard Digital features.