



SPECIFICATIONS

Model Name	GeForce® GT 1030 4GD4 LP OC
Graphics Processing Unit	NVIDIA® GeForce® GT 1030
Interface	PCI Express 3.0 x16 (uses x4)
Core Clocks	Boost: 1430 MHz
CUDA® CORES	384 Units
Memory Speed	2100 MHz
Memory	4GB DDR4
Memory Bus	64-bit
Output	DisplayPort x 1 (v1.4a) HDMI™ x 1 (Supports 4K@60Hz as specified in HDMI™ 2.0b)
HDCP Support	2.2
Power consumption	20 W
Recommended PSU	300 W
Card Dimension (mm)	150 x 69 x 19 mm
Weight (Card / Package)	131 g / 371 g
DirectX Version Support	12
OpenGL Version Support	4.5
Afterburner OC	Y
Maximum Displays	2
Accessories	Low Profile Bracket x 1

CONNECTIONS



1. HDMI™
2. DisplayPort

FEATURES



LOW PROFILE DESIGN

Low Profile design saves space to allow building a slim/small form factor system.



OC PERFORMANCE

MSI OC graphics cards are equipped with higher clock speeds out of the box for increased performance.



Military Class 4 Components

Using only the highest quality components means you get reliable and stable in-game performance.



Afterburner

Take full control with the most recognized and widely used graphics card overclocking software in the world.