



Poly Rove 20 Single Cell DECT 1920-1930 MHz B1 Base Station and 20 Phone Handset Kit (8F3E1AA)



Overview

We've got you covered

Keep the conversation going whenever, wherever in the office. Built for on-site employees the Poly Rove 20 wireless DECT™ IP phone solution delivers the freedom to move and the flexibility to scale as you grow.

Clarity meets function

Designed for busy professionals, Poly Rove 20 handsets emphasize usability, functionality, and style. Enjoy HD voice for lifelike conversations, customizable line keys, and effortless call parking.

You grow, we scale

You shouldn't have to worry about outgrowing your communication solution or feel held back by its options. Poly Rove 20 wireless DECT™ IP phone solution has the flexibility to scale with handsets, bases, and repeaters as you grow.

Features

Privacy is ensured

Conversations are safe and secure with DECT™ wireless security. And it doesn't stop there - maintain DECT™ encryption even when you add a base or repeater to your solution.

Extended battery life

Enable employees on the move to communicate more effectively, respond faster to requests and alerts, and be more productive with up to 35 hours of talk time (Eco-mode) and up to 300 hours of standby time.

Grab a Poly headset and go

Communicate hands-free with Poly wired headsets with the dedicated 3.5 mm handset connection. Perfect for users who feel more comfortable wearing a headset.^[1]

Easy-to-clean handsets

Ideal for healthcare environments, these handsets are specifically designed for easy cleaning with smooth surfaces and no gaps between buttons.

Pro-grade features

Single-cell DECT™ handset with 4-line keys and easy call park functionality. Push-to-talk for inter-handset communication. And with the 2" TFT color LCD with backlight users will see productivity soar.

Single Cell DECT™ Base

Entry-level DECT™ base station for small deployments needing up to 5,000 sq ft of coverage. Compatible with the Rove 20, Rove 30, Rove 40 handsets, and up to 3 Rove R8 Repeaters.

[1] Poly wired headset sold separately.

Additional specifications

Audio	Full-duplex handsfree speakerphone with acoustic echo cancellation and background noise suppression
Audio codecs	G.165, 168 echo cancellation
Battery life	Up to 35 hours (talk time) using Eco mode; Up to 300 hours (standby time)
Battery type	Rechargeable Li-ion
Cartons per layer	7
Cartons per pallet	63
Certifications and compliances	UL 62368-1
Certified collaboration software	Zoom
Color	Black
Country of origin	Made in China
DECT frequency	1880 to 1900 MHz
Datasheet photo 1	AHID/41f54a94e9f5cc9b9a81a198ef0f4a4ad192cafb
Datasheet photo 2	AHID/343b45863a7b93e5285195eabdc2cececb8e5719
Datasheet photo 3	AHID/802bf1d7242fdca2c74749262358bf6b584c964a
Display features	Adjustable font size selection (regular, medium, large)
Display size (diagonal)	5.1 cm (2")
Display size (diagonal)	2"
ECCN	5A991
Energy star certified	ENERGY STAR® certified
HTS code	8517140080
Headset and handset compatibility	Compliant with ADA Section 508 Subpart B 1194.23 (all)
Headset ports	1 3.5 mm headset jack
Management Software	Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management
Manufacturer Warranty	Poly standard one-year limited warranty
Minimum dimensions (W x D x H)	55.2 x 127 x 26.3 mm
Minimum dimensions (W x D x H)	2.2 x 5 x 1 in
Multiple order quantity	10
Native resolution	128 x 160
Network protocols, supported	Manual or dynamic host configuration protocol (DHCP) network setup; Time and date synchronization using SNTP
Onscreen controls	Three multi-colored mute indicators; Three sets of capacitive touch volume and mute buttons

Operating humidity range	5 to 95%
Operating temperature range	-10 to 55°C
Operating temperature range	14 to 131°F
Package dimensions (W x D x H)	230 x 173 x 60 mm
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Package weight	300 g
Pallet (layers)	9
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	357 kg
Pallet weight	787.05 lb
Panel technology	Color TFT LCD
Power	External universal AC adapter: 5V 1A DC
Products per pallet	630
Products per pallet layer	70
Security management	DECT™ security certified
Special features	Push-to-talk
Storage temperature range	-40 to 70°C
Storage temperature range	-40 to 158°F
Telephony and call handling features	4 line keys
UNSPSC code	43191511
UPC number	197497473247
VoIP features	Ten (10) service provider configuration profile assignments (ITSP Profile A – J)
Weight	1 lb
Weight	455 g
What's in the box	Safety information sheet; Handset; Quick start guide; AC power adapter; Charging cradle; Spare battery; Base station; Ethernet cable; Belt clip
Wireless range	Up to 50 m indoor
Wireless range (imperial)	Up to 165 ft indoor

Services

Poly Services

★ : Recommended

Poly Support Services

3 Year Poly+ Rove 20 and B1 Single Cell DECT Base Station	P88080312 ★
1 Year Partner Poly+ Rove 20 and B1 Single Cell DECT Base Station	P88080160
1 Year Poly+ Rove 20 and B1 Single Cell DECT Base Station	P88080112
3 Year Partner Poly+ Rove 20 and B1 Single Cell DECT Base Station	P88080362
5 Year Next Business Day HW Replacement Rove 20 and B1 Single Cell DECT Base Station Poly DaaS Svc	D88080DS5

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Jul 02, 2024 6:20 AM UTC+0000