



Poly Savi 7320 Office DECT 1920-1930 MHz TAA (7E2L1AA)



Overview

Ensure secure conversations

Keep conversations private. With up to 2x better density, this secure DECT™ wireless headset is an ideal choice for financial, medical, government, and contact centers or anywhere sensitive conversations happen.

DECT™ security

Savi 7300 headsets don't just meet security expectations, they exceed them with secure pairing, 128-bit authentication, and military-grade features, such as 256-bit AFS encryption. Conversations stay private and secure.

Keep conversations private

Make sure nearby conversations are not overheard. The noise-canceling microphone enhanced with Poly Acoustic Fence technology, that meets the Microsoft Teams Open Office specification, private conversations stay private[1].

Interference-free audio

With 2x better density than other DECT™ headsets, more people in shared spaces benefit from wireless headsets with clear, interference-free audio. IT can deploy more Savi 7300 Office Series compared to other DECT™ headsets without concern.

[1] Make sure nearby conversations are not overheard. The noise-canceling microphone enhanced with Poly Acoustic Fence technology, that meets the Microsoft Teams Open Office specification, private conversations stay private.

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Audio	Noise and echo reduction
Base controls	Desk phone configuration; Softphone selector
Base ringer	Incoming calls (when not wearing the headset)
Battery life	Up to 13 hours (talk time); Up to 52 hours (standby time)
Battery type	Rechargeable Li-ion polymer
Button user controls	Call answer/end; Mute; Volume +/-; Power on/off
Charge time	2 hours
Color	Black
Connection type	DECT™
Connects to	Desk phone; PC
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear (stereo)
Indicator light	On call
Management Software	Plantronics Hub (desktop); Plantronics Manager Pro suites (Asset Management and Adoption, Call Quality and Analytics, Health and Safety)
Manufacturer Warranty	Poly standard two-year limited warranty
Speaker size	14.2 mm
Special features	Adjustable headband
UNSPSC code	52161514
UPC number	197192156384
Voice alerts	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
Weight	160 g
Weight	0.35 lb
What's in the box	Wireless headset; Office base; Micro USB to Type-A cable; Micro USB to Type-C® cable; USB Type-C® to USB Type-A cable; Telephone cable; Quick start guide
Wireless range	Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial)	Up to 590 ft in open area; Up to 180 ft in typical office environment

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 03, 2023 5:10 AM UTC+0000