



# Poly Savi 7210 Office DECT 1920-1930 MHz Headset TAA (7E2K1AA)

## Overview

### Move freely, get more done

Help office workers be more productive — it's easier than you think. The Savi 7200 office series of DECT™ wireless headsets for desk phones are crowd pleasers that let workers roam far. Compatible with 800+ desk phones, they're cost effective, too.

### Hands-free productivity

Everyone in the office could use more flexibility. They can roam confidently 400 ft / 120 m from the headset base with up to 12 hours of talk time. And collaboration is simple, since teams can conference up to four headsets on a single base.

### DECT™ Adaptive Power

Optimize range, save power, and maximize office space with the DECT™ adaptive power system. It automatically adjusts wireless signal strength based on distance from the headset base.

### Easy integration

Savi 7200 wireless headsets offer instant integration with over 800 analog and IP desk phones from industry leading makers – including a wide range of phones that Poly offers.

# Features

## Roam farther

Give workers more flexibility and hands-free productivity with a roaming range of up to 120 m / 400 ft from the headset base.

## 12 hours talk time

Build more confidence into every call with up to 12 hours of talk time with each charge.

## Training made easy

Collaboration is easier with conferencing of up to 4 headsets on one base.

## Charge indicator

Provide the peace of mind that comes from knowing headsets are always fully charged with the headset docking charge indicator.

## Keep conversations private

Help make every conversation clearer, with a flexible noise-canceling microphone boom that's easy to adjust for optimal placement on every call.

## Desk phone compatibility

Take advantage of one-stop shopping, since these headsets are compatible with the wide range of phones that Poly offers.

---

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard Digital <sup>[1,2]</sup>
<b>Audio</b>	Noise cancellation (NC)
<b>Battery life</b>	Up to 12 hours (talk time)
<b>Battery type</b>	Rechargeable Li-ion polymer
<b>Button user controls</b>	Call answer/end; Mute; Volume +/-; Power on/off
<b>Charge time</b>	3 hours
<b>Color</b>	Black
<b>Connection type</b>	DECT™
<b>Connects to</b>	Desk phone
<b>Ear cushions</b>	Artificial leather (surface material)
<b>Headphone type</b>	On-ear (monoaural)
<b>Indicator light</b>	On call
<b>Management Software</b>	Plantronics Hub (desktop and mobile versions)
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>Microphone type</b>	Omnidirectional
<b>Minimum dimensions (W x D x H)</b>	6.1 x 6.53 x 2.63 in
<b>Minimum dimensions (W x D x H)</b>	155 x 166 x 67 mm
<b>Package dimensions (W x D x H)</b>	210 x 185 x 115 mm
<b>Paired devices</b>	Up to 4
<b>Special features</b>	Adjustable headband
<b>UNSPSC code</b>	52161514
<b>UPC number</b>	197192156285
<b>Weight</b>	104 g
<b>Weight</b>	0.23 lb
<b>What's in the box</b>	Wireless headset; Office base; AC power adapter; AC interchangeable plugs; Telephone cable; Safety guide; Warranty card; Quick start guide
<b>Wireless range</b>	Up to 120 m from base
<b>Wireless range (imperial)</b>	Up to 400 ft from base

---

*[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).*

*[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.*

---

# Services

## Poly Services

★ : Recommended

### Poly Support Services

3 year Poly+ Savi Service	<b>PSAVI312 ★</b>
3 year Partner Poly+ Savi Service	PSAVI362

## Hybrid Work Solutions

### Audio

★ : Recommended

#### Audio Accessories

Poly APA-23 Electronic Hookswitch TAA	85Q50AA
Poly APA-24 Electronic Hookswitch TAA	85Q52AA
Poly APC-43 Electronic Hookswitch (Bagged) TAA	85Q56AA
Poly APC-43 Electronic Hookswitch TAA	85Q55AA
Poly APC-45 Electronic Hookswitch TAA	85Q57AA
Poly APC-82 Electronic Hookswitch TAA	8H981AA
Poly APD-80 Electronic Hookswitch TAA	85Q58AA
Poly APN-91 Electronic Hookswitch TAA	85Q59AA
Poly APP-51 Electronic Hookswitch TAA	85Q60AA
Poly APS-11 Electronic Hookswitch TAA	85Q78AA
Poly APT-31 Electronic Hookswitch TAA	85Q84AA
Poly APU-72 Electronic Hookswitch TAA	85Q95AA
Poly APU-75D Electronic Hookswitch TAA	85Q99AA
Poly APU-76 Electronic Hookswitch TAA	85R00AA
Poly APV-63 Electronic Hookswitch TAA	85R01AA
Poly APV-66 Electronic Hookswitch TAA	85R02AA
Poly EHS 3.5mm to 3.5mm Cable	85R17AA
Poly HL10 Extended Arm	8L554AA
Poly HL10 Handset Lifter	784Q1AA
Poly HL10 Handset Lifter TAA	8R713AA
Poly HL10 Handset Lifter with Straight Plug TAA	784Q2AA
Poly HL10 Lifter Arm +Ring Detector Accessory	8A7E3AA
Poly RD-1 Electronic Hookswitch	85R71AA
Poly Savi 7200 Battery with Removal Tool	85R92AA
Poly Savi 7200 Leatherette Ear Cushion (1 Piece)	85Q53AA
Poly Savi 7200 USB-C Charging Cable	85R96AA
Poly Savi D400 UC DECT 1880-1890 MHz Dongle	8J8V9AA
Poly Savi D400 UC DECT 1880-1900 MHz Dongle	8J8V7AA
Poly Savi D400 UC DECT 1893-1906 MHz Dongle	8J8V6AA
Poly Savi D400 UC DECT 1910-1920 MHz Dongle	8J8V8AA

Poly Savi D400 UC Microsoft Teams Certified DECT 1880-1900 MHz Dongle	8J8W1AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1893-1906 MHz Dongle	8J8W0AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1910-1920 MHz Dongle	8J8W2AA
Poly Savi Hard Case	85R51AA
Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA	8L5A2AA
Poly Savi Office S2 Telephone Cable	85R55AA
Poly Savi Office Straight Plug Online Indicator	85R52AA
Poly Savi Office Telephone Interface Cable	85R57AA
Poly Savi Universal Power Supply -9V 500mA	85R63AA
Poly TR-11 Electronic Hookswitch	85R84AA

---

## Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 14, 2023 5:51 AM UTC+0000