



# Poly Voyager 4320-M Microsoft Teams Certified USB-A Headset +BT700 dongle TAA (7E2M1AA)



## Overview

### Cut wires. Cut Costs.

Free your workers from their desks with the entry-level Bluetooth® wireless headset. Meet the Voyager 4300 UC Series. It's everything your teams need to stay productive and connect to all their devices whether at home or in the office.

### Freedom to work

Move freely between all your workspaces with this portable headset. Roam with ease with up to 50 m / 164 ft of wireless range. Reduce background noise and control your conversations with Acoustic Fence technology.

### Round-the-clock efficiency

Boost your productivity with continuous comfort, up to 24 hours of talk time, and connectivity to multiple devices. Extend your talk time by using the desktop charge stand or by using the headset in the corded USB mode.[1,2]

---

[1] Connectivity includes: PC via included BT700 Bluetooth® adapter or via USB cable; smartphone via Bluetooth v5.2; desk phone with Voyager Office base, available as an accessory, sold separately.

[2] Desktop charge stand available with certain models or sold separately.

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard Digital <sup>[1,2]</sup>
<b>Audio</b>	Flexible noise cancellation; Noise cancellation with Acoustic Fence technology
<b>Battery life</b>	Up to 24 hours (talk time, online indicator off); Up to 18 hours (talk time, online indicator on); Up to 47 hours (music time); Up to 50 days (standby time)
<b>Battery type</b>	Rechargeable Li-ion
<b>Button user controls</b>	Call answer/end; Mute; Volume +/-; Power on/off; Pairing
<b>Cable length</b>	Up to 150 cm
<b>Cable length (imperial)</b>	Up to 5 ft
<b>Certified collaboration software</b>	Microsoft Teams; Zoom
<b>Charge time</b>	<1.6 hours
<b>Color</b>	Black
<b>Compatibility</b>	Compatible with PCs via included BT700 USB Type-C®/USB-A Bluetooth® adapter and smartphones via Bluetooth® - Voyager 4300 UC Series; Connects to a desk phone (via telephone interface cable), PCs (via USB-A or USB Type-C® cable) and mobile (via Bluetooth®) - Voyager 4300 UC series with Voyager Office base
<b>Compatible Operating Systems</b>	Windows; macOS
<b>Connection type</b>	Bluetooth® 5.2; USB Type-A
<b>Datasheet photo 1</b>	<a href="https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08400559.png">https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08400559.png</a>
<b>Datasheet photo 2</b>	<a href="https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08404231.png">https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08404231.png</a>
<b>Ear cushions</b>	Artificial leather (surface material)
<b>Headphone type</b>	On-ear (stereo)
<b>Indicator light</b>	On call; Connectivity
<b>Management Software</b>	Poly Lens
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>Microphone bandwidth</b>	100 Hz to 6.8 kHz
<b>Microphone type</b>	MEMS & ECM
<b>Minimum dimensions (W x D x H)</b>	155 x 67 x 166 mm
<b>Minimum dimensions (W x D x H)</b>	6.1 x 2.6 x 6.5 in
<b>Number of microphones</b>	2
<b>Package dimensions (W x D x H)</b>	8.27 x 7.28 x 2.17 in
<b>Package dimensions (W x D x H)</b>	210 x 188 x 55 mm
<b>Package weight</b>	0.32 kg

<b>Package weight</b>	0.71 lb
<b>Paired devices</b>	Up to 8
<b>Speaker size</b>	32 mm
<b>Special features</b>	Multipoint technology
<b>Supported bluetooth profiles</b>	A2DP; AVRCP; HFP; HSP
<b>UNSPSC code</b>	52161514
<b>UPC number</b>	197192156483
<b>Voice alerts</b>	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
<b>Voice assistant</b>	Siri; Google
<b>Weight</b>	0.35 lb
<b>Weight</b>	162 g
<b>What's in the box</b>	Quick start guide; Travel pouch; Wireless headset; USB Type-A charging cable; BT700 Bluetooth® USB adapter
<b>Wireless range</b>	Up to 50 m; Up to 91 m (with Voyager Office base)
<b>Wireless range (imperial)</b>	Up to 164 ft; Up to 300 ft (with Voyager Office base)

---

*[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).*

*[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.*

---

# Services

## Poly Services

★ : Recommended

### Poly Support Services

3 year Poly+ Voyager Service	PVOYAG312 ★
3 year Next Business Day Hardware Advance Replacement Voyager Poly DaaS Service	DVOYAGDS3
3 year Partner Poly+ Voyager Service	PVOYAG362

# Hybrid Work Solutions

## Audio

★ : Recommended

### Audio Accessories

Poly BT600 USB-A Bluetooth Adapter	85Q79AA
Poly BT600 USB-A Bluetooth Adapter (Bagged)	85Q81AA
Poly BT600 USB-C Bluetooth Adapter	85Q85AA
Poly BT600 USB-C Bluetooth Adapter (Bagged)	85Q87AA
Poly BT700 USB-A Bluetooth Adapter	786C4AA
Poly BT700 USB-C Bluetooth Adapter	786C5AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA
Poly Voyager 4300 Case	786D1AA
Poly Voyager 4300 Leatherette Ear Cushion (1 Piece)	783R9AA
Poly Voyager 4300 Leatherette Ear Cushions (2 Pieces)	783R5AA
Poly Voyager Microsoft Teams Certified Office Base	786D0AA
Poly Voyager Office Base	786C9AA
Poly Voyager USB-A Charging Stand	783R6AA
Poly Voyager USB-C Charging Stand	783R7AA

## Disclaimer — Copyright

Bluetooth® is a trademark owned by its proprietor and used by HP Inc. under license.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.