



Poly Studio Focus Room Kit for MS Teams: Studio P15 Personal Video Bar with GC8 (84H32AA)

Overview

Smarter rooms, better meetings



Elevate virtual meetings with AI-driven features for immersive collaboration. Enjoy high-resolution video, noise-blocking, smart camera framing, and a secure conferencing PC in Microsoft Teams Rooms. Experience the future with Poly Studio Room Kits [1].

A better way to meet and share

Poly Studio Room kits for Microsoft Teams Rooms give you distraction-free meetings with innovative Poly camera tech. From focus to large conference rooms, stay productive with technology that empowers the whole team, wherever they work.

Peace of mind you can call on

Our Poly + device support team is available 24/7, across the world. This extensive global network of support professionals help you confidently plan and successfully deploy Microsoft Teams Rooms.

Engineered for your enterprise

It's easy to make every Poly Studio Room a Microsoft Teams Room. Certified and purpose built, this cutting-edge meeting solution fits perfectly into office workflows, offers a consistent user experience and is simple for IT to setup.

Features

Smart + intuitive meetings

Make sure everyone is seen clearly with smart camera technology. Its fast and accurate auto-framing delivers an unrivaled video experience.

Up close and professional

Feel like you're face-to-face on both sides of the call. The 4K high-resolution camera sensor captures the entire room with life-like video and everyone in it with total clarity.

Take control with a touch

Jump in and out of meetings with ease. The user-friendly Poly GC8 touch controller lets you start, stop, and control meetings all at your fingertips.

Be free to focus

Let clearer audio do the talking with Poly NoiseBlockAI and Acoustic Fence technologies. These noise-eliminating, smart technologies blocks distractions and prevents noise from interrupting the flow of your team's discussions.

Security that means business

The powerful and secure conferencing PC is protected from malicious attacks at the BIOS level so you can deploy your solution with total confidence.^[1]

Microsoft Teams certified

The Microsoft Teams Devices Certification Program ensures all devices meet the performance standards and quality metrics across the entire user experience — audio, video, and interface.

[1] HP Mini Conferencing PC sold separately.

Additional specifications

Audio	Full duplex audio; Acoustic echo cancellation; Background noise suppression; Poly NoiseBlockAI technology; Poly Acoustic Fence technology
Audio standards	UAC Plug and Play compatible
Cable length	130 cm
Cable length (imperial)	51.18 in
Camera features	Manual pan, tilt and zoom control
Camera resolution	2160p, 4K UHD (3840 x 2160); 1080p, FHD (1920 x 1080); 720p, HD (1280 x 720)
Camera type	Single-lens
Certified collaboration software	Microsoft Teams
Color	Sand
Datasheet photo 1	AHID/f3ac7e8f47400ca5944e333c7f969c4b258450b1
Diagonal field of view (dFoV)	90°
Lens cover capabilities	Integrated
Management Software	Poly Lens
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone type	Three-microphone element beamforming array
Minimum dimensions (W x D x H)	425 x 70 x 78 mm (with monitor clamp); 425 x 65 x 78 mm (without monitor clamp)
Minimum dimensions (W x D x H)	17 x 3 x3 in (with monitor clamp); 17 x 2.5 x 3 in (without monitor clamp)
Non-Operating Humidity Range	5 to 95%
Operating altitude	3,000 m
Operating altitude	10,000 ft
Operating humidity range	15 to 80%
Operating temperature range	0 to 40 °C
Operating temperature range	32 to 104 °F
Package dimensions (W x D x H)	18.67 x 7.36 x 3.7 in
Package dimensions (W x D x H)	47.42 x 18.69 x 9.39 cm
Physical security	Standard Kensington lock slot
Power	12V/3A
Power adapter port	1 x 4.5 mm
Power supply type	External
Sensitivity (speaker)	80 dB
Speaker type	Single speaker

Special features	Integrated privacy shutter; Adjustable monitor clamp; Tripod ready; Status LED indicates calling and mute state
UNSPSC code	86141702
UPC number	197497525229
Video frame rate	30 fps
Video standards	UVC Plug and Play compatible
Weight	1 lb
Weight	0.682 kg
What's in the box	Power cable; Poly Studio P15; Poly GC8 controller; USB Type-A to USB Type-C® cable
Zoom capability	4x

Poly Services

★ : Recommended

Poly Support Services

1 Year Elite Poly Focus Room Kit includes P15 video bar GC8 touch controller	E87700112
1 Year Partner Poly+ Focus Room Kit incl P15 video bar GC8 touch controller	P87700160
1 Year Partner Poly+ Onsite Focus Room Kit incl P15 video bar GC8 touch controller	P87700158
1 Year Poly Elite Onsite Focus Room Kit Includes P15 video bar GC8 touch controller	E87700114
1 Year Poly+ Focus Room Kit incl P15 video bar GC8 touch controller	P87700112
1 Year Poly+ Onsite Focus Room Kit incl P15 video bar GC8 touch controller	P87700114

Video

★ : Recommended

Video Accessories

Poly Active Optical USB 3.1 Cable (10M)	875H1AA
Poly Active Optical USB 3.1 Cable (25M)	875H3AA
Poly Active Optical USB 3.1 Cable (40M)	875H4AA
Poly GC8 Studio X30 Power Supply without Power Cord	874R5AA
Poly GC8 Touch Controller	875J6AA
Poly GC8 Touch Controller GSA/TAA	875J8AA
Poly GC8 USB CAT5e Extender Kit (ABA)	9R1Y8AA
Poly Studio Room Kit for Microsoft Teams BYOD Pack CAT5e Extender USB Switch Hub3+ (ABA)	9C9U6AA
Poly Video IEC Power Cord	874T5AA

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.