



SPECIFICATIONS

Number of Fans	2
Fan Dimensions	120 x 120 x 25mm / 4.7 x 4.7 x 0.98 inches
Fan Power Consumption	3W(Max:4.8W)
Fan Rated Current	0.25A(Max:0.4A)
Fan Life Expectancy	50,000 hrs@40°C
Fan Bearing	Fluid Dynamic Bearing (FDB)
Fan Air Flow	25.5~75.04 CFM
Fan Lighting	ARGB
Water Cooling Tube Material	Black Rubber
PWM Mode	YES
Fan Cable Length (5V ARGB / PWM cable)	500 mm
Radiator Material	Aluminum
Radiator Dimensions	277 x 119.2 x 27mm / 10.91 x 4.69 x 1.06 inches
Block Dimensions	41±0.2*47.6±0.2mm
Pump Life Expectancy	200,000 hours in typical use
Fan Connector	4-pin
Pump Noise Level	20 dBA (avg.)
RGB Connector	3-pin + Socket
Pump Speed	3000 RPM ± 10%
Pump Power Consumption	3W (Max: 6W)
Pump Rated Current	0.25A (Max: 0.5A)
Pump Connector	4-pin
Intel Socket	LGA 1150/1151/1155/1156/1200/1700
AMD Socket	AM5/AM4
Accessories	1 x 1 to 2 Fan PWM cable 1 x Molex 4-Pin to 4-Pin fan cable 1 x Thermal paste
Cold Plate Material	Copper
Radiator Size	240 mm