

Poly Voyager 4320-M +USB-A to USB-C Cable +BT700 dongle

Cut wires. Cut Costs.

Free your workers from their desks with the entry-level Bluetooth® wireless headset. Meet the Voyager 4300 UC Series. It's everything your teams need to stay productive and connect to all their devices whether at home or in the office.

Freedom to work

Move freely between all your workspaces with this portable headset. Roam with ease with up to 50 m / 164 ft of wireless range. Reduce background noise and control your conversations with Acoustic Fence technology.

Round-the-clock efficiency

Boost your productivity with continuous comfort, up to 24 hours of talk time, and connectivity to multiple devices. Extend your talk time by using the desktop charge stand or by using the headset in the corded USB mode.^{1,2}

Poly Voyager 4320-M +USB-A to USB-C Cable +BT700 dongle

Specifications

Compatible with

Compatible operating systems: Windows; macOS

Connectivity and communications

Wireless range: Up to 50 m; Up to 91 m (with Voyager Office base)

Wireless range (Imperial): Up to 164 ft; Up to 300 ft (with Voyager Office base)

Paired devices: Up to 8

Supported bluetooth profiles: A2DP; AVRCP; HFP; HSP

Connection type: USB Type-A; Bluetooth®

Ear cushions: Artificial leather (surface material)

Headphone type: On-ear (stereo)

Voice assistant: Siri; Google

Voice alerts: Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low

User interface features

Button user controls: Call answer/end; Mute; Volume +/-; Power on/off; Pairing

Audio

Audio features:

Flexible noise cancellation

Noise cancellation with Acoustic Fence technology

Microphone type: MEMS & ECM

Microphone bandwidth: 100 Hz to 6.8 kHz

Speaker bandwidth: 20 Hz to 20 kHz

Speaker size: 32 mm

Charge time: <1.6 hours

Battery

Battery life: Up to 24 hours (talk time, online indicator off); Up to 18 hours (talk time, online indicator on); Up to 47 hours (music time); Up to 50 days (standby time)

Battery description: Rechargeable Li-Ion

Battery capacity: 350 mAh

Certifications

Certified collaboration software: Microsoft Teams; Zoom

Special features: Multipoint technology

Environmental

Acoustic protection technology: SoundGuard Digital^{1,2}

Applications supported

Management software:

Poly Lens

Minimum system requirements

USB Type-A port; Bluetooth®

Weight and dimensions

Product Primary Color: Black

Cable length (Imperial): Up to 5 ft

Cable length (metric): Up to 150 cm

Product number: 7Y211AA

Warranty

Poly standard two-year limited warranty

What is in the box

Quick start guide

Travel pouch

Wireless headset

USB Type-A charging cable

BT700 Bluetooth® USB adapter

USB Type-A to USB Type-C® adapter

Key Selling Points Footnotes

¹ Connectivity includes: PC via included BT700 Bluetooth® adapter or via USB cable; smartphone via Bluetooth v5.2; desk phone with Voyager Office base, available as an accessory, sold separately. ² Desktop charge stand available with certain models or sold separately.

Technical Specifications Footnotes

¹ SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the ² Requires Poly Lens Desktop App to enable SoundGuard Digital features.