



Poly Blackwire C3225 Stereo USB-C Headset TAA (8M3X7AA)

Overview

Freedom to work your way

The Blackwire 3200 Series provides a quality audio experience in a headset that's built for enterprise needs. With a sleek design and flexible microphone boom for a customizable fit, what's not to love?

Poly signature audio quality

Experience the high-quality audio you expect from Poly with a headset that offers PC wideband, a noise-canceling mic, and hi-fi stereo sound options. Dynamic EQ optimizes call quality and automatically adjusts the settings for listening to multimedia.

Long-lasting comfort and portability

Relax while you talk knowing your headset is secure- lightweight metal headband offers durability plus a custom fit. Leatherette ear cushions fold flat for easy portability.

Advanced connectivity

Ideal for managing calls on your PC, mobile phone, or tablet combined with the comfort and durability of a corded headset for greater flexibility.

Features

Enhanced call quality

Dynamic EQ optimizes the quality of your voice on calls, and automatically adjusts the EQ settings when you want high-quality sound for listening to music or for multimedia playback.

Connectivity options

Select the right option for your device: USB-A or USB Type-C® for PC and 3.5 mm for mobile connectivity with select models.

Wearing style

Hi-fi stereo wearing style for those who want a richer, more immersive experience.

Comfort and design

A lightweight metal headband offers durability and a comfortable custom fit.

Simple call management

Use the intuitive inline controls to answer/end calls, control volume, and mute to simplify call management. Conveniently placed indicator lights provide helpful but unobtrusive user call, mute, and volume status.

Optimized for communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.^[1]

[1] Visit <https://www.poly.com/us/en/products/headsets/blackwire/blackwire-3200> for more detail.

Additional specifications

Acoustic protection technology	SoundGuard ^[1]
Audio	Dynamic EQ optimized; Digital signal processing (DSP); Noise cancellation (NC)
Boom mic length (ft)	0.43 ft
Boom mic length (mm)	130 mm
Boom mic rotation	270°
Button user controls	Call answer/ignore/end/hold; Redial; Mute; Volume +/-
Cable length	129.5 cm (inline module to headset); 90 cm (USB to inline module); 227 cm (total USB to headset)
Cable length (imperial)	4.25 ft (inline module to headset); 2.95 ft (USB to inline module); 7.45 ft (total USB to headset)
Certified collaboration software	Skype for Business; Cisco Jabber; Avaya
Color	Black
Compatibility	Compatible with PCs via USB/USB Type-C®, connects to mobile devices and tablets via 3.5 mm and devices that support USB Type-C®
Compatible Operating Systems	Windows 11; Windows 10; macOS
Connection type	Wired USB Type-C® ; 3.5 mm audio
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear (stereo)
Impedance	32 ohms
Management Software	HP Headset Control Center
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone bandwidth	100 Hz to 10 kHz
Microphone type	Omnidirectional
Minimum System Requirements	USB Type-C® port; 3.5 mm audio
Minimum dimensions (W x D x H)	6.1 x 1.25 x 7.1 in
Minimum dimensions (W x D x H)	155 x 32 x 178 mm
Package dimensions (W x D x H)	185 x 56 x 207 mm
Package dimensions (W x D x H)	7.28 x 2.2 x 8.14 in
Package weight	250 g
Package weight	0.55 lb
Sensitivity (microphone)	-38 dBV/Pa
Sensitivity (speaker)	90 dB
Signal-to-noise ratio	>118 dB
Speaker size	28 mm

Special features	Adjustable headband; Voice alerts
UNSPSC code	43191638
UPC number	197497914979
Weight	0.19 lb (with cable); 0.14 lb (without cable)
Weight	87 g (with cable); 64 g (without cable)
What's in the box	Headset; USB Type-C® cable

[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.

Services

Poly Services

★ : Recommended

Poly Support Services

3 year Poly+ Blackwire Service	PBLKWIRE312 ★
3 year Next Business Day Hardware Advance Replacement Blackwire Poly DaaS Service	DBLKWIREDS3
3 year Partner Poly+ Blackwire Service	PBLKWIRE362

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly Blackwire 3200 Leatherette Ear Cushions (2 Pieces)	85S24AA
Poly Blackwire 3200 USB-A Inline Controls	85R03AA
Poly Blackwire 3200 USB-C Inline Controls	85R04AA
Poly Blackwire 3300 Case	85R06AA
Poly Blackwire 3310/3320 Foam Ear Cushions (2 Pieces)	85S23AA
Poly Blackwire 3315/3325 Leatherette Ear Cushions (2 Pieces)	85S22AA
Poly Blackwire 5000 Leatherette Ear Cushions (2 Pieces)	85S19AA
Poly Blackwire 5200 USB-A Inline Controls	85Q62AA
Poly Blackwire 5200 USB-C Inline Controls	85Q64AA
Poly Blackwire 5200 Y Training Cable	85S08AA
Poly Blackwire 7225 Case	85Q69AA
Poly Blackwire 8225 Leatherette Ear Cushions (2 Pieces)	783Q9AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 18, 2023 9:52 AM UTC+0000