

36V Extended Battery Module (EBM) for SmartOnline UPS Systems, 2U Rack/Tower

MODEL NUMBER: BP36RT



Provides extended runtime for compatible UPS systems in education, healthcare, military, government and other IT applications in small or mid-size networks.

Features

Backup Battery Module Gives Your Compatible UPS System Extended Runtime

The valve-regulated lead-acid (VRLA) BP36RT offers extended battery runtime when used in conjunction with SU750RTXLCD2U, SU750RTXLCD2UN, SU1000RTXLCD2U and SU1000RTXLCD2UN SmartOnline® UPS systems. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

Versatile Installation Options

You can mount the BP36RT in 2U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or an optional 2-post rail kit (RK2PC, sold separately). You can also adapt it for tower installation using the UPS system's support stands.

Highlights

- Connects to select expandable Eaton series SmartOnline UPS systems to add critical runtime
- Includes heavy-gauge battery cabling with high-current 36V DC connectors
- Daisy-chain connector supports additional battery packs for even longer runtime

System Requirements

Compatible only with 2023 redesign SU750RTXLCD2U, SU750RTXLCD2UN, SU1000RTXLCD2U and SU1000RTXLCD2UN UPS systems

Package Includes

- 36V Extended Battery Module
- External battery cable
- Rack-mounting hardware
- Quick start guide

Specifications

OVERVIEW	
UPC Code	037332279705
INPUT	
Input Phase	Single-Phase
Input Cord Details	15.7 in. connector cord
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
DC System Voltage (VDC)	36



Powering Business Worldwide

TRIPP LITE
SERIES

Replacement Battery Cartridge	 744-A3959
Battery Replacement Description	Hot-swappable, user replaceable batteries. EBM requires 2 Replacement Battery Cartridges.
UPS Connection	UPS specific DC connector
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	2U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; Tower
Installation Form Factors Supported with Optional Accessories	2 post rackmount (RK2PC)
Shipping Dimensions (hwd / in.)	9.40 x 22.80 x 21.70
Shipping Weight (kg)	27.40
Unit Dimensions (hwd / in.)	3.410 x 17.330 x 17.720
Unit Weight (lbs.)	48.1
Unit Weight (kg)	21.82
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-96% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Extended Service Plans	ADVANCED DEPOT EXCHANGE Service Part Number: TL9SW5Y-3000BCExpedited parts coverage for 5 yearsParts, electronics and batteries coverageNext business day shippingTechnical support 5-YEAR ON-SITE PLAN (US ONLY) Service Part Number: TLWEBN75XX-7000BCOnsite parts and labor coverage for 5 yearsParts, electronics and batteries coverage24x7 onsite labor coverage, next-day responseNext-day shippingTechnical support

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.