

ThinkPad T14s Gen 4 (AMD)

Designed for business travelers, this laptop powered by up to AMD Ryzen 7 pro processor lets users debug processes and manage projects effortlessly. AMD Radeon 740M or 780M graphics offer high performance, allowing content creators to work with high-resolution images, videos, and 3D content more smoothly and efficiently. Moreover, with up to 32GB LPDDR5 memory and up to 2TB SSD storage, this laptop easily accommodates large software databases, multimedia files, and work documents.



Lenovo devices that are a class apart

The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

Experience superior audio quality with 2W dual Dolby Audio stereo speakers, perfect for conference calls and multimedia presentations. The optional FHD 1080p camera with privacy shutter ensures crisp video quality and security for professionals on the go.

Security features include BIOS security and discrete TPM 2.0 chipset that ensures robust protection for sensitive data, crucial for content creators handling proprietary content.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center
 Lenovo pays for all shipping between the customer and service facility
 Avoid unplanned operational expense with a simple annual fee

Accessories

Thinkpad Essential 16" Backpack (Eco)

Two internal compartments (one for notebooks up to 16"), two front zipper pockets, and one side mesh water bottle sleeve that ensure you'll never run out of space.

A padded top handle. And a rear luggage strap. Every feature is crafted for convenience and comfort.

Elegant black nylon exterior, grey interior lining, and a splash of red accents.



PN: 4X41C12468

Lenovo Essential USB Mouse

Convenient and easy plug-and-play connection to PCs via a USB cable

Ergonomic full-size design provides a comfortable grip for all day comfort

Ambidextrous design, high-resolution 1600 DPI optical sensor experience smooth movement



PN: 4Y50R20863

ThinkPad T14s Gen 4 (AMD)

Performance

Processor AMD Ryzen 5/7
Operating System Windows 11 Pro Windows 11 Home Windows 11 Home Single Language Windows 11 DG Windows 10 Pro 64 Linux Ubuntu Linux
Graphics AMD Radeon 740M Graphics (integrated) AMD Radeon 780M Graphics (integrated)
Memory 16GB LPDDR5-6400, soldered 32GB LPDDR5-6400, soldered
Storage ¹ Up to 1x 2TB M.2 2280 PCIe NVMe SSD
¹ The storage capacity supported is based on the test results with current Lenovo storage offerings.
Audio High Definition (HD) Audio Stereo speakers, 2W x2, Dolby Audio Dual-microphone array, 360° far-field, Dolby Voice*
Camera FHD 1080p, with privacy shutter 5.0MP + IR discrete, with privacy shutter
Battery ² 57Wh (up to 15.67 hr) battery, Rapid Charge
² Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.
Power Adapter 45W USB-C adapter, PD 3.0 65W USB-C adapter, PD 3.0 65W USB-C slim adapter, PD 3.0

Design

Display ³ 14" WUXGA (1920x1200) IPS Anti-glare 16:10 - 300nits, 45% NTSC - 300nits, 45% NTSC, touch - 400nits, 100% sRGB, low power, Eyesafe - 500nits, 100% sRGB, touch, ThinkPad Privacy Guard
14" 2.2K (2240x1400) IPS Anti-glare 16:10 - 300nits, 100% sRGB, TÜV Low Blue Light Method 2
14" 2.8K (2880x1800) OLED AGARAS 16:10 - 400nits, 100% DCI-P3, DisplayHDR True Black 500, Dolby Vision, Eyesafe
³ IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.
Keyboard 6-row, spill-resistant, backlight
Touchpad TrackPoint and glass-like Mylar surface touchpad 61 x 115 mm (2.40 x 4.53 inches)
Dimensions ⁴ 317.5 x 226.9 x 16.9 mm (12.5 x 8.93 x 0.67 inches)
⁴ The system dimensions may vary depending on configurations.
Weight ⁵ Starting at 1.26 kg (2.77 lbs)
⁵ The system weight is approximate and may vary depending on configurations
Color Deep black Storm grey
Case material Carbon fiber hybrid or aluminium (top) Aluminium (bottom)

Connectivity

WLAN + Bluetooth ^{6 7} 802.11ax (Wi-Fi 6E), Bluetooth 5.1
⁶ Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.
⁷ Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.
WWAN 4G LTE CAT4 4G LTE CAT16 5G Sub-6 GHz with embedded eSIM
NFC Near Field Communication*
Ports 1x USB 3.2 Gen 1 1x USB 3.2 Gen 1 (Always On) 2x USB4 40Gbps (data, PD 3.0, DP 1.4a) 1x HDMI 2.1, up to 4K/60Hz 1x Headphone / microphone combo jack (3.5mm) 1x Smart card reader* 1x Nano-SIM card slot (WWAN support models)*

Docking Docking support via USB-C

Security & Privacy

Discrete TPM 2.0 and Microsoft Pluton TPM 2.0 Kensington Nano Security Slot Smart card reader* Touch style MOC fingerprint reader* Camera privacy shutter* IR camera for Windows Hello* Privacy Guard with Privacy Alert* Glance by Mirametrix Ultrasonic Human Presence Detection*

Manageability

DASH*

Certifications

Green Certifications ^{8 9} ENERGY STAR 8.0* EPEAT Gold Registered* ErP Lot 6/26 TCO Certified 9.0 RoHS compliant
⁸ The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.
⁹ EPEAT is registered where applicable, please see https://www.epeat.net for registration status by country
Other Certifications Eyesafe Certified* TÜV Rheinland Low Blue Light Method 2* MIL-STD-810H