

# ThinkBook 14 G6 ABP

Whether it's a creative, a business executive, or a digital nomad, this laptop is tailored to cater to their unique needs while they are working from a cafe or co-working space. Equipped with up to AMD Ryzen 7 processor, it ensures seamless performance while juggling multiple apps, running data analysis, and managing complex projects. With the 14" display with optional 2.2k resolution, combined with AMD Radeon graphics, colors pop and details shine while designing graphics or editing videos.



The integrated fingerprint reader and an optional IR camera shutter ensure the data stays protected. Work confidently in public spaces without compromising on privacy. Wi-Fi 6E keeps professionals connected wherever they go, ensuring seamless video conferences and quick file transfers.

Business professionals can immerse themselves in crystal-clear audio during virtual meetings or when unwinding with their favorite music. Its exceptional sound quality provided by Dolby Audio ensures they never miss a beat.

Optional ENERGY STAR 8.0 and optional EPEAT Gold certifications make it an energy-efficient device.

## Lenovo devices that are a class apart

ThinkBook combines the style and user experience of consumer devices with the security and business-class support of ThinkPad.

## Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center  
 Lenovo pays for all shipping between the customer and service facility  
 Avoid unplanned operational expense with a simple annual fee

## Accessories

### Lenovo 15.6" Laptop Casual Backpack

Extra cushioning and padding for maximum comfort  
 Waterproof fabric to keep your gadgets dry and safe  
 Conveniently placed compartments and pockets for easy access.



PN: GX40Q17225

### Lenovo Essential Compact Wireless Mouse

Compact and easy to carry, weighs just under 50g (1.76oz)  
 Ergonomic and ambidextrous design with 3 buttons  
 Highly durable design, tested to last up to 8 million clicks



PN: 4Y50R20864 – (with battery) 4Y50R20865 – (w/o battery)

# ThinkBook 14 G6 ABP

## Performance

### Processor

AMD Ryzen 3/5/7

### Operating System

Windows 11 Pro  
Windows 11 Home  
Windows 11 Home Single Language

### Graphics

AMD Radeon Graphics (integrated)

### Memory <sup>1</sup>

Up to 64GB DDR4-3200, 2x SO-DIMM

<sup>1</sup>Maximum memory is only to test technical readiness of notebook. Available memory to sell would vary.

### Storage <sup>2 3</sup>

Up to two M.2 PCIe NVMe SSD  
M.2 2242 SSD up to 1TB  
M.2 2280 SSD up to 2TB

<sup>2</sup>The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

<sup>3</sup>The system supports dual SSD via two M.2 slots, but Lenovo only offers one SSD configuration, another SSD slot for user self-extension. The max storage capacity is only technical readiness and may be different with current Lenovo storage offerings.

### Audio

High Definition (HD) Audio  
Stereo speakers, 2W x2, Dolby Audio  
Dual-microphone array with smart noise-cancelling

### Camera

HD 720p, with privacy shutter  
FHD 1080p, with privacy shutter  
FHD 1080p + IR hybrid, with privacy shutter

### Battery <sup>4</sup>

45Wh (up to 10.82 hr) battery, Rapid Charge Pro  
60Wh (up to 12.82 hr) battery, Rapid Charge

<sup>4</sup>Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

### Power Adapter

65W USB-C adapter, PD 3.0  
65W USB-C slim adapter, PD 3.0

## Design

### Display <sup>5</sup>

14" WUXGA (1920x1200) IPS Anti-glare 16:10  
- 300nits, 45% NTSC, 60Hz  
- 300nits, 45% NTSC, 60Hz, touch

14" 2.2K (2240x1400) IPS Anti-glare 16:10  
- 300nits, 100% sRGB, 60Hz

<sup>5</sup>IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

### Keyboard

6-row, spill-resistant, optional backlight

### Touchpad

Mylar surface touchpad  
75 x 120 mm (2.95 x 4.72 inches)

### Dimensions <sup>6</sup>

313.5 x 224 x 16.9 mm (12.34 x 8.82 x 0.67 inches)

<sup>6</sup>The system dimensions may vary depending on configurations.

### Weight <sup>7</sup>

Starting at 1.38 kg (3.04 lbs)

<sup>7</sup>The system weight is approximate and may vary depending on configurations

### Color

Arctic grey, dual-tone design

### Case material

Aluminium (top)  
Aluminium (bottom)

### Special Features

Modern Standby

## Connectivity

### Ethernet

Gigabit onboard Ethernet

### WLAN + Bluetooth <sup>8</sup>

802.11ax (Wi-Fi 6 or Wi-Fi 6E), Bluetooth 5.1

<sup>8</sup>Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.

### Ports

1x USB 3.2 Gen 1  
1x USB 3.2 Gen 1 (Always On)  
2x USB-C 3.2 Gen 2 (data, PD 3.0, DP 1.4)  
1x HDMI 2.1, up to 4K/60Hz  
1x Card reader  
1x Ethernet (RJ-45)  
1x Headphone / microphone combo jack (3.5mm)

### Docking

Docking support via USB-C

## Security & Privacy

Firmware TPM 2.0  
Kensington Nano Security Slot  
Touch style fingerprint reader on smart power button  
Camera privacy shutter  
IR camera for Windows Hello\*

## Certifications

### Green Certifications <sup>9 10</sup>

EPEAT Gold Registered\*  
ENERGY STAR 8.0\*  
FSC certified carton  
ErP Lot 6  
ErP Lot 26  
TCO Certified 9.0  
RoHS compliant

<sup>9</sup>The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

<sup>10</sup>EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country

### Other Certifications

TÜV Rheinland Low Blue Light (Software Solution)\*  
TÜV Rheinland Low Blue Light (Hardware Solution)\*  
MIL-STD-810H