

HP 27mq 27-inch Display (1F2J9AA)



Looks great. Performs even better

Enjoy a 27-inch diagonal big screen experience with this stylish, height-adjustable HP display, and get up to 178° ultra-wide viewing angles with consistent detail and vibrant color. This ultraslim, nearly borderless design with QHD[1] resolution comes at a great value and gives you the connections you need to easily hook up your laptop or desktop.



More screen in less space

Experience more desk space with this ultraslim, height-adjustable micro-edge display.

Outstanding viewing experience

See your screen with consistent detail, vibrant color, ultra-wide 178° viewing angles, and crisp QHD[1] resolution.

Easy connectivity

Conveniently connect your devices with HDMI and VGA ports.

Featuring

Share the panoramic view

Ultra-wide 178-degree viewing angles with consistent detail and vibrant color.

Step up to the best

IPS technology brings you clear views from almost any angle. Every seat is the best seat in the house.

QHD Display


Ultra-sharp details and captivating definition with 3.7 million pixels. [1]

Off the desk and on the wall

VESA mounts for easy mounting on a wall or arm.

Three-sided micro-edge display

See more of your screen with a three-sided micro-edge display that maximizes your viewing area.



Specifications

Display size (diagonal)	27"
Panel technology	IPS
Display size (diagonal)	68.6 cm (27")
Aspect ratio	16:9 ^[1]
Native resolution	QHD (2560 x 1440)
Resolutions supported	1024 x 768; 1280 x 1024; 1280 x 720; 1280 x 800; 1440 x 900; 1600 x 1200; 1600 x 900; 1680 x 1050; 1920 x 1080; 1920 x 1200; 640 x 480; 720 x 400; 800 x 600; 2560 x 1400
Pixel pitch	0.233 mm
Brightness	300 nits ^[1]
Contrast ratio	1000:1 ^[1]
Response time (typical)	5ms GtG ^[1]
Minimum dimensions (W x D x H)	61.42 x 5.05 x 36.79 cm (Without stand.)
Minimum dimensions (W x D x H)	24.18 x 1.984 x 14.48 in (Without stand.)
Dimensions With Stand (W x D x H)	61.42 x 21.16 x 50.49 cm
Weight	6.84 kg (With stand.)
Weight	15.08 lb (With stand.)
Display features	Anti-glare; Language selection; LED backlights; On-screen controls; Pivot rotation; Plug and Play; Height adjustable; Low blue light mode
Display Input Type	1 HDMI 1.4 (with HDCP support); 1 VGA
Onscreen controls	Brightness; Color control; Contrast; Exit; Image control; Information; Language; Management; Power control; Input control; Menu control
Display scan frequency (horizontal)	30-80 KHz
Display scan frequency (vertical)	50-60 Hz
Camera	No integrated camera
Power	Input voltage 100 to 240 VAC
Power consumption	36 W (maximum), 32 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% non-condensing
Sustainable impact specifications	Arsenic-free display glass; Low halogen; Mercury-free display backlights
Certifications and compliances	BSMI; CB; CCC; CEL
Physical security	Security lock-ready ^[3]
UPC number	(A2N) 195122299231; (ABA) 195122299262; (ABB) 195122299293; (ABT) 195122299316; (ABU) 195122299323; (ABV) 195122299361; (ABY) 195122299385; (ACQ) 195122299415; (UUG) 195122299446; (UUZ) 195122299453
What's in the box	AC power cord; Documentation; HDMI cable

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] QHD (Quad High Definition) content required to view QHD images.

Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

[3] Lock is sold separately.

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

