



EXT3-C-WP-XR-T

4K60 4:4:4 USB-C Wall-plate Transmitter
with USB, Ethernet, RS-232, & IR over
Extended-Reach HDBaseT 3.0

| HDMI | Ethernet - RJ-45 | HDBaseT
| 4K/60 UHD (4:4:4)



EXT3-C-WP-XR-T USB-C transmitter is a high-performance, extended-reach HDBaseT 3.0 transmitter for 4K60Hz (4:4:4) HDMI, USB, Ethernet, RS-232, and IR signals over twisted pair. The EXT3-C-WP-XR-T transmitter converts all input signals into the transmitted HDBaseT 3.0 signal and extends it over HDBT to a compatible receiver. The EXT3-C-WP-XR-T transmitter accepts power over the copper extension cable from a PoE provider remote device

FEATURES

Neat Room Integration - Aesthetic and modern front panel look and design that integrates nicely with design of room and podium deployments, in addition with wall-plate clean and convenient user interface, substantially increase customer and user quality of experience

High Performance Standard Extender - Professional HDBaseT extender for providing extended-reach signals over twisted-pair copper infrastructures. EXT3-C-WP-XR-T is a standard extender that can be connected to any market-available HDBaseT-compliant extension product. For optimum extension reach and performance, use recommended Kramer cables

BYOD Ease and Convenience - Connect any DP-Alt-Mode-capable USB-C device as an AV presentation source, while providing the connected device with USB 2.0 and Ethernet connection, and (if PD-2.0-capable) up to 60 watts of power, via a single USB-C cable connection only

Convenient Display Power On/Off Control - Simply press the DISPLAY ON button to toggle on and off the power of the remote CEC-enabled display; button LED indicates the power on/off status of the remote display

HDMI Signal Extension - Uncompressed 4K@60Hz (4:4:4) HDMI, HDCP 2.3, EDID and CEC signals are passed through from the source to the display

HDMI Support - Supports HDR10, deep color, x.v.Color™, HDMI uncompressed audio channels, Dolby TrueHD, DTS-HD, 2K, 4K, and 3D as specified in HDMI 2.0

HDMI Mirroring - Transmitter mirrors input HDMI signal to loop output port for connecting a local monitor

Flexible USB 2.0 Extension - An active USB host is connected to the extender at either the transmitter or receiver sides. USB 2.0 signals are extended between the extender transmitter and receiver sides, enabling connection of the active USB host to both local and remote USB devices, such as camera and audio devices, or HID (Human Interface Devices) mouse or keyboard devices

I-EDIDPro™ Kramer Intelligent EDID Processing™ - Intelligent EDID handling, processing, and pass-through algorithm that ensures Plug and Play operation for HDMI source and display systems

Multi-channel Audio Transmission - Up to 32 channels of digital stereo uncompressed signals for supporting studio-grade surround sound

Ethernet Extension - Ethernet interface data flows in both directions allowing extension of up to 1 Gbps Ethernet connectivity for LAN communication and device control

Bidirectional RS-232 Extension - Serial interface data flows in both directions allowing data transmission and device control

Infrared Extension - IR interface data flows to output port, allowing remote control of peripheral devices located at the transmitter proximity

Remote Powering - Device can be powered by PoE (power over ethernet), reducing the need for power sources

Cost-effective Maintenance - Status LED indicators for HDMI, Loop, HDBT, PoE and USB active host ports, facilitate easy local maintenance and troubleshooting

Easy and Elegant Installation - Compactly fits into standard WW 2-gang in-wall box size, supporting decorative integration with room deployed user interfaces such as electrical switches. Wall-plate installation is fast and cost-effective via a single twisted pair cable, providing multiple signals and power connections



TECHNICAL SPECIFICATIONS

Inputs	1 DP Alt Mode & PD 3.0 USB-C: On a USB type-C female connector
Outputs	1 HDBT On a female RJ-45 connector 1 LOOP HDMI On a female HDMI connector 1 IR On a 2-pin Terminal Block Connector
Ports	2 USB 2.0 On USB device type-A female connectors 1 Gbps LAN On an RJ-45 female connector 1 RS-232: On a 3-pin terminal block for serial extension
USB Features	Integrated USB Hubs 1
Extension Line	Reach: Up to 90m (295ft) Note: When using Kramer HDBaseT cables Standards Compliance: HDBaseT 3.0
Video	Max Data Rate: 18Gbps bandwidth (6Gbps per graphic channel) Max Resolution: 4K@60Hz (4:4:4) 24bpp resolution Content Protection: HDCP 2.3 HDMI Support: 4K as specified in HDMI 2.0b
Extended USB	Data Rate: Up to 480Mbps Transmitted Data Bandwidth: Up to 300Mbps Standards Compliance: 1.1 and 2.0 USB
Extended Ethernet	Max Data Rate: 1 Gbps
Extended RS-232	Baud Rate: 300 to 115200
Power	Power Adapter: Source: 20V DC, 6A Consumption: 20V DC, 4.35A Max. Power: 88W PoE Consumption: 410mA Max. Power: 19.7W USB-C Charging Max. Power: 60W Compliance: PD 3.0 USB Device Charging Max. Total Current: 2A
Enclosure	Size: WW 2 Gang Material: Aluminum Cooling: Fan ventilation

Environmental Conditions	Operating Temperature: 0° to +40°C (32° to 104°F)
	Storage Temperature: –40° to +70°C (–40° to 158°F)
	Humidity: 10% to 90%, RHL non–condensing
Regulatory Compliance (Standards Compliance)	Safety: CE, UKCA
	Environmental: RoHs and WEEE
General	PRODUCT DIMENSIONS: US: 12.1cm x 4.7cm x 12.1cm (4.8" x 1.85" x 4.8") W, D, H EU: 15.1 x 8cm x 4cm (5.9" x 3.14" x 1.5") W, D, H UK: 15.1cm x 8.6cm x 4cm (5.9" x 3.38" x 1.5") W, D, H
	PRODUCT WEIGHT: US: 0.097kg (0.21lbs) EU: 0.264kg (0.58lbs) UK: 0.28kg (0.61lbs)
	SHIPPING DIMENSIONS: US: 11.5cm x 4.7cm x 7cm (4.5" x 1.85" x 2.7") EU/UK: 29.1cm x 24cm x 8cm (11.4" x 9.44" x 3.14") W, D, H
	SHIPPING WEIGHT: US: 0.666kg (1.47lbs) approx. EU: 1.22kg (2.68lbs) approx. UK: 1.14kg (2.5lbs) approx
	Accessories Included: 1 Multi signal USB–C cable (1m), power adapter and cord
	Product Dimensions US: 12.10cm x 4.70cm x 12.10cm (4.76" x 1.85" x 4.76") W, D, H 15.10cm x 8.00cm x 4.00cm (5.94" x 3.15" x 1.57") W, D, H
Product Weight	US: 0.1kg (0.2lbs) approx
	0.3kg (0.6lbs) approx
Shipping Dimensions	US: 11.50cm x 4.70cm x 7.00cm (4.53" x 1.85" x 2.76") W, D, H
	29.10cm x 24.00cm x 8.00cm (11.46" x 9.45" x 3.15") W, D, H
Shipping Weight	US: 0.7kg (1.5lbs) approx
	1.1kg (2.5lbs) approx



CONFIGURATIONS

EXT3-C-WP-XR-T/US(W)	US Wall-Plate Transmitter, White Decora® Design Panel
EXT3-C-WP-XR-T/US(B)	US Wall-Plate Transmitter, Black Decora® Design Panel
EXT3-C-WP-XR-T/UK(W)	UK Wall-Plate Transmitter, White Panel
EXT3-C-WP-XR-T/UK(B)	UK Wall-Plate Transmitter, Black Panel
EXT3-C-WP-XR-T/EU(W)	EU Wall-Plate Transmitter, White Panel
EXT3-C-WP-XR-T/EU(B)	EU Wall-Plate Transmitter, Black Panel

