



TP-580CT

4K60 4:2:0 USB-C Transmitter with RS-232
& IR over Long-Reach HDBaseT

| HDBaseT | 4K/60 UHD (4:2:0)



TP-580CT is a high-performance, long-reach HDBaseT transmitter for 4K@60Hz (4:2:0) USB-C video, RS-232 and IR signals over twisted pair. TP-580CT converts the USB-C input video signal, along with all other input signals, into the transmitted HDBaseT signal. It extends video signals to up to 40m (130ft) over CAT copper cables at up to 4K@60Hz (4:2:0) 24bpp video resolution and provides even further reach for lower HD video resolutions

FEATURES

High Performance Standard Extender - Professional HDBaseT extender for providing long-reach signals over twisted-pair copper infrastructures. TP-580CT is a standard extender that can be connected to any market-available HDBaseT-compliant extension product. For optimum extension reach and performance, use recommended Kramer cables

BYOD Ease and Convenience - Connect any DP-Alt-Mode-capable USB-C device as an AV presentation source, while providing the connected device (if PD-2.0-capable) with up to 60 watts of power

HDMI Signal Extension - HDCP 2.2 compliant. Supports deep color, x.v.Color™, lip sync, HDMI uncompressed audio channels, Dolby TrueHD, DTS-HD, 2K, 4K, and 3D as specified in HDMI 2.0. EDID signals are passed through between the source and the display

Multi-channel Audio Extension - Up to 8 HD channels of digital stereo uncompressed signals for supporting studio-grade surround sound

Bidirectional RS-232 Extension - Serial interface data flows in both directions, allowing data transmission and device control

Bidirectional Infrared Extension - IR interface data flows in both directions, allowing remote control of peripheral devices located at either end of the extended line

Cost-effective Maintenance - Status LED indicators for power, input, output, and HDBaseT connection facilitate easy local maintenance and troubleshooting

Easy Installation - Compact DigiTOOLS® fan-less enclosure for dropped-ceiling mounting, TBUS IN-table mounting, or side-by-side mounting of 3 units in a 1U rack space with the recommended rack adapter



TECHNICAL SPECIFICATIONS

Inputs	1 DP Alt Mode & PD 3.0 USB-C: On a USB type-C connector
Outputs	1 HDBT: On an RJ-45 connector
Ports	1 IR: On a 3.5mm mini jack connector 1 RS-232: On a 3-pin terminal block connector
Extension Line	Up to 40m (130ft): At 4K @60Hz (4:2:0) Up to 70m (230ft): At full HD (1080p @60Hz 36bpp) Compliance: HDBaseT 1.0 Note: When using Kramer HDBaseT cables
Video	Max Data Rate: 10.2Gbps bandwidth (3.4Gbps per graphic channel) Max Resolution: 4K UHD @60Hz (4:2:0) 24bpp Content Protection: HDCP 2.2 signals pass-through compliance HDMI Support Deep color, x.v.Color™, lip sync, HDMI uncompressed audio channels, Dolby TrueHD, DTS-HD, 2K, 4K, and 3D as specified in HDMI 2.08, 10, or 12-bit color depth, HDR10, HLG
Extended RS-232	Baud Rate 300 to 115200
Control RS-232	Baud Rate 115200
Extended IR	Frequency 20kHz to 100kHz (bi-directional)
Power	Source: 20V DC, 6A Consumption: 3.3A
Enclosure	Size: DigiTOOLS® Type: Aluminum Cooling: Convection ventilation
Environmental Conditions	Operating Temperature: 0° to +40°C (32° to 104°F) Storage Temperature: -40° to +70°C (-40° to 158°F) Humidity: 10% to 90%, RHL non-condensing
Accessories	Power adapter:
Product Dimensions	12.00cm x 7.15cm x 2.44cm (4.72" x 2.81" x 0.96") W, D, H
Product Weight	0.2kg (0.5lbs) approx
Shipping Dimensions	23.20cm x 13.40cm x 9.70cm (9.13" x 5.28" x 3.82") W, D, H
Shipping Weight	1.0kg (2.1lbs) approx

