



C2G 25ft (7.6m) RJ45 8P8C Crossed/Rollover Modular Cable Part No. CG-02980



Constructed from heavy duty 26 AWG silver satin wire, this crossed modular cable is ideal for voice, telephone and modem communication applications. has gold-plated connectors for clearer communication. This cable is also known as a "rollover" cable which is commonly used when configuring routers.

Features & Benefits

Constructed from heavy duty 26 AWG silver satin wire

Gold-plated connectors for clearer communication

Specifications

General Info

Product Line	C2G	Color	Gray
UPC Number	757120029809	Country Of Origin	Vietnam
Application Sector	Commercial, Industrial, Residential	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	25.0 FT	Cable Length	25 ft
-------------------	---------	--------------	-------

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	REACH Compliant	Yes
--------------	-----	-----------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	26 AWG
Cable Type	Crossover, Modem	Jacket Rating	Standard / Non-Rated
Indoor/Outdoor	Indoor	Connector 2	RJ-45 Male
Connector 1	RJ-45 Male	Operating Temperature	-20°-80°C
Insulation Material	PP (Polypropylene)	Storage Temperature	-20° - 80° C