

AK-PMH1 MEDICAL MOUSE 3-BUTTON SCROLL

Corded Medical Mouse with three scroll buttons



Models may vary from the image shown

The AK-PMH12 disinfectable Medical Mouse is particularly suitable for use in the hygienically sensitive environments of hospitals, medical practices, and microbiological laboratories. The fully sealed silicone membrane enables safe surface disinfection and protects the mouse against dirt, water and liquids. Germ growth from disinfectant residues is effectively prevented by thorough wipe cleaning.

Due to the three scroll buttons and two mouse buttons as well as the high resolution optical sensor, the AK-PMH12 medical mouse enables maximum comfort and precision work.

FUNCTION AND PERFORMANCE

- Fully sealed silicone membrane with IP68 rating
- Thorough wipe disinfection from all sides
- Ergonomic design for right- and left-handers
- 5 mechanically guided mouse buttons
- High resolution optical sensor for easy and accurate cursor guidance

TECHNICAL DATA

| | |
|--|--|
| Weight main product: | 4 oz |
| Dimensions product without packaging: | 4,45 in x 2,44 in x 1,38 in |
| Weight of product incl. packaging (g): | 5.64 oz |
| Dimensions product incl. packaging: | 5,31 in x 4,53 in x 1,77 in |
| Content of master carton (pieces): | 60 |
| Weight of master carton incl. content: | 388.01 oz |
| Dimensions master carton: | 19.29 in x 16.73 in x 10.51 in |
| Cable length: | 5.91 ft |
| Storage temperature: | -4 °F - 140 °F |
| Working temperature: | 32 °F - 122 °F |
| Max. Current consumption (mA) | |
| Mouse: | 17 mA |
| Product approvals: | <ul style="list-style-type: none">• CE• EU RoHS• FCC• EN60601-1-2-2015 (IEC 4th edition)• CAN/ISED |
| System Requirements-Hardware: | USB-A |
| Operating system: | All operating systems that support USB mouse interface |
| Scope of delivery: | <ul style="list-style-type: none">• Manual• Mouse |
| Switch type: | tactile |
| Number of keys: | 5 |
| Max. resolution (dpi): | 1.000 dpi |

| | |
|---------------|---|
| Reprocessing: | <ul style="list-style-type: none">• Recommended for Wipe Disinfection• Water Tight (IP68)• Chemical-Thermal Disinfection with IP68 Sealing Caps Mounted |
|---------------|---|

| |
|---|
| <ul style="list-style-type: none">• Approved for wipe disinfection according to CDC Guideline for Disinfection and Sterilization in Healthcare Facilities according to manufacturer’s instructions. |
|---|

Protection class: IP 68

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

| Designation | Part number |
|---------------------------------------|-----------------|
| AK-PMH1 Medical Mouse 3-Button Scroll | AK-PMH120B-US-W |