

Comparison Chart



	A30	CAM130	CAM520 Pro2	CAM520 Pro3
Part Number	VISIONA30	COMCAM130	COM520PR2	COM520PR3
Room Type	Home Office/Huddle/Small	Home Office/Huddle/Small	Medium/Large	Medium/Large
Document Camera	✔	✘	✘	✘
Zoom	23X Digital	4X Digital	18X Total (12X Optical)	18X Total (12X Optical)
FOV	110°	120° Wide or 90° Depth	84.5°	80.5°
Pan	ePTZ	ePTZ	±170°	±170°
Tilt	ePTZ	ePTZ	90° (up) / 30° (down)	90° (up) / 30° (down)
Display Resolution	4K	4K	1080p	1080p
SmartFrame	✘	✔	✔	✔
SmartComposition	✘	✘	✘	✔
SmartSpeaker	✘	✘	✘	✘
Preset Framing	✘	✔	✔	✔
Presets	✘	10	10	10 on remote (128 vis RS232)
Microphone	✔	2	✘	✘
Speaker	✔	✘	✘	✘
Audio Fencing	✘	✘	✘	✘
WDR	✘	✔	✔	✔
HDMI	✔	✘	✘	✔
Bluetooth	✘	✘	✘	✘
Ethernet	✘	✘	✔	✔
PoE+	✘	✘	✔	✔
RS232	✘	✘	✔	✔
IP Streaming	✘	✘	✔	✔
Gesture Control	✘	✘	✘	✘
Fill Light	✔	✔	✘	✘
Remote	✔	✘	✔	✔
Privacy Shutter	✔	✔	✘	✘
Warranty	5 Year	3 year	3 year	3 year
Advanced Replacement	1 year	1 year	1 year	1 year



CAM550	CAM570	VB130	VB342 Pro	VB350
COMCAM550	COMCAM570	COMMVB130	COMVB342P	COMMVB350
Medium/Large	Medium/Large	Home Office/Huddle/Small	Huddle/Medium	Medium/Large
✘	✘	✘	✘	✘
24X Total (12X Optical, 2X Digital)	36X Total (12X Optical, 3X Digital)	4X Digital	15X Total (3X Optical, 5X Digital)	18X Hybrid Zoom
85°(Optical lens); 95°(AI lens)	90°(Optical lens); 95°(AI lens)	120° Wide or 90° Depth	92°	113°
±170°	±170°	ePTZ	Mechanical Pan 180°	165°
120°	120°	ePTZ	Mechanical Tilt 105°	101°
4K	4K	4K	4K	4K
✔ (Auto Framing, Preset Tracking)	✔ (Auto Framing, Preset Tracking)	✔	✔	✔
✘	✘	✘	✘	✘
✘	✔	✔	✔	✔
✔	✔	✔	✔	✔
10 on remote (128 via RS232)	10 on remote (128 via RS232)	10	10	✔
✘	✘	5	10pcs	14
✘	✘	✔	✔	✔
✘	✘	✔	✔	✔
✔	✔	✔	✔	✔
HDMI Out (1080p/60)	HDMI Out (1080p/60)	✘	✔	✔
✘	✘	✔ (optional dongle)	✔(optional dongle)	✘
✔	✔	✔	✔	✔
✔	✔	✘	✘	✘
✔	✔	✘	✔	✔
✔	✔	✘	✘	✔
✔	✔	✔	✔	✔
✘	✘	✔	✘	✘
3 year	3 year	3 year	3 year	3 year
1 year	1 year	1 year	1 year	1 year



	VC520 Pro2	VC550
Part Number	COMVCPRO2	COMMVC550
Room Type	Medium/Large	Medium/Large
Document Camera	✗	✗
Zoom	18X Total (12X Optical)	24X Total (12X Optical, 2X Digital)
FOV	84.5°	85°(Optical lens); 95°(AI lens)
Pan	±170°	±170°
Tilt	90° (up) / 30° (down)	120°
Display Resolution	1080p	4K
SmartFrame	✓	✓ (Auto Framing, Preset Tracking)
SmartComposition	✗	✗
SmartSpeaker	✗	✗
Preset Framing	✓	✓
Presets	10	10 on remote (128 via RS232)
Microphone	2	2
Speaker	✓	✓
Audio Fencing	✗	✗
WDR	✓	✓
HDMI	✗	HDMI 1.3 (1080p/30/60)
Bluetooth	✗	✓
Ethernet	✓	✓
PoE+	✗	✓
RS232	✓	✓
IP Streaming	✓	✓
Gesture Control	✗	✓
Fill Light	✗	✗
Remote	✓	✓
Privacy Shutter	✗	✗
Warranty	3 year	3 year
Advanced Replacement	1 year	1 year

	FONE540
Part Number	COMFON540
Room Type	All Sizes
Microphone	2 Omnidirectional Microphones
Pickup Distance	5m
Speakerphone	✓
Bluetooth	✗
Warranty	2 year
Advanced Replacement	1 year