

# Specifications

Last updated: 11-14-2024



	A30	CAM130	VC520 Pro3	CAM520 Pro3
Part Number	VISIONA30	COMCAM130	COMVCPR03	COM520PR3
Room Type	Home Office/Huddle/Small	Home Office/Huddle/Small	Medium/Large	Medium/Large
Document Camera	✓	✗	✗	✗
Zoom	23X Digital	4X Digital	36X Total (12X Optical)	18X Total (12X Optical)
FOV	110°	120° Wide or 90° Depth	80.5°	80.5°
Pan	ePTZ	ePTZ	±170°	±170°
Tilt	ePTZ	ePTZ	90° (up) / 30° (down)	90° (up) / 30° (down)
Display Resolution	4K	4K	1080p	1080p
SmartFrame	✗	✓	✓	✓
SmartComposition	✗	✗	✓	✓
SmartSpeaker	✗	✗	✗	✗
Preset Framing	✗	✓	✓	✓
Presets	✗	10	10	10 on remote (128 vis RS232)
Microphone	✓	2	2	✗
Speaker	✓	✗	✓	✗
Audio Fencing	✗	✗	✗	✗
WDR	✗	✓	✓	✓
HDMI	✓	✗	✓	✓
Bluetooth	✗	✗	✗	✗
Ethernet	✗	✗	✓	✓
PoE+	✗	✗	✓	✓
RS232	✗	✗	✓	✓
IP Streaming	✗	✗	✓	✓
Gesture Control	✗	✗	✓	✗
Fill Light	✓	✓	✗	✗
Remote	✓	✗	✓	✓
Privacy Shutter	✓	✓	✗	✗
Warranty	5 Year	3 year	3 year	3 year
Advanced Replacement	1 year	1 year	1 year	1 year



	CAM550	CAM570	VB130	VB342 Pro	VB350
Part Number	COMCAM550	COMCAM570	COMMVB130	COMVB342P	COMMVB350
Room Type	Medium/Large	Medium/Large	Home Office/Huddle/Small	Huddle/Medium	Medium/Large
Document Camera	✗	✗	✗	✗	✗
Zoom	24X Total (12X Optical, 2X Digital)	36X Total (12X Optical, 3X Digital)	4X Digital	15X Total (3X Optical, 5X Digital)	18X Hybrid Zoom
FOV	85°(Optical lens); 95°(AI lens)	90°(Optical lens); 95°(AI lens)	120° Wide or 90° Depth	92°	113°
Pan	±170°	±170°	ePTZ	Mechanical Pan 180°	165°
Tilt	120°	120°	ePTZ	Mechanical Tilt 105°	101°
Display Resolution	4K	4K	4K	4K	4K
SmartFrame	✓ (Auto Framing, Preset Tracking)	✓ (Auto Framing, Preset Tracking)	✓	✓	✓
SmartComposition	✗	✗	✗	✗	✗
SmartSpeaker	✗	✓	✓	✓	✓
Preset Framing	✓	✓	✓	✓	✓
Presets	10 on remote (128 via RS232)	10 on remote (128 via RS232)	10	10	✓
Microphone	✗	✗	5	10pcs	14
Speaker	✗	✗	✓	✓	✓
Audio Fencing	✗	✗	✓	✓	✓
WDR	✓	✓	✓	✓	✓
HDMI	HDMI Out (1080p/60)	HDMI Out (1080p/60)	✗	✓	✓
Bluetooth	✗	✗	✓ (optional dongle)	✓ (optional dongle)	✗
Ethernet	✓	✓	✓	✓	✓
PoE+	✓	✓	✗	✗	✗
RS232	✓	✓	✗	✓	✓
IP Streaming	✓	✓	✗	✗	✓
Gesture Control	✓	✓	✗	✓	✓
Fill Light	✗	✗	✓	✗	✗
Remote	✓	✓	✓	✓	✓
Privacy Shutter	✗	✗	✓	✗	✗
Warranty	3 year	3 year	3 year	3 year	3 year
Advanced Replacement	1 year	1 year	1 year	1 year	1 year



	FONE540	FONE700
Part Number	COMFON540	COMFON700
Room Type	All Sizes	Small/Medium/Large
Microphone	2 Omnidirectional Microphones	3 units directional + 18 units omnidirectional microphones
Pickup Distance	5m	3.5m* (*depending upon speakerphone height)
Speakerphone	✓	✓
Acoustic Echo Cancellation (AEC)	✗	✓
Advanced Noise Reduction (NR)	✗	✓
Automatic Gain Control (AGC)	✗	✓
Double-Talk Detection	✗	✓
De-Reverberation	✗	✓
AI Noise Suppression	✗	✓
Voice Fencing	✗	✓
Audio Tracking	✗	Enabled with AVer USB camera
Bluetooth	✓	✓ (optional)
Warranty	2 year	✗
Advanced Replacement	1 year	✗