

# V6 ViewPro Series

MAXHUB ViewPro series for corporate delivers a superior video conferencing experience and effortless collaboration that creates a more efficient and engaging workplace. Powered by Windows OPS, the all-in-one design integrates an intelligent dual-camera, advanced audio processing, interactive whiteboarding, and an intuitive meeting launcher into one complete collaboration display. The powerful combination makes meetings more dynamic and introduces flexible, creative interaction to your organization.



4K


## Professional 4K Display

High Color Accuracy,  $\Delta E \leq 2$   
Wide Color Gamut, NTSC 90%




## Touch Screen

20 Touch Points,  
Minimum Object Recognition - 2mm



## Wireless Screen Sharing

Share your screen through  
MAXHUB Share App




## Built-in Camera

Dual Camera(48MP+8MP)  
3x Optical Zoom  
WDR Technology Supported




## Built-in Microphone

12 meters of voice pick-up  
8 mics arrays, clear conversations



## Built-in Speaker

2.1 Channel  
2x 10W + 20W



## 10th Gen Intel CPU

Powerful performance, fluid experience  
\* With use of MT61 PC Module



## Smart Whiteboard

OCR supported,  
Multiple built-in templates



**Display**

Model	V6530	V8630
Diagonal Size(inch)	65	86
Backlight	Direct-lit LED	Direct-lit LED
Panel Technology	VA	VA
Aspect Ratio	16 : 9	16 : 9
Resolution	3840 x 2160	3840 x 2160
Response Time	6.5ms	8ms
Brightness(typ)	350cd/m <sup>2</sup>	350cd/m <sup>2</sup>
Contrast Ratio	5000 : 1	4000 : 1
Viewing Angle	178°/178°	178°/178°
Color Gamut(typ)	90% NTSC	90% NTSC
Display Orientation	Landscape	Landscape
Operating Hour	16/7	16/7

**Dimension&Weight**

Product Dimensions(WxHxD)	1500 x 921 x 88 mm 59.06 x 36.26 x 3.46 inch	1969 x 1184 x 97 mm 77.52 x 46.61 x 3.82 inch
Shipping Dimensions(WxHxD)	1638 x 1005 x 208mm 64.49 x 39.57 x 8.19 inch	2121 x 1304 x 225 mm 83.50 x 51.34 x 8.86 inch
Net Weight(kg /pounds)	37.3 kg / 82.23 pounds	60.6kg / 133.6 pounds
Gross Weight(kg /pounds)	49.0kg / 108 pounds	81.5kg / 179.68 pounds
Wall Mount(VESA)	600 x 400mm / 23.6 x 15.75inch	800 x 600mm / 31.50 x 23.62inch
Screws For VESA	M8 x 25mm / M8 x 0.99inch	M8 x 25mm / M8 x 0.99inch

**POWER**

Power Supply	AC100-240V,50/60Hz	AC100-240V,50/60Hz
Max Power Consumption	350W	450W
Standby	≤0.5W	≤0.5W

**Touch System**

Touch Sensor	IR
Accuracy	± 1mm
Max Touch Points Supported	20
Object Recognition Range	≥2mm
Glass	Zero parallax , 3mm Angi-glare, Antibacterial
Supported Operating System(Touch Return)	Windows10/Windows8/Windows7/WindowsXP/ Android/Linux/Mac OS X/Chrome OS

**Connectivity**

Input	HDMI IN x 1 , USB 2.0 x 1, USB 3.0 x 2, TOUCH 2.0 x 1 , USB Type-C x 2
Audio	Audio out x 1
Control	RS232 x 1
OPS Slot	Yes, 3840 x 2160@60fps
OPS Module Compatible	MT61
Wifi Module	SI06

**Camera/Audio/Microphone**

Built-in Camera	Yes , Dual Camera 48MP(fixed lens)+8MP(with 3x optical zoom)
Camera Features	Auto Frame / Speaker Tracking
Built-in Speakers	2.1 Channel , 10W x 2 + 20W
Microphone Array	8 x Far-field , beam-forming microphone - max 12m range

**Environment**

Operating Temperature	0 C ~40 C
Storage Temperature	10%~90%RH
Operating Humidity	-20 C ~60 C
Storage Humidity	10%~90%RH

**What's In The Box**

Standard Power Cord, 1 x Wifi module, 2 x Passive Stylus, 1 x Wall Mount, 1 x Type-C Cable (1.8m | 70.9inch)

Optional  
(Mobile Stand)



ST41B



ST23C



EST09



EST11