




REV.	DESCRIPTION	ENG.	APPROVAL

P1





Ultra High Speed HDMI™ Cable with Ethernet E***** 兄 AWM STYLE 20276 80℃ 30V VW-1

P2



SKU	Length
5001-76B-3M	3000±30

PIN Assignment
P1 HDMI AM P2 HDMI AM



SHELL _____ SHELL _____

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF INTRACOM Asia Co.,Ltd. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF INTRACOM Asia Co.,Ltd.

UNLESS OTHERWISE SPECIFIED;DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE:±1°

TOLERANCE(INCH) TOLERANCE(MM)

X ±0.02" X ±0.5mm

X.X ±0.01" X.X ±0.20mm

X.XX ±0.008" X.XX ±0.15mm

X.XXX ±0.005" X.XXX ±0.10mm

6	Cable	(1/0.34BC+1P+D/10.254TC+AL-Foil+ADHESIVE-PET)5C++1/0.32BC*1C+10.254BC*3C+AL-Foil+D/7.0.16TC+160#0.12AL BLACK PVC Jacket OD:7.3±0.15mm	M
5	MODEL	BLACK 4SP PVC molding	xxg
4	SHELL	Gun metal Black SHELL	2PCS
3	MODEL	PE,Nature color	xxg
2	Copper foil	Copper foil size:5mm	cm
1	Connector	Connector HDMI AM 19P PIN/G/F, SHELL: Gold plated & Template	2PCS
NO	ITEM	DESCRIPTION	QTY

ELECTRICAL TEST:
1.100% OPEN SHORT MIS WIRE TEST
2.CONTACT RESISTANCE:10 OHM MAX
3.INSULATION RESISTANCE:5M OHM MIN
4.HI-POT TEST:DC 300V/10ms
5.PASS 8K@60Hz,4K120Hz,4.4:4:4 TEST



安達康股份有限公司
INTRACOM Asia Co.,LTD.

TITLE:
HDMI Cable with Ethernet M-M Black

APPD
Check

YAN

CUSTOMER:

Drawer

YAN

Date
2021/05/28

CUSTOMER P/N:

Unit

mm

Projection
A4

ICT P/N:

Scale

1:1

Size:
A4

DWG.NO:

Sheet

1 of

REV. A