



Poly Sync 60 Microsoft Teams Certified Speakerphone (77P41AA)

Overview

Premium, powerful sound



Everyone deserves to hear the whole meeting — loud and clear. This smart speakerphone fills conference rooms with remarkable sound using powerful twin speakers. And be heard with six mics focusing on voices, not the noise.

Big sound, meet smart ideas

Get down to business and hear voices clearly with the smart speakerphone designed for conference rooms with Poly signature audio. Twin speakers and the six-mic array ensure everyone has a voice while helping to keep echo and noise out.

Let's get started

Users enjoy easy connectivity with their preferred way to work — connect wirelessly via Bluetooth® or wired via combined USB-A/USB Type-C®. And with a built-in USB video camera input moving from an audio to video call is super easy.[1]

Features

Six-microphone array

Experience conference calls with outside noise and distractions tuned out. A six-microphone array focuses on your voice — not the surrounding noise.

Full-duplex audio

Collaboration gets tough when one voice dominates the conversation. Full-duplex audio makes simultaneous conversations a breeze.

Audio clarity

Enjoy more clarity on every call thanks to the bass reflex system with dual passive radiators for natural voice and deep bass.

Consistent voice level

Being on the far end of the call becomes difficult in a conference call with various speakers. Poly Sync 60 features adaptive gain control for consistent voice level even if the speaker stands far from the unit.

Simple for IT

Just deploy and you're done — no new interface to learn — teams use their own devices, and work in the collaboration tools they're comfortable with. For IT, inventory tracking and updates are made easy with Poly Lens remote device management.

Certified for Microsoft Teams

Full Microsoft Teams certification takes your Microsoft Teams experience to the next level with a button for instant access to the app and more.

[1] Poly USB video device sold separately.

Additional specifications

Audio	Full duplex audio; Noise and echo reduction; Bass reflect with dual passive radiators
Bluetooth version	5.1
Button user controls	Power on/off; Wireless daisy chain
Cable length	1500 mm
Cable length (imperial)	59 in
Cartons per layer	8
Cartons per pallet	56
Certifications and compliances	CE; FCC; Rohs
Charging plug	USB Type-A to USB Type-A
Color	Silver
Compatible Operating Systems	Windows 10; macOS
Connection type	USB Type-C®; Bluetooth®; USB Type-A
Country of origin	Made in China
ECCN	EAR99
HTS code	8517620090
Indicator light	On call; On muted call; Pairing
Management Software	Poly Lens
Manufacturer Warranty	Poly standard two-year limited warranty
Master carton upc code	10017229172507
Microphone bandwidth	100 Hz to 6.7 kHz
Microphone type	Bidirectional
Minimum System Requirements	USB Type-A port
Minimum dimensions (W x D x H)	1.4 x 4.5 x 15.5 in
Minimum dimensions (W x D x H)	3.7 x 11.6 x 39.4 cm
Multiple order quantity	5
Nominal sound pressure level	95 dB SPL
Number of microphones	6
Package dimensions (W x D x H)	9.52 x 18.26 x 2.12 in
Package dimensions (W x D x H)	242 x 464 x 54 mm
Package weight	1850 g
Package weight	4.07 lb
Pallet (layers)	7
Pallet dimensions	40 x 48 x 77.95 in

Pallet dimensions (W x D x H)	101.6 x 121.9 x 198 cm
Pallet weight	517.28 kg
Pallet weight	1140.4 lb
Products per pallet	280
Products per pallet layer	40
Sensitivity (microphone)	-45 +/-3 dB
Signal-to-noise ratio	>55 dB
Speaker size	50 mm
Special features	Two highly visible status light bars for 360 degree call status indication
Supported bluetooth profiles	A2DP; AVRCP; HFP; HSP; BLE
Touch user controls	Call/answer end; Mute; Volume +/-; Programmable function button; Bluetooth® pairing; Microsoft Teams
UNSPSC code	43191515
UPC number	017229172500
Weight	2.2 lb
Weight	1 kg
What's in the box	Poly Sync 60-M; User guide; AC power adapter; USB Type-A cable with USB Type-A to USB Type-C® adapter; Installation tool
Wireless range	Up to 30 m
Wireless range (imperial)	Up to 98 ft

Services

Poly Services

★ : Recommended

Poly Support Services

3 year Poly+ Sync 60 Service	PSYNC60312 ★
1 year Poly Elite Sync 60 Service	ESYNC60112
3 year Next Business Day Hardware Advance Replacement Sync 60 Poly DaaS Service	DSYNC60DS3
3 year Partner Poly+ Sync 60 Service	PSYNC60362

Audio

★ : Recommended

Audio Accessories

Poly BT700 USB-A Bluetooth Adapter	786C4AA
Poly BT700 USB-C Bluetooth Adapter	786C5AA
Poly Sync 20 Case	85R77AA
Poly Sync 40 Charging Stand with Power Supply	85T35AA
Poly Sync 40 Charging Stand with Universal Power Supply	85R78AA
Poly Sync 40 Desk Mount	85R80AA
Poly Sync 60 Universal Power Supply	85R82AA

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.