


Interactive Display

Sharp/ NEC PN-LA752



- Most natural writing experience – InGlass™ M5 premium touch system supports patented pressure sensitivity using passive pens as well as Windows Ink and palm rejection.
- Optional Windows based Intel SDM slot-in PC – driving unlimited versatility with powerful integrated computing for quick and easy access to your apps offering a secure and locked environment.
- Energy efficiency – built-in functionality including an ambient light sensor, human presence detection and eco modes help to reduce power consumption.
- Secure by design – the non-Android platform with additional security features meets the highest IT security standards.
- Increase your productivity – benefit from a free one-year license for FlatFrog Board for Rooms. FlatFrog Board whiteboard software makes hybrid work easy and productive for everyone

Specifications

DISPLAY MODULE DATA

Panel Technology	IPS with Direct LED backlights
Native Resolution (Pixels)	3840 x 2160
Diagonal Size (inches / cm)	75 / 189.3
Aspect Ratio	16:9
Backlight Technology	LED
Brightness (cd/m2)	450
Contrast Ratio	1200:1
Response Time (grey to grey avg) ms	8
Viewing Angle (H/V) @ CR >10	178 / 178
Colour Depth [bn]	1.073 (10bit)

POWER SUPPLY AND OPERATING ENVIRONMENT

Operating Voltage(ACV) / Frequency(Hz)	100-240; 50 / 60
Power Consumption (W) (Operating MAX)	205 shipping
Operating Temperature (oC)	+5 to +35
Humidity (%)	20 to 80
Power Savings Mode [W]	< 0.5 (ECO Standby); < 2 (Networked Standby)

INSTALLATION

Landscape	•
Portrait	•
Horizontal	•
Mounting (VESA/Number of Points/Pitch mm)	4; 600 x 400

CONNECTIVITY (AUDIO/VIDEO) OUTPUT

DisplayPort	1
Audio/Headphone 3.5mm Jack	1

ACCESSORIES

Shipping Contents	1x 300 cm USB Cable; 2 x Passive Stylus; 2x AAA batteries; Blank Sticker; Bracket for Camera; Bracket for Mini PC; Cable Clamps; Display; Power Cable; Remote Control; Setup Manual
-------------------	---

KEY SPECIFICATIONS

Special Characteristics	DICOM Simulation; HDMI ARC; Powered USB Port (5 W)
24/7 Operation Certified	•
Local Dimming	•
Built in Speakers (W)	10 W + 10 W
Power Management	•

WEIGHTS AND MEASURES

Bezel Size (L/R) mm	4.8
Bezel Size (U/L) mm	4.8 / 32.3
Product Dimensions (W/H/D) mm	1,720.1 x 1,025.9 x 86.5
Product Weight Without Stand (Kg)	56.5

CONNECTIVITY (AUDIO/VIDEO) INPUT

HDMI	2
DisplayPort	1

CONNECTIVITY (CONTROL/SERIAL DATA)

RS232C IN	1
LAN Port	1
USB	4

