



10-Port USB Charging Station - 120 W

Three USB-C PD Ports up to 18 W per Port, Seven USB-A Ports up to 12 W / 2.4 A per Port, 120 W Total Output, White/Gray

Part No.: [180856](#)

EAN-13: 0766623180856 | UPC: 766623180856

Desktop Charging Station - smart and fast power for USB-C and USB-A devices

The Manhattan 10-Port USB Charging Station keeps USB-powered devices - tablets, phones, cameras, Bluetooth headphones and portable game consoles - charged and ready to go. It plugs into any standard wall outlet and offers rapid charging, so it's perfect for home, school and office use. To help with organization, ten wide bays fit most devices in their cases, keeping the countertop clean and clutter-free. That means everything can charge in one place, without having lots of chargers plugged into a power strip or devices spread all over your desk. It also means you'll have some freed-up USB chargers to stow in a laptop bag, purse, luggage bag or briefcase for when you need to charge devices away from home or the office.

Safe and high-powered charging on 10 ports simultaneously

This charging station is ultra-powerful with 10 ports pumping out a total of 120 watts of power, which means simultaneous higher-powered multi-device charging. An adaptive smart chip detects and delivers the optimal charging current for connected devices. Three USB-C Power Delivery (PD 3.0) ports deliver up to 18 W per port so newer iPhones®, iPads®, Samsung® Galaxy Tabs and other PD devices can have full batteries in a short amount of time. The other seven USB-A ports fast-charge devices with power up to 12 W / 2.4 A per port. All ports feature smart, built-in safety measures to prevent short-circuits, over-voltage, over-current and overheating.

Great for families and offices

Tech-savvy families often own two or more mobile devices, with big charging needs per family member. Bring them together with this extensive charging solution and enjoy a phone-free dinner table. In offices and conference rooms, it gives your co-workers access to charging when they need it.

Features:

- Powerful 10-in-1 fast-charger for phones, tablets, portable game consoles and other mobile devices
- Three USB-C Power Delivery (PD 3.0) ports delivering up to 18 W per port
- Seven USB-A ports delivering up to 12 W / 2.4 A per port
- Extensive charging solution for ten devices, ideal for families and offices
- Smart IC for ideal power allocation
- Overload, overcurrent and overheating protection
- Ten device storage bays, each 15 mm (0.6 in.) wide, for clutter-free use
- Rubber feet for non-slip desktop use
- Two-pole on/off switch
- Blue power LED
- Durable plastic housing
- Internal power supply and detachable 1.5 m (5 ft.) power cord included
- Three-year warranty

Specifications:

Standards and Certifications

- CE
- RoHS
- REACH
- FCC
- ETL
- UKCA

Electrical

- AC input: 100.0 - 240.0 V; 2.0 A; 50/60 Hz
- Voltage/current settings (maximum):
 - USB-C PD 18.0 W output:
 - 5.0 V / 3.0 A
 - 9.0 V / 2.0 A
 - 12.0 V / 1.5 A
 - USB-A 12.0 W output:
 - 5.0 V / 2.4 A

- Rated power: 120.0 W (max.)
- Overshoot voltage: ≤5%
- Compatible devices include but are not limited to: iPhone® 13, 13 Pro, 13 Pro Max, 13 mini, SE 2022, 12, 12 mini, 12 Pro, 12 Pro Max, X, XS, XS Max, XR, 8 Plus, 8; iPad® 10.2" / iPad mini® 8.3" / iPad Pro® 12.9" / iPad Pro 10.5" / iPad Pro 11" / iPad mini 5, Samsung® Galaxy S22, S22 Ultra, S21, S20, S10, S10 Plus, S10E, S9, S9 Plus, Note 9, S8, S8 Plus, Note 8, S7 Edge, S7, S6 Edge plus, Note 5; Google Pixel™ 6, 6XL, 5, 5XL, 4, 4 XL, 3, 3 XL; LG V60 ThinQ, V50 ThinQ, V50, V40 ThinQ, V35, V30+, V30, G8 ThinQ, G8, G6; AirPods® and AirPods Pro®, phones from Huawei®, Asus®, Sony® and more

Protection Characteristics

- Short-circuit (SCP) with auto-recovery mode
- Overvoltage (OVP) with auto-recovery mode
- Overcurrent (OCP) — current limit: 150% (max)
- Over-temperature (OTP)

Physical

- Dimensions (L x W x H): 235 x 128 x 83 mm (9.25 x 5.04 x 3.27 in.)
- Bay width: 15 mm (0.6 in.)
- Net weight: 772 g (1.7 lbs.)
- Gross weight: 848 g (1.87 lbs.)
- Housing: plastic

Operating Environment

- Operation temperature: 0 - 40°C (32 - 104°F)
- Storage temperature: -20 - 80°C (-4 - 176°F)
- Humidity (noncondensing): 5 - 90%

Package Contents

- 10-Port USB Charging Station - 120 W
- Power cord, 1.5 m (5 ft.)
- Instructions



