



Outdoor Vandalproof Gigabit PoE++ Injector

One 60 W Port, IEEE 802.3bt (4PPoE) Compliant, IP67 Waterproof, IK10 Vandalproof, Metal Housing
SKU: 561785 | EAN-13: 0766623561785 | UPC: 766623561785

Outdoor Gigabit PoE++ Injector - 60 W for an IEEE 802.3bt Powered Device

The Intellinet Network Solutions Outdoor Vandalproof Gigabit PoE++ Injector lets you connect your IEEE 802.3bt/af/at-compliant wireless access point, IP phone, network camera and more to a non-PoE LAN switch port so it can supply both a power and a network connection up to 100 meters (328 ft.) away. This 4PPoE injector has an output power rating up to 60 watts, which is enough for even very power-hungry PoE++ devices like motorized PTZ cameras, thin clients, point-of-sale systems, lighting controllers and digital signage applications.

Hardened design for outdoor and industrial use

This PoE++ injector is the right power and data connector for its suitability to a wide variety of environments. Its weatherproof IP67 (waterproof and dustproof) rating, vast operating temperature range of -40 to 75°C (-40 to 167°F) and vandal-proof IK10 score make this Power over Ethernet injector able to withstand harsh conditions and industrial environments. Beyond that, it has rating for shock (IEC 60068-2-27), freefall (IEC 60068-2-32) and vibration (IEC 60068-2-6).

Reduced wiring costs

There's no need to run AC power lines to get your PD set up and working. Once you've quickly wired DC power to the injector through its two-pin terminal block, simply connect this Ultra PoE Injector to the LAN switch port, and use the existing Cat5/6/6a cabling to deliver power as well as transfer data at 10/100/1000 Mbps speeds up to 100 m (328 ft.).

Safe protection for your expensive network equipment

The auto-sensing technology of this high-power PoE Injector ensures that your products are protected from power problems like short circuits (short GND), current overloads and high voltages. Port surge protection up to 6 kV and ESD protection up to 8 kV make its safety complete.

Wall-mount option

For full installation flexibility indoors or outdoors, you can mount the injector on the wall through its four built-in holes. The required mounting kit comes included in the package.

Features:

- Power over Ethernet with output up to 60 watts
- IP67-rated, dustproof and waterproof
- IK10-rated, vandal-proof
- Suitable for extreme operating temperatures of -40 to 75°C (-40 to 167°F)
- Compatible with IEEE 802.3bt/at/af-compliant powered devices (PD) such as network cameras, wireless access points, VoIP phones and more
- Supports 10/100/1000 Mbps data rates
- Distance support: up to 100 m (328 ft.)
- Auto-sensing PoE awareness to ensure that power is only sent to IEEE 802.3bt/at/af-compliant devices; non-PoE devices only receive data
- Short-circuit, overload and high-voltage protection
- Grounding point to protect equipment from external electrical surges
- Port surge protection up to 6 kV
- ESD protection up to 8 kV (air) and 6 kV (contact)
- Rated for shock (IEC 60068-2-27), freefall (IEC 60068-2-32) and vibration (IEC 60068-2-6)
- Mounting holes for wall mounting
- Earthing kit included
- Saves time and money by delivering data and power via existing network cables

For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Plug-and-play installation; no configuration required
- Fully NDAA-compliant
- Three-year warranty

Specifications:**Standards**

- IEEE 802.3af (Power over Ethernet)
- IEEE 802.3at (High-Power PoE+ Power over Ethernet)
- IEEE 802.3bt (PoE++/4PPoE Power over Ethernet)
- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3u (100Base-TX Fast Ethernet)
- IEEE 802.3ab (1000BASE-T Gigabit Ethernet)

General

- Media support:
 - 10Base-T Cat5e/6/6a UTP/STP RJ45
 - 100Base-TX Cat5e/6/6a UTP/STP RJ45
 - 1000Base-T Cat5e/6/6a UTP/STP RJ45
- Ports:
 - One RJ45 Gigabit data input port
 - One 2-pin terminal block power input port
 - One RJ45 PoE power + Gigabit data output port
- MTBF: 411,808 hours
- Certifications: FCC Class A, CE, RoHS, UKCA, NDAA

Electrical

- DC input: 24.0 - 56.0 V DC, 3.05 A max.; 2-pin terminal block
- DC output: 60.0 W, 55.0 V DC, 1.2 A max.; RJ45 PoE port
- Power consumption: 72.0 W (max.)

PoE Pinout (Mode A)

- Pin 1: DC (-)
- Pin 2: DC (-)
- Pin 3: DC (+)
- Pin 6: DC (+)
- Pin 7: DC (-)
- Pin 8: DC (-)

LEDs

- Power (PWR, green) and PoE (green)

Physical

- Dimensions (L x W x H): 150 x 73 x 44 mm (5.9 x 2.87 x 1.73 in.)
- Weight: 475 g (16.76 oz.)
- Housing ratings: IP67 (weather), IK10 (vandal), IEC 60068-2-27 (shock), IEC 60068-2-32 (freefall), IEC 60068-2-6 (vibration)

Environmental

- Operating temperature: -40 - 75°C (-40 - 167°F)
- Storage temperature: -40 - 80°C (-40 - 176°F)
- Operating humidity: 10 - 90% RH, non-condensing
- Storage humidity: 5 - 90% RH, non-condensing

Package Contents

- Outdoor Vandalproof Gigabit PoE++ Injector
- Earthing kit
- Three IP67-rated cable glands
- Mounting kit for wall
- Instructions

