

OS	Front panel I/O
Chrome OS	USB3 Gen1 x 3
CPU	Audio jack x 1(Combo)
Intel Jasper Lake CPU N4500	Power button with LED x 1
Memory	External power switch x 1
Dual Channel LPDDR4x 4266MT/s, 4G 4G x 2 = 8GB	Rear panel I/O
Storage	HDMI1.4b x 2
EMMC 32G	USB3 Gen1 x 2
Graphics	USB Type C x 1 (USB3 Gen1 Data transfer/Power Delivery PD65W, charging15W/DisplayPort)
Intel® UHD Graphics, integrated on CPU	GbE LAN RJ45 x 1
LAN	DC Jack x 1
Giga LAN x 1, 10/100/1000 Mbps (RTL8111)	Dual band antenna x 2
Wireless	Recovery button x 1, Kensington slot x 1
WiFi 6 802.11 b/g/n/ac/ax + BT5.2 (AX201)	Input Voltage
Dimension	AC 100~240V
159 x 119 x 31mm	Power supply
Weight	65W DC Adapter 20V/3.25A
N.W. TBC	Temperature
G.W. TBC	Operating : 0 to 40 °C
Others	Humidity
Supports Zero-TouchEnrollment	90% RH max
EPEAT Silver	Accessories
MIL-STD-810H	L-bracket
	VESA bracket (option)