

HL-L2480DW

Advance Specification Sheet

brother
at your side

Specifications:

Print	
Print Technology	Electrophotographic Laser
Simplex Print Speed (max.) ¹	Up to 36ppm
Time to First Page ²	Less than 8.5 seconds
Print Resolution (max.)	Up to 1200 x 1200
Print Emulations	PCL6, BR-Script ³ , PDF Version 1.7
Scan	
Scan Resolution (max.)	Optical: 1200 x 1200 dpi (from document glass); Interpolated: 19200 x 19200 dpi ⁴
Scan To Capability	PC (Image, Email, OCR, File), Network Folder ⁴ , SharePoint ⁴ , FTP, Mobile Devices ⁵
Advanced Scanning Features	File split, Multi-page to single-page, Base color removal
Copy	
Copy Speed / Copy Resolution (max.)	Up to 36cpm / Up to 600 x 600 dpi
Copy Options	Sorting, N-in-1, Multi-copying (up to 99), Reduce / Enlarge 25 - 400% in 1% increments
Connectivity & Compatibility	
Standard Interfaces	Wireless 802.11b/g/n (2.4GHz) / 802.11a/n (5GHz), Ethernet, Hi-Speed USB 2.0
Operating Systems Compatibility ⁶	For the latest OS compatibility and to download drivers, visit support.brother.com.
Cloud Services (Web Connect) ⁷	Google Drive™, Evernote®, OneDrive, OneNote, Dropbox, Box, SharePoint Online
Brother Cloud Apps ⁸	Easy Scan to Email, Scan to Mobile, Cloud Secure Print, Scan to Search- able PDF, Scan to Word, Scan to Excel, Scan to PowerPoint
Alexa Print	Yes
Mobile Device Compatibility ⁵	AirPrint®, Mopria™, Brother Mobile Connect, Wi-Fi Direct®
Security	
Security Features	Enterprise Security (802.1x), TLS/SSL, IP Filter, SNMP v3
Paper Handling	
Input Capacity (max.) ⁹	250-sheets paper tray, single-sheet manual feed slot
Output Capacity (max.) ⁹	100 sheets
Document Glass Size	Up to 8.5" x 11" (Letter)
Paper Size	Standard Tray: Letter, Legal, Executive, A4, A5, A6, B5, B6, Folio Manual Feed Slot: Width 3" to 8.5", Length 5" to 14" Duplex: Letter, Legal, Folio
Media Types	Standard Tray: Plain Paper, Thin Paper, Thick Paper, Recycled Paper Manual Feed Slot: Plain Paper, Thin Paper, Thick Paper, Recycled Paper, Bond, Label, Envelope (single)
Media Weights	Standard Tray: 16 to 43 lbs ¹⁰ Manual Feed Slot: 16 to 61 lbs
General	
Automatic Duplex Capability	Print
Display	2.7" Color Touchscreen
Processor	600 MHz
Memory (std.)	256 MB
Included Software ⁵	Brother Mobile Connect for iOS® and Android™ Brother iPrint&Scan (desktop) for Windows and Mac® BRAdmin Light, BRAdmin Pro, Status Monitor ⁴ , Kofax PaperPort™ SE 14 ⁴
Refresh EZ Print Subscription Eligible	Yes
Energy Star® Qualified	Yes
EPEAT Certified	Yes (Silver Rated)
Maximum Monthly Duty Cycle ¹¹	Up to 35,000 pages
Recommended Monthly Volume ¹²	Up to 2,500 pages

Replacement Supplies & Optional Accessories:

brother
genuine

TN830	Standard Yield Toner Cartridge (1,200 pages) ¹³
TN830XL	High Yield Toner Cartridge (3,000 pages) ¹³
TN830V	Value High Yield Toner Cartridge (3,300 pages) ¹³
TN830XL 2PK	Twin Pack of High Yield Black Toner Cartridges (3,000 pages per cartridge) ¹³
DR830	Drum Unit (15,000 pages) ¹⁴

Setup Information:

UPC Code	012502672678
Unit Dimensions / Weight	16.1" (W) x 15.7" (D) x 10.7" (H) / 22.2 lbs.
Carton Dimensions / Weight	22.8" (W) x 22.4" (D) x 17.1" (H) / 27.8 lbs.
Pallet Ti/Hi	4 / 2
Pallet Quantity	8
Country of Origin	Vietnam
Tariff / Harmonized Code	8443.31.0000

Carton Contents:

Brother HL-L2480DW, Starter Black Toner Cartridge (700 pages)¹³, DR830 Drum Unit (15,000 pages)¹⁴, AC Power Cord, Product Safety Guide, Reference Guide, Warranty Card, Quick Setup Guide



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

COMPATIBLE WITH
WINDOWS



- Based on one sided printing. Change from default setting required.
- From ready mode and standard tray.
- PostScript[®]3™ compatible.
- Windows only.
- May require free download. Compatibility may vary by device and operating system. Requires connection to a wireless network.
- For the latest OS compatibility and to download drivers, visit support.brother.com. Printing or scanning via macOS requires the use of AirPrint. Mac printer drivers are not provided. Server 2012/2016/2019 network printing only.
- Requires an Internet connection and an account with desired service.
- Requires and Internet connection.
- Maximum capacity based on using 20 lb. paper.
- Print speed may vary depending on size/type of paper used and paper source.

- Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
- The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
- Approximate toner cartridge yields in accordance with ISO/IEC 19752 (Letter/A4)
- Approximately 15,000 pages based on 1 page per job (letter/A4 single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media size.