



C2G

12ft (3.7m) USB-C® Male to USB-C Male Cable (20V 5A) - USB 2.0 (480Mbps)

Part No. CG-C2G28880



The USB-C® Male to USB-C Male Cable (20V 5A) - USB 2.0 (480Mbps) cable is the perfect solution for connecting two standard USB-C enabled devices or accessories for charging and data transfer.

Ensure that a USB-C equipped laptop, smartphone, or tablet is fully charged and ready to go with the 5A charging output, while simultaneously transferring photos, music, or data at speeds up to 480 Mbps.

The USB-C connector has a symmetrical design which is identical on both sides, so no more worrying about whether it's upside-down or right-side-up. It will plug in the first time, every time—while preventing damage to the connector port.

Note: C2G28880 only is USB-IF Certified

Features & Benefits

5A charging output

Data transfer speeds up to 480 Mbps

Syncs and charges USB-C enabled devices

A reversible, symmetrical USB-C connector

Plug and Play—no driver required

Specifications

General Info

Product Line	C2G	UPC Number	757120288800
Country Of Origin	China	Features	USB-C Charging
Application Sector	Residential, Commercial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	12.0 FT	Cable Length	12 ft
-------------------	---------	--------------	-------

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Bend Radius	55 mm
Thickness	5 mm	Cable Type	USB
Jacket Rating	VW-1	Amperage	5 A
Data Transfer Rate	480 MBPS	Adapter Rear	USB-C Male
Adapter Front	USB-C Male	Operating Temperature	0 C, 0 to 50 deg C C, 50 C
Voltage	20 V, 30, 0		
