



NO OPERATING SYSTEM



HIGH PRECISION WRITING



EASY SETUP



WINDOWS INK COMPATIBLE



OPS-PC READY



SIMPLICITY MADE FOR EVERY USER

A 4K interactive display that is ready when you are. Just connect your device to start, no setup, no hassle, and no learning curve. With paper-like writing, 40 touch points, built-in speakers, and Plug and Play USB Type-C connectivity, it is a complete solution. Designed to be easy and effective, the Newline C Series keeps you focused on teaching or teamwork, not on technology.



BUILT-IN COMPUTER INTERGRATION

Complete your display with an embedded OPS PC, bringing Windows directly to your display for a seamless all in one experience. Turn it on and get started!



ALL YOUR APPS AND FILES, INSTANTLY READY!

With **Plug and Play**, just connect one USB-C cable for instant audio, video, power, data, and touch. No delays, just start working.



USB Type-C



Broad Compatibility



4K HD Resolution



Maximum Viewing Angle



High Quality Sound System



Diverse Connectivity

65"

75"

86"

MODEL

C Series 65"	TT-6523C
C Series 75"	TT-7523C
C Series 86"	TT-8623C

PANEL

Backlight	Direct LED
Glass Surface	Anti-Glare Glass
Bonding Technology	Certified Zero Bonding
Display Area	65": 1429 x 804 mm
	75": 1651 x 929 mm
	86": 1896 x 1066 mm
Display Ratio	16:9
Resolution	3840 x 2160 (4K)
Colours	1,07 Billion
	65": 450 cd/m ²
	75": 450 cd/m ²
Brightness	86": 450 cd/m ²
Contrast Ratio	4000:1
Response Time	5 ms
Viewing Angle	178°
Display Life Time	≥ 50 000 hours
Transparency	> 88%
Haze	2 % ~ 5 %
Touch Surface Hardness	7 MoHs, Pencil 9H

POWER CONSUMPTION

Standard Mode*	65": 91 W
	75": 116 W
	86": 146 W
Standby mode*	<0,5 W

TOUCH

Touch Technology	Stellar Touch Technology
Touch Points	40 Windows
	20 Android/MAC/Linux
Touch Screen Writing Tools	Passive pen, Finger, Fist
Number of stylus	2
Accuracy	±1 mm

SPEAKER

Speaker Position	Front Facing
Speaker Rated Impedance	6 Ω
Speaker Max.Power Output	15 W x 2

FRONT I/O

USB Type-C	1
HDMI IN 2.0 (4k @60 Hz)	1
USB 2.0 Type-B (Touch)	1
USB 3.0 Type-A (Dynamic)	2
Microphone In (Jack 3,5 mm)	1

REAR I/O

HDMI IN 2.0 (4k @60 Hz)	2
USB 2.0 Type-B (Touch)	1
USB Type-A 2.0 (Dynamic)	2
USB Type-A 2.0 (Embedded)	1
RS232	1
RJ45 (Gigabit)	In x 1 / Out x 1
OPS Slot	1
SPDIF	1
Audio Line Out (Jack 3,5 mm)	1
VGA In	1
USB Type-C (Camera Slot)	1

SMART SYSTEM

SoC Chipset	Arm Cortex-A55 x 4
RAM	2 GB
Total Storage	8 GB
Operating System	No OS

DIMENSIONS / WEIGHT

Outline Dimensions* (Excl. wall mount)	65": 1513 x 923 x 110 mm
	75": 1735 x 1048 x 111 mm
	86": 1981 x 1186 x 111 mm
Net Weight*	65": 38,5 Kg
	75": 50 Kg
	86": 74 Kg
VESA*	65": 600 x 400 mm
	75": 800 x 400 mm
	86": 800 x 400 mm

* The provided measures are indicative and subject to further adjustments. They are not yet considered definitive.