

8K@60Hz DisplayPort 1.4 Cable

DisplayPort Male to Male, 1 m (3 ft.), Supports 4K@144Hz, HDR, Gold-plated Contacts, PVC Jacket with Latches, Black

Part No.: 355568

EAN-13: 0766623355568 | UPC: 766623355568

DisplayPort Cable featuring future-proof 8K@60Hz for high-end gaming and AV applications

The Manhattan DisplayPort Monitor Cable makes you ready for even the most demanding graphic challenges in gaming, digital signage and other high-end AV applications. Its superior DisplayPort 1.4 standard delivers images in brilliant 8K (7680 x 4320) at rapid 60 Hz or 4K UHD at blazing fast 144 Hz with HDR for perfect contrast and colors. The triple shielding and gold-plated contacts provide maximum conductivity as well as crisp, clear signal transmissions with zero EMI interference.

Features:

- DisplayPort 20-pin male to DisplayPort 20-pin male latching connections
- DisplayPort 1.4 with state-of-the art, future-proof features for high-end gaming and AV applications
- Supports resolutions 8K@60Hz, 4K@144Hz, 1440p@144Hz (UWQHD), 1440p@165Hz (WQHD) and 1080p@240Hz
- HDR for superior contrast and brilliant colors
- Supports Dolby Vision™ and Dolby Atmos®
- Up to 32.4 Gbps bandwidth
- Gold-plated contacts for corrosion-free connections
- Triple shielded to reduce EMI and other interference sources

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.
All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Unwired Pin 20 to prevent short circuits
- Supports Multi-Stream Transport (MST) to daisy-chain multiple displays
- Uncompressed 32-channel audio
- Fully compliant with DisplayPort High Bit Rate 3 (HBR3)
- Display Stream Compression 1.2 (DSC) for maximum resolution output
- HDCP 2.2 compliant
- Lifetime warranty

Specifications:

Standards and Certifications
• DisplayPort v1.4
• CE
• RoHS
• HDCP 2.2

Connectors
• Two DisplayPort 20-pin males with latches
• 19 conductors
• Gold-plated contacts
• ABS shell housing

Cable
• 28 AWG
• Triple shielding: aluminum foil and braid
• Withstanding voltage: 300 VDC
• Insulation resistance: 5 MOhm
• Contact resistance: 10 Ohm
• PVC jacket
• Length: 1 m (3 ft.)
• Weight: 69 g (2.43 oz.)

Operating Environment
• Operation temperature: 0 - 40°C (32 - 104°F)
• Storage temperature: -20 - 60°C (-4 - 140°F)
• Humidity (noncondensing): 0 - 96%

Package Contents
• 8K@60Hz DisplayPort 1.4 Cable

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.
All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.









For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.
All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.