

This USB-A to USB-C Dongle Adapter Converter for AV Ring is an easy and convenient solution for connecting a USB-C cable, USB-C hub, or USB-C peripherals to a USB-A female port on a laptop or source device. The eyelet hole on the adapter makes it a perfect addition to your new or existing HDMI AV Adapter Ring.

Pair this adapter with a USB-A laptop and the Barco ClickShare to enjoy a hybrid meeting space with flexibility for virtual collaboration.

Easily attach this USB-A to USB-C Dongle Adapter to any of our [HDMI Adapter Rings](#).

Note: This USB-A to USB-C Adapter supports USB 2.0 (480 Mbps) and will not support video transmission.

Features and Benefits:

- Adapts a USB-A female port of a laptop or source device to a USB-C port for data transmission
- Dongle style adapter reduces strain, prolonging the life of the port
- Plug-and-play, so no additional software or drivers needed
- Adapter includes a blue band around it, making it quickly identifiable when added to an HDMI AV Adapter Ring



Additional Technical Specifications

SIGNAL SPECIFICATIONS

- Testing: 100% Functional Test @ USB 2.0 (480 Mbps)

ELECTRICAL SPECIFICATIONS

- Conductor Resistance: at 20°C Max, 28 AWG: 237Ω/KM; 24 AWG: 93Ω/KM
- Voltage Rating: 30V
- Insulation Resistance: 10 Ω/KM min at 20°C DC 500V
- Dielectric Strength: AC 500V/1 Minute No Breakdown

PHYSICAL SPECIFICATIONS

- Temperature Rating: 105°C
- Minimum Bend Radius: 25mm

PHYSICAL CHARACTERISTICS

- Connector 1: USB-A Male; Solder Type, Contacts: Brass, Gold Flash, Housing: PBT, White, Shell: Nickel Plated
- Connector 2: USB-C Female; Solder Type, Contacts: Brass, Gold Flash, Housing: LCP, Black, Shell: Nickel Plated
- Adapter Hood: Molded Black (Pantone/#Black 6C) PVC
- Color Band: Blue (Pantone#801C)
- Jacket Material: PVC
- Jacket Thickness: 0.55mm AVG
- Product is CE Marked and Conforms to 2011/65/EU ROHS 2

Features & Benefits

Adapts a USB-A female port of a laptop or source device to a USB-C port for data transmission

Dongle style adapter reduces strain, prolonging the life of the port

Plug-and-play, so no additional software or drivers needed

Adapter includes a blue band around it, making it quickly identifiable when added to an HDMI AV Adapter Ring

Specifications

General Info

Product Line	C2G	Color	Black
--------------	-----	-------	-------

UPC Number	757120300618	Country Of Origin	China
------------	--------------	-------------------	-------

Application Sector	Commercial, Residential	Warranty Type	5-Year
--------------------	-------------------------	---------------	--------

Type	Active Device, Adapter, Converter
------	-----------------------------------

Dimensions

Product Length US	6.4 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

REACH Compliant	Yes
-----------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Bend Radius	25 mm
-----------------	--------------------------	-------------	-------

Jacket Rating	FT1 Rated, VW-1 Rated	Data Transfer Rate	480 Mbps
---------------	-----------------------	--------------------	----------

Adapter Rear	USB-A Male	Adapter Front	USB-C Male
--------------	------------	---------------	------------

Voltage	30 V
---------	------
