




SPECIFICATIONS

OS	Windows 11 Home Windows 11 Pro - MSI recommends Windows 11 Pro for business
CPU	Intel® Core™ i7 processor 14700 (33M Cache, 2.10 GHz up to 5.40 GHz) Intel® Core™ i5 processor 14400 (20M Cache, 2.50 GHz up to 4.70 GHz) Intel® Core™ i3 processor 14100 (12M Cache, 3.50 GHz up to 4.70 GHz)
Graphics	Intel® UHD Graphics
Chipset	Intel® H610
Memory	2x DDR5 SO-DIMMs, up to 64GB *Actual specifications will vary depending on the model.
Storage	1x M.2 SSD (PCIe / SATA Auto Switch) 1x 2.5" HDD / SSD
LAN	Intel® I219-V
Wireless LAN	Intel Wi-Fi 6E AX211 / Intel Wireless AC 9462, either one
Bluetooth	5.3 (for AX211) / 5.1 (for AC 9462)
Audio	Realtek ALC897
Audio Speaker	2x 3W
I/O	Side: 2x USB 3.2 Gen 1 Type A Rear: 1x USB 3.2 Gen 2 Type C 1x USB 3.2 Gen 2 Type A 2x USB 2.0 Type A 1x RJ45 1x HDMI™ out (supports 4K @60Hz as specified in HDMI™ 2.1) 1x DP out (1.4) 1x Mic-in 1x Line-out
Webcam	Built-in FHD Webcam which supports Windows Hello Removable webcam cover design
Touch Panel	Non-touch
Panel Resolution	27" IPS Grade Panel LED Backlight (1920*1080 FHD) with MSI Anti-Flicker technology
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Height)	0 ~ 100 mm
AC Adapter	120W
DIMENSION (WxDxH)	613.49 x 362.46 x 499.51 mm (24.15 x 14.27 x 19.67 inch)
Net Weight	6.65 kg (14.66 lbs)
Gross Weight	12.25 kg (27.01 lbs)

FEATURES



27" FHD 1080P

View your applications, spreadsheets and more with a perfect 27 inches screen with a breathtaking viewing experience that comes with Full HD resolution



100Hz High Refresh Rate

Experience smooth gaming with a blazing fast 100Hz refresh rate, that gives you the upperhand in fast moving games.




Anti-Flicker technology

MSI Anti-Flicker technology provides a very comfortable viewing experience by reducing the amount of screen flicker.



Less Blue Light

Effectively reduce blue light which could cause serious long-term damage to your eyes.



Adjustable Stand

Adjust the stand to the angle that is most suitable for you to keep yourself work comfortably.



DDR5 Memory

Elevate system performance with dual-channel DDR5 technology to enhance efficiency and stability for users.



dTPM 2.0 Support

dTPM 2.0 design secures your confidential data with encryption keys.



Tool Less Design

Assemble and disassemble the stand without any tools needed.



MSI Cloud Center


MSI Cloud Center app brings you a private cloud and helps backup files of your mobile devices (Android & iOS)



VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

CONNECTIONS



- | | |
|--|------------------------------|
| 1. 1 x DC Jack | 2. 1 x HDMI™ out (2.1) |
| 3. 1 x DisplayPort out (1.4) | 4. 1 x RJ-45 LAN |
| 5. 1 x USB 3.2 Gen 2 Type C / 1 x USB 3.2 Gen 2 Type A | 6. 2 x USB 2.0 Type A |
| 7. 1 x Mic-in | 8. 1 x Line-out |
| 9. 1 x Kensington Lock | 10. 2 x USB 3.2 Gen 1 Type A |



SECURITY UTILITY & DEVICE	MSI Center: System Diagnosis
	Tobii Aware:
	Security and Privacy: Privacy Screen/ Auto Lock/
	Peeker Detection
Certificates	Dim Screen: Energy saving
	Windows Snap
	TPM 2.0 Support
Keyboard / Mouse	Optional
MANAGEMENT UTILITY	MSI Cloud Center: Backup all of the photos and
	videos of the mobile devices (Android & iOS) MSI
	Center: Hardware Monitoring, Free Up Memory,
	Clean Up Disk, MSI Recovery, F3 Recovery, Devices
	Speed Up, Smart Priority, Smart Image Finder, Noise
	Cancellation, Live Update, Microsoft App Update,
	System Info, Troubleshooting, Contact Us, MSI Forum
	& Channel MSI Display Kit: Split Window, Display
	Setting (Orientation, resolution, refresh rate, size of
	text and app), Display Color Setting (Customizable
	Link App: Eye Saver Mode, Personal setting,
	Standard, Gaming, FPS, RTS/RPG, Cinema), Connect
	to wireless display, On-screen keyboard, Mouse
	Sensitivity, Power setting, Magnifier (Zoom in / Zoom
	out), Project way setting (internal/ Clone/ Extend/
	External)