

QUICK GUIDE

RUGGED LITE KEYBOARD, BACKLIT



A. FEATURES

1. USB 2.0 Output Cable
2. Rubber Backlit Keys
3. Touchpad
4. Mouse Buttons
5. Mounting Pockets
6. Mounting Holes
7. USB 2.0 Input Port
8. Backlit Control
9. Part Number Label



B. IMPORTANT INFORMATION

- Plug & Play USB 2.0: Supports Windows (XP or newer), Android, Linux, and Mac OS/iOS platforms (Feature 1)
- Programmable 'Emergency' Key
- Temperature Range:
 - Operating -20°C to 60°C
 - Storage -40°C to 85°C
- IP54 ingress, FCC, CE, RoHS, REACH, RCM compliant
- Tested to full Gamber-Johnson rugged standards
- Easily mount keyboard utilizing the purposefully built Gamber-Johnson Quick Release Cradle (7160-1470-00) and below mounting features:
 - Mount using the Mounting Pockets (Feature 5)
 - Or attach using #6 screws and two holes (Feature 6)
- Connect a flash drive or other digital data device to the USB 2.0 port on the side of the keyboard (Feature 7)
- Use the F12 key to cycle through the red backlit brightness. Setting 1 is the highest, setting 4 is the lowest, and setting 5 is off. (Feature 8)
- Reference the Part Number Label for product information regarding any service needs (Feature 9)

Thank you for choosing Gamber-Johnson for your keyboard needs. To learn more visit gamberjohnson.com and search part number 7160-1683.