

ThinkPad E14 Gen 6 (Intel)

Unlock new AI experiences with this ThinkPad featuring Intel® U or H Series Core™ Ultra 7 Processors, designed for high performance and ideal for demanding tasks such as gaming, content creation, and multitasking. Supported by up to 64GB DDR5-5600 memory, this laptop offers faster data transfer rates compared to previous generations, resulting in smoother multitasking, faster application load times, and overall improved system responsiveness. Moreover, with up to 1TB SSD storage, professionals can experience significantly faster read and write speeds, leading to a more efficient computing experience.



Built for business with cutting-edge technology

The entry-level ThinkPad, E Series features the famous keyboard and trackpoint, and is MIL-SPEC tested ensuring the build quality for which ThinkPad is renowned.


The HD 2W dual Dolby Atmos stereo speakers offer a rich, immersive sound experience, empowering professionals to seamlessly collaborate with colleagues and clients, even while on the move. Furthermore, the dual-microphone array with intelligent noise-cancelling technology guarantees crystal-clear voice transmission during video calls and conferences, even amidst noisy surroundings.

By connecting to a docking station or external monitor via Thunderbolt or USB-C, you can transfer data at high speed and seamlessly connect multiple displays, peripherals, and accessories. This enables efficient multitasking, fosters collaboration, and optimizes workflow.

With its compact design, optional WiFi 6 technology and thoughtful features like the optional fingerprint reader integrated power button, this device offers a great user experience at an attractive price point.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

ThinkPad Bluetooth Silent Mouse

- Left/Right hand, easy-to-carry low profile mouse
- Switch between 2 devices with dual-host Bluetooth 5.0 connectivity
- 2-way scrolling with on-the-fly DPI adjustment (2400, 1600, 800)



PN: With Battery : 4Y50X88822 Without Battery : 4Y50X88823

Lenovo Go Wireless Split Keyboard

- Human-inspired true ergonomic split keyboard with tactile and responsive, scissor switch keys
- 13-degrees splay for straight typing, comfortable neck and shoulders
- 11-degrees vertical tenting for more natural typing posture



PN: 4Y41C33748~4Y41C33789

ThinkPad E14 Gen 6 (Intel)

Performance

Processor

Intel U or H Series Core Ultra 5/7 Processor (Series 1)

Operating System

Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Ubuntu Linux

Graphics¹

Intel Graphics (integrated)
Intel Arc Graphics (integrated)

¹Intel Arc graphics only available on select H-series Intel Core Ultra processor powered systems with at least 16GB of system memory in a dual-channel configurations, otherwise it will function as Intel Graphics.

Memory²

Up to 64GB DDR5-5600, 2x SO-DIMM

²Maximum memory is only to test technical readiness of notebook. Available memory to sell would vary.

Storage^{3 4}

Up to two M.2 PCIe NVMe SSD
M.2 2242 SSD up to 1TB
M.2 2280 SSD up to 1TB

³The storage capacity supported is based on the test results with current Lenovo storage offerings.

⁴The system supports dual SSD via two M.2 slots, but Lenovo only offers one M.2 2242 SSD configuration and M.2 2280 slot for user self-extension.

Audio

High Definition (HD) Audio
audio by HARMAN stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array with noise-cancelling

Camera*

HD 720p, with privacy shutter
FHD 1080p, with privacy shutter
FHD 1080p + IR hybrid, with privacy shutter

Battery⁵

47Wh or 57Wh battery, up to 11.8 hr
47Wh battery supports Rapid Charge Pro
57Wh battery supports Rapid Charge

⁵Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0

Design

Display⁶

14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 300nits, 45% NTSC, 60Hz
- 300nits, 45% NTSC, 60Hz, touch

14" 2.2K (2240x1400) IPS Anti-glare 16:10
- 300nits, 100% sRGB, 60Hz, Eyesafe

⁶IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS

Keyboard

6-row, spill-resistant, optional backlight

Touchpad

TrackPoint and Mylar surface touchpad
56 x 115 mm (2.24 x 4.53 inches)

Dimensions⁷

Aluminium (top), aluminium (bottom) models:
313 x 219.3 x 17.99 mm (12.32 x 8.63 x 0.71 inches)

Aluminium (top), PC-ABS (bottom) models:
313 x 219.3 x 18.59 mm (12.32 x 8.63 x 0.73 inches)

⁷The system dimensions may vary depending on configurations.

Weight⁸

Aluminium (top), aluminium (bottom) models:
starting at 1.44 kg (3.17 lbs)

Aluminium (top), PC-ABS (bottom) models:
starting at 1.42 kg (3.14 lbs)

⁸The system weight is approximate and may vary depending on configurations

Color

Black
Grey

Case material

Aluminium (top), aluminium (bottom)
Aluminium (top), PC-ABS (bottom)

Connectivity

Ethernet

Gigabit onboard Ethernet

WLAN + Bluetooth*^{9 10}

802.11ax (Wi-Fi 6 or Wi-Fi 6E), Bluetooth 5.2 or 5.3
Up to Intel Wi-Fi 6E AX211, 802.11ax, Bluetooth 5.3

⁹Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

¹⁰Bluetooth may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
1x USB-C (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 & DP 1.4
1x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Ethernet (RJ-45)
1x Headphone / microphone combo jack (3.5mm)

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

Discrete TPM 2.0
Kensington Nano Security Slot
Touch style MOC fingerprint reader on power button*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*

Manageability

System Management*¹¹

Intel vPro Enterprise*

¹¹Intel vPro offers a superset of DASH's defined capabilities

Certifications

Green Certifications^{12 13 14}

EPEAT Gold Registered
ENERGY STAR 8.0
ErP Lot 6
ErP Lot 26
TCO Certified 9.0
RoHS compliant

¹²The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

¹³EPEAT registration and ENERGY STAR certification are dependent on system OS.

¹⁴EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications

Eyesafe Certified 2.0*
TÜV Rheinland Low Blue Light (Hardware Solution)*
TÜV Rheinland Low Blue Light (Software Solution)*
MIL-STD-810H