

AK-PMH3 MEDICAL MOUSE 3-BUTTON SCROLL WL

Wireless Medical Mouse with 3-button scroll for glossy surfaces



Models may vary from the image shown

The wireless AK-PMH3 Medical Mouse is ideal for hygiene-critical environments in hospitals, medical practices, and microbiological laboratories. It is 100% waterproof and can be sprayed, wiped or fully immersed in water and/or hospital-approved disinfectants. The gap-free design facilitates optimal wipe disinfection and protects against the ingress of dirt and liquids.

The technical features of the AK-PMH3 are equally impressive: the ergonomic shape, the precise 3-button scrolling and the useful wake-up-by-motion function all ensure maximum comfort and productivity. The blue light sensor guarantees precise cursor control even on glossy surfaces and the 2.4 GHz wireless connection enables safe and reliable data input.

The AK-PMH3 is an indispensable tool for both right and left-handed users in hospitals and medical practices.

FUNCTION AND PERFORMANCE

- Symmetrical left and right-handed mouse for applications in which hygiene is of the utmost importance
- Modern, elegant design that meets the highest ergonomic requirements

- Flat, gap-free design, optimally suited for wipe-down disinfection
- Fully sealed silicone membrane with IP68 rating
- Blue light sensor embedded in the bottom panel enables precise cursor control on glossy surfaces
- 2.4 GHz wireless transmission
- "Wake-up-by-motion" function

TECHNICAL DATA

Weight main product:	3 oz
Dimensions product without packaging:	4,61 in x 2,56 in x 1,3 in
Weight of product incl. packaging:	5.19 oz
Dimensions product incl. packaging:	5,31 in x 4,53 in x 1,77 in
Content of master carton (pieces):	60
Weight of master carton incl. content:	398.6 oz
Dimensions master carton:	19.29 in x 16.73 in x 10.51 in
Storage temperature:	-4 °F - 140 °F
Working temperature:	32 °F - 122 °F
Product approvals:	• CE • FCC • CAN/ISED • EU RoHS • EN60601-1-2-2015 (IEC 4th edition)
Operating system:	All operating systems that support USB mouse interface
Scope of delivery:	• Mouse • Manual • 2 x AA battery • Screwdriver
Number of keys:	5
Max. resolution (dpi):	1.000 dpi
USB dongle:	yes
2.4 Ghz wireless connection:	yes

Wireless range (m):	33 ft
Number of batteries:	2
Battery type:	Alkaline
Battery design:	AA
Battery rechargeable:	no
Battery replaceable:	yes

Reprocessing:	• Approved for wipe disinfection according to CDC Guideline for Disinfection and Sterilization in Healthcare Facilities according to manufacturer's instructions. • Chemical-Thermal Disinfection with IP68 Sealing Caps Mounted • Recommended for Wipe Disinfection • Water Tight (IP68)
Protection class:	IP 68

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Designation

AK-PMH3 Medical Mouse 3-Button Scroll WL