

AK-PMH3 MEDICAL MOUSE SCROLL SENSOR

Medical Mouse with scroll sensor for glossy surfaces



Models may vary from the image shown

The waterproof AK-PMH3 Medical Mouse is the perfect pointing device for hygiene-critical environments like hospitals, medical practices, and microbiological laboratories. It is fully sealed and can be sprayed, wiped down and completely immersed in water without damaging the device. The overall gap-free design of the AK-PMH3 allows for effortless and thorough cleaning, helping healthcare professionals and end users to main a safe and clean environment.

With its ergonomic shape that prevents wrist strain, the intuitive scrolling and the useful wake-up-by-motion function the AK-PMH3 promotes comfort and productivity. The blue light sensor enables precise cursor control even on glossy surfaces and the USB plug-and-play ensures easy setup and use in any workspace.

Both right- and left-handed users will appreciate the AK-PMH3 as an indispensable tool in healthcare settings with stringent cleaning protocols.

FUNCTION AND PERFORMANCE

- Symmetrical left and right-handed mouse for applications in which hygiene is a top priority
- Modern, elegant design that meets the highest ergonomic requirements
- Flat, gap-free design and enclosed scroll sensor for efficient and thorough wipe disinfection
- Fully sealed silicone membrane with IP68 rating
- Flat, covered blue light sensor embedded in the bottom panel enables precise cursor guidance on glossy surfaces.
- "Wake-up-by-motion" function

TECHNICAL DATA

Weight main product:	4 oz
Dimensions product without packaging:	4,61 in x 2,56 in x 1,3 in
Weight of product incl. packaging:	5.68 oz
Dimensions product incl. packaging:	5,31 in x 4,53 in x 1,77 in
Content of master carton (pieces):	60
Weight of master carton incl. content:	391.54 oz
Dimensions master carton:	19.29 in x 16.73 in x 10.51 in
Cable-length:	5.91 ft
Storage temperature:	-4 °F - 140 °F
Working temperature:	32 °F - 122 °F
Product approvals:	<ul style="list-style-type: none">• CE• FCC• CAN/ISED• EU RoHS• EN60601-1-2-2015 (IEC 4th edition)
Operating system:	All operating systems that support USB mouse interface
Scope of delivery:	<ul style="list-style-type: none">• Mouse• Manual
Number of keys:	3

Max. resolution (dpi):	1.000 dpi
Reprocessing:	<ul style="list-style-type: none"> • Approved for wipe disinfection according to CDC Guideline for Disinfection and Sterilization in Healthcare Facilities according to manufacturer's instructions. • Chemical-Thermal Disinfection with IP68 Sealing Caps Mounted • Recommended for Wipe Disinfection • Water Tight (IP68)
Protection class:	IP 68

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Designation

AK-PMH3 Medical Mouse Scroll Sensor