

N3981K

N-Series Professional Displays



- **Ideal solution for professional environments - Customize your content and display in portrait or landscape orientation across one or multiple displays**
- **Intuitive friendly software - Built-in apps enable users to connect, present and collaborate globally, both in-person and remotely**
- **Built-in media player and scheduling functionality - Create, customize and schedule media playlists and display content at a specific date or time**
- **Optimized for conferencing solutions - Compatible with a variety of accessories such as web cameras, Bluetooth speakers, and motorized carts**



The N-Series Professional Displays are designed to enhance the current conferencing setups of corporate and education settings to accommodate hybrid work and distance-learning scenarios. Intuitive friendly software enables users to connect, present and collaborate globally, both in-person and remotely.

Featuring portrait and landscape orientation, the N-Series are built for usage in corporate lobbies and reception areas, conference rooms, lecture halls, digital signage and other professional environments.

Specifications

UPC: 796435 69 049 6, EAN: 5055387666887, Colour: Black

Display	
Back light	Direct type LED
Size (diagonal)	98"
Resolution	3840x2160
Brightness	500
Contrast ratio	1,200:1
Contrast ratio (dynamic)	3,000:1
Viewing angle	178°
Response time	8ms
Life	50,000 hours
Display colors	1,070
Speaker count	2
Watts per speaker	10W
Surface hardness	3H
Glass	HAZE: 25%
Air gap	4.00mm



Physical spec	
Dimensions (W x D x H)	87.09" x 3.13" x 49.94"
Wall-hanging screw spec	M8*25mm
VESA holes	800*600
In the box	European Standard Power Cord American Standard Power Cord British Standard Power Cord HDMI Cable 3M Remote Control Battery QSG

Connections	Inputs 3 x HDMI 2.0, 1 x USB-C, 1 x USB 2.0, 1 x USB 3.0, 1 x RS232, 2 x RJ45, 1 x OPS slot Outputs 1 x HDMI 2.0, 1 x S/PDIF, 1 x Audio 3.5mm
-------------	--

Bezel size (top)	26.00mm
Bezel size (bottom)	26.00mm
Bezel size (left)	26.00mm
Bezel size (right)	26.00mm
Operating conditions	24/7
Operating temperature (max)	40°C
24/7 operation	Yes
Net weight	153 lbs
Gross weight	199.08 lbs
Wireless - antenna	Optional Accessory
Wireless - technology	802.11ac/b/g/n/a/ax
Wireless - operating frequency	2.4Ghz/5Ghz

Power	
Power supply	100-240V~ 50/60Hz
Power consumption (standby)	0.5W
Power consumption (max)	515W
Power consumption - average (watts)	340

Operation System	
System version	Android 11
CPU	Quad A55
GPU	Mali G51
RAM	4GB
Storage	32GB
OSD / display languages	17 languages: Arabic, Czech, Danish, Dutch, English, French, German, Italian, Polish, Portuguese, Romanian, Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish
Desktop software	Optoma Management Suite (OMS), Creative Board, File manager, Media player