

M-800RCT-AM

REMOTE AUDIO CONTROL PANEL W/ DISPLAY



Designed for exclusive use with the M-8080D, the M-800RCT Remote Audio Control Panel with touch display, can do volume adjustments, routing choices, preset choices and give system information.

Attention:

1. A network router is required for setting up the M-8080D.
2. All accessory connections between the M-8080D and the RD ports must be made using shielded Category 5 cables or higher, along with shielded connectors.

Key features

- 4.3" touch screen
- Input/Output signal routing
- RD port IN, for connection to M-8080D
- Preset Control
- RD port LINK for daisy chain connection
- Direct power supply by network cable
- LCD screen with output level display
- 100M Shielded CAT 5e (or better) length

Specifications

Power Source	24 V DC (Powered by M-8080D or M-804EX or external)
Input	Transmits and receives AES3 digital audio plus control dataConnect to M-8080D or M-804EX, or M-800RC, M-800RCT for daisy chain, RJ45 Connector
Output	RD EXP: Transmits and receives control dataConnect to M-800RC, or M-800RCT, RJ45 Connector
Operating Temperature	0 °C to +40°C (32°F to 104°F)
Finish	Polycarbonate + ABS resin, black
Dimensions	150 (W) x 115 (H) X 28 (D) mm (5.90" X 4.53" X 1.10")
Weight	0.28 kg (0.63 lbs.)
Included Accessories	Wall mounting screws (4 x 30)...4, Box mounting screw (4 x 20)...4Plastic anchor...4

A&E specifications

UNDEFINED TEXT